



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00						
			Z	REVISED PER ECO-14-011808	09AUG2014	AP	SB



- 1. NOTE DELETED.
- 2. NOTE DELETED.
- 3. NOTE DELETED.
- 4. NOTE DELETED.
- 5. NOTE DELETED.
- 6. SHELLS: .000200 MIN ZINC WITH YELLOW CHROMATE COATING. CONTACTS: .000030 MIN GOLD ON MATING END, .000100 MIN TIN-LEAD ON SOLDER END, BOTH OVER .000050 MIN NICKEL. OR GOLD FLASH OVER PALLADIUM-NICKEL .000030 MIN TOTAL ON MATING END, .000100 MIN TIN-LEAD ON SOLDER END, BOTH OVER .000050 MIN NICKEL.



- 7. SHELLS: .000200 MIN ZINC WITH YELLOW CHROMATE COATING. CONTACTS: GOLD PLATED FOR LENGTH OF .150 MIN FROM MATING END, GOLD FLASH IN MATED AREA, .000100 MIN TIN-LEAD ON SOLDER END, ALL OVER .000050 MIN NICKEL.
- 8. MOLDED PARTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED. COLOR: BLACK SHELLS: CARBON STEEL CONTACTS: BRASS

SUPSD BY 205733-7	7	.188	205733-8
	6	.188	205733-7
SUPSD BY 745410-5	7	.651	205733-6
SUPSD BY 745410-5	6	.651	205733-5
SUPSD BY 205733-3	7	.427	205733-4
SUPSD BY 745410-1	6	.427	205733-3
SUPSD BY 205733-1	7	.125	205733-2
	6	.125	205733-1
CONTACT FINISH		A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

8

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	.005
4 PLC	±	-
ANGLES	±	-
FINISH	6	7

DWN J. POLIGNONE 01FEB07

CHK E. BRIANT 01FEB07

APVD E. BRIANT 01FEB07

PRODUCT SPEC 108-40025

APPLICATION SPEC 114-40013

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

PLUG ASSEMBLY, SIZE 1, 9 POSN, VERTICAL AMPLIMITE HDP

SIZE A2 CAGE CODE 00779 DRAWING NO C-205733

RESTRICTED TO -

SCALE NTS SHEET 1 of 1 REV Z