



Micro ISO  
1 Form C type



Micro ISO  
1 Form A type

**RoHS compliant**

### FEATURES

- **Low profile:**  
22.5 mm(L)×15 mm(W)×15.7 mm(H)  
.886 inch(L)×.591 inch(W)×.618 inch(H)
- **Low temperature rise**  
Terminal temperature has been reduced compared with using our conventional product
- **Low sound pressure level**  
Noise level has been reduced approx.10dB compared with using our conventional product.
- **Wide line-up**  
Micro ISO terminal types and resistor inside type.
- **Plastic sealed type**  
Plastically sealed for automatic cleaning.
- **Compact and high-capacity 20A load switching**  
N.O.: 20A 14V DC, N.C.: 10A 14V DC  
(Max. carrying current: at 85°C 185°F)

### TYPICAL APPLICATIONS

- Headlights
- Magnetic clutches
- Radiator fans
- Blowers
- Fog lamps
- Tail lights
- Heaters
- Defoggers
- Horns
- Condenser fans, etc.

### ORDERING INFORMATION

ACV

Contact arrangement

1: 1 Form C

3: 1 Form A

Mounting classification

1: Micro ISO plug-in type

Protective element

0: None (Standard type)

2: With resistor inside

Coil voltage, DC

12: 12 V

### TYPES

Contact arrangement	Coil voltage	Protective construction	Mounting classification	Part No.
1 Form A	12 V DC	Sealed type	Micro ISO plug-in type	ACV31012
1 Form C			Micro ISO plug-in type	ACV11012

Note: Please use "ACV\*\*212" to order built-in resistor type. (Asterisks "\*" should be filled in from ORDERING INFORMATION.)

Standard packing: Carton: 50 pcs.; Case: 200 pcs.

### RATING

#### 1. Coil data

Nominal coil voltage	Pick-up voltage* (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [±10%] (at 20°C 68°F)	Coil resistance [±10%] (at 20°C 68°F)	Nominal operating power (at 20°C 68°F)	Usable voltage range (at 85°C 185°F)
12V DC	Max. 7.0 V DC (Initial)	Min. 0.6 V DC (Initial)	67 mA, 84 mA (with resistor)	180Ω, 142.3Ω (with resistor)	0.8 W, 1.0 W (with resistor)	10 to 16V DC

Note: \* Other pick-up voltage types are also available. Please contact us for details.

## 2. Specifications

Characteristics		Item		Specifications	
Contact	Arrangement		1 Form A		1 Form C
	Contact resistance (Initial)		Typ 3mΩ (By voltage drop 6V DC 1A)		
	Contact voltage drop (after electrical life test)		N.O.: Max. 0.2 V (By voltage drop 14 V DC 20 A)		N.O.: Max. 0.2 V (By voltage drop 14 V DC 20 A) N.C.: Max. 0.5 V (By voltage drop 14 V DC 10 A)
	Contact material		Ag alloy (Cadmium free)		
Rating	Nominal switching capacity (resistive load)		N.O.: 20 A 14V DC		N.O.: 20 A 14V DC, N.C.: 10 A 14V DC
	Max. carrying current (at 85°C 185°F, continuous)		N.O.: 20 A 14V DC		N.O.: 20 A 14V DC N.C.: 10 A 14V DC
	Nominal operating power		0.8 W, 1.0 W (built-in resistor type)		
	Min. switching capacity (resistive load)*1		1 A 12V DC		
Electrical characteristics	Insulation resistance (Initial)		Min. 20 MΩ (at 500V DC)		
	Breakdown voltage (Initial)	Between open contacts	500 Vrms for 1 min. (Detection current: 10mA)		
		Between contacts and coil	500 Vrms for 1 min. (Detection current: 10mA)		
	Operate time (at nominal voltage) (at 20°C 68°F)		Max. 10ms (excluding contact bounce time) (Initial)		
Mechanical characteristics	Release time (at nominal voltage) (at 20°C 68°F)		Max. 10ms (excluding contact bounce time) (Initial)		
	Shock resistance	Functional	Min. 100 m/s² {10G} (Half-wave pulse of sine wave: 11ms; detection time: 10μs)		
		Destructive	Min. 1,000 m/s² {100G} (Half-wave pulse of sine wave: 6ms)		
	Vibration resistance	Functional	10 Hz to 100 Hz, Min. 44.1 m/s² {4.5G} (Detection time: 10μs)		
		Destructive	10 Hz to 500 Hz, Min. 44.1 m/s² {4.5G}, Time of vibration for each direction; X, Y, Z direction: 4 hours		
Expected life	Mechanical		Min. 10⁶ (at 120 cpm)		
	Electrical (at nominal switching capacity)		Min. 10⁵ (operating frequency: 2s ON, 2s OFF)		
Conditions	Conditions for operation, transport and storage*2		Ambient temperature: -40°C to +85°C -40°F to +185°F*3, Humidity: 5% R.H. to 85% R.H. (Not freezing and condensing at low temperature), air pressure: 86 to 106kPa		
Mass			Approx. 15 g .53 oz		

Notes: \*1. This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load.

\*2. The upper operation ambient temperature limit is the maximum temperature that can satisfy the coil temperature rise value. Please refer to "Usage ambient condition" in CAUTIONS FOR USE OF AUTOMOTIVE RELAYS.


\*3. Please inquire if you will be using the relay in a high temperature atmosphere.

\* Regarding solder, this product is not MIL (Military Standard) compliant. Please evaluate solder mounting by the actual equipment before using.

## REFERENCE DATA


## 1. Coil temperature rise (20A)

Point measured: Inside the coil  
Contact carrying current: 20A  
Coil applied voltage: 13.5V




## 2. Distribution of pick-up and drop-out voltage

Sample: ACV11012, 100pcs




## 3. Distribution of operate and release time

Sample: ACV11012, 100pcs.



## 4. Ambient temperature and operating voltage range



# CV (ACV)

## 5-(1). Electrical life test (Resistive load)


Sample: ACV11012, 3pcs.

Load: Resistive load (NC switching) 10A


Switching frequency: ON 1s, OFF 1s

Ambient temperature: Room temperature


### Circuit




### Change of pick-up and drop-out voltage



### Change of contact resistance



## Load current waveform



## 5-(2). Electrical life test (Lamp load)


Sample: ACV31212, 3pcs.

Load: 55Wx4, inrush: 90A/steady: 20A, lamp actual load


Switching frequency: ON 1s, OFF 14s

Ambient temperature: Room temperature

### Change of pick-up and drop-out voltage




### Change of contact resistance




## Load current waveform

Inrush current: 90A, steady current: 20A




5-(3). Electrical life test (Motor load)  
 Sample: ACV31212, 3pcs.  
 Load: inrush: 80A/steady: 18A,  
 radiator fan actual load (motor free)  
 Switching frequency: ON 2s, OFF 6s  
 Ambient temperature: Room temperature


## Circuit



## Change of pick-up and drop-out voltage




## Change of contact resistance



## Load current waveform


Inrush current: 80A, steady current: 18A




## DIMENSIONS (mm inch)

## 1. Micro ISO plug-in type

## CAD Data




## External dimensions




## Schematic (Bottom view)

## 1 Form A



## 1 Form C



Note: Intervals between terminals is measured at A surface level.

## For Cautions for Use, see Relay Technical Information.