







Boardlock not shown
in this view

Part Number	Contact Area Plating Finish
K88X-ED-9P-BR	Gold Flash (standard option)
K88X-ED-9P-BR15	15u" Gold (15 option)
K88X-ED-9P-BR30	30u" Gold (30 option)

Material And Finish

Shell: Steel, Tin plated

Insulator: PBT with glass-fiber reinforcement,
UL 94V-0 rated,
color-black

Contact Material:

Plug - Brass

Plating Options:

(Standard) Gold flash on mating end,
tin on termination end
with nickel underplate

-15: 15 u" Gold on mating end
tin on termination end
with nickel underplate

-30: 30 u" Gold on mating end
tin on termination end
with nickel underplate

Electrical Specifications

Rated Current: 2A

Rated Voltage: 30V RMS

Dielectric Withstanding Voltage:
500 V (rms) AC for 1 minute

Insulation Resistance:
more than 1000 Megohm
at 500 V DC

Contact Resistance:
13 milliohm max.

Temperature Rating:
-55°C to +105°C

Durability:
500 mating cycles min.

RoHS COMPLIANT
EU Directive 2002/95/EC



Tolerances
X.X ± 0.25
X.XX ± 0.15
Unless Stated Otherwise

REV.	DATE	DESCRIPTION	REV. BY	CHK. BY	DRAWN BY	DATE
A1	02/14/06	New Drawing	R. Aguirre	H. MA	R. Aguirre	02/14/06
A2	1/24/08	ECO# 07-052	WILL H.	H. MA		

K88X-ED-9P-BR

D-Sub, Vertical, 9 Pin Male, RoHS Compliant, RoHS Compliant

Formed Contacts, w/ Boardlocks

