

Point of Sale

G81-8000 Series POS Keyboards



**Multifunctional Keyboards
with Magnetic Card Reader
for Commercial Applications**



Main Applications

Point of Sale

- Retail
- Hospitality
- Airlines
- Postal Services
- Car Rentals

Point of Transactions/Service

- Banking
- Government
- Healthcare
- Education
- Transportation

Key Features

- Full Size Keyboard Layout.
- Mechanical Keyswitches are Rated at 50 Million Actuations to Withstand Harsh Environments and Ensure Long Product Lifetime.
- Full US 104 Position Key Layout
- Available with PS/2 and USB Interface
- 43 Freely Programmable Keys for Easy Layout Configuration
- High Performance Magnetic Stripe Reader with Freely Programmable Headers and Terminators for Each Track
- Selection of Non-keyboard Hexcodes Enhances Security for Credit Card Processing (USB)
- Free Parsing and Configuration of Magnetic Stripe Data Stream (USB)
- Powerful 'Cherry Tools' Configuration Software Enhances Functionalities when Switching into 'Virtual Programming Mode' and Allows for Quick Product Setup & Configuration

- Easy Configuration File Transfer with Windows Explorer
- UPOS Drivers for Windows and Linux Support of Client-Server architectures
- Remote Network Installation with 'Cherry Tools' Runtime Version (USB)

Options

- 2 USB Downstream Ports (USB)
- 6&9 Pin Ports for Barcode Scanner (PS/2)
- 3-Track Magnetic Card Reader

Point of Sale

G81-8000 Series POS Keyboards

Part Number Legend



Main Part Numbers cont.

G81-8000LPAUS-2

Black PS/2 keyboard with 3-track magnetic stripe reader and 2 barcode reader ports, US 104 position key layout. Mechanical keyswitches with laser etched keycaps, 43 programmable keys. Includes Cherry Tools multifunctional configuration software and UPOS drivers.

G81-8000LUVEU-2

Black USB keyboard with 3-track magnetic stripe reader and US 104 position key layout. Mechanical keyswitches with laser etched keycaps, 43 programmable keys. Includes Cherry Tools multifunctional configuration software and UPOS drivers.

G81-8000LPAUS-0

Light grey PS/2 keyboard with 3-track magnetic stripe reader and 2 barcode reader ports, US 104 position key layout. Mechanical keyswitches, 43 programmable keys. Includes Cherry Tools multifunctional configuration software and UPOS drivers.

G81-8000LPDUS-0

Light grey PS/2 keyboard with 3-track magnetic stripe reader, US 104 position key layout. Mechanical keyswitches, 43 programmable keys. Includes Cherry Tools multifunctional configuration software and UPOS drivers.

G81-8000LPDUS-2

Black PS/2 keyboard with 3-track magnetic stripe reader and US 104 position key layout. Mechanical keyswitches, 43 programmable keys. Includes Cherry Tools multifunctional configuration software and UPOS drivers. Laser etched keys.

G81-8000LPAUS-2

Black PS/2 keyboard with 3-track magnetic stripe reader and two barcode reader ports, US 104 position key layout. Mechanical keyswitches, 43 programmable keys. Includes Cherry Tools multifunctional configuration software and UPOS drivers.

G81-8000LUVEU-0

Light grey USB keyboard with 3-track magnetic stripe reader and US 104 position key layout. Mechanical keyswitches, 43 programmable keys. Includes Cherry Tools multifunctional configuration software and UPOS drivers.

Additional product versions on request.

Point of Sale

G81-8000 Series POS Keyboards

Technical Data

Interface

PS/2, USB 2.0

Current Input

max. 100 mA (PS/2)
max. 400 mA (USB)

Magnetic Strip Reader

Standards:
ISO 7811-12, AAMVA, JIS
others on request

Reader head:
up to 1 million cycles

Reading speed:
3–125 inch/s at 75 Bit/inch
3–50 inch/s at 210 Bit/inch

Data is decoded to keyboard scancodes.

Barcode Ports

6-pin DIN 240 plug (right side)
9-pin SUB-D plug (right rear)

Touchpad

Resolution: 1000 dpi
Two switch-activated mouse buttons

Barcode Decoder

Data is decoded to keyboard scancodes. Supported barcode formats are:

EAN/UPC, Code 39, Code 128, Codabar

Interleaved 2/5, Industrial 2/5, Matrix 2/5

Code 93, Code 11, Code 16k, MSI,
Plessey

Cable Length

Approx. 1.75 m

Key Layout

Full size 104 position US key layout
including Windows keys

Weight (without/with packaging)

1800/2050 kg

Dimension

470 x 220 x 64 mm (keyboard)
520 x 280 x 72 mm (packaging)

Packaging Units

31 keyboards per master carton
2 master cartons per pallet

Keyswitch Lifetime

50 million operations

Storage Temperature

-20°C to 60°C

Operating Temperature

0°C to 50°C

Available Software

Cherry Tools
MS Windows™ 98, ME, 2000, XP

Cherry Tools Runtime:
MS Windows™ 98, ME, 2000, XP
XP Embedded

OPOS Local Edition

(OLE for Point of Sale):
MS Windows™ 98, ME, NT4, 2000,
XP, XP Embedded

OPOS Client/Server Edition:
MS Windows™ NT4, 2000, XP,
XP Embedded

JavaPOS Local Edition
(Java for Point of Sale):
MS Windows™ 98, ME, NT4, 2000,
XP, XP Embedded
Suse Linux V8.0 / Kernel 2.4 or higher
IBM JRE v1.3.x and SUN JRE V1.4.x

JavaPOS Client/Server Edition:
MS Windows™ 98, ME, NT4, 2000,
XP, XP Embedded
Suse Linux V8.0 / Kernel 2.4 or higher
IBM JRE v1.3.x and SUN JRE V1.4.x

Approvals

CE, GS, VDE, cURus, FCC, C-Tick,
VCCI, BSMI (USB only) WHQL
(Designed for Windows™ 2000 and XP)

Delivery Volume

Keyboard, Manual, CDROM

Warranty

2 years

For information on repairs or
warranty status contact:

Cherry Technical Support

Phone: 800.510.1689

E-Mail: keyboardsupport@cherrycorp.com

Contact

Call, fax or visit our
website for more information.

Last Update: 3/12/08

Cherry Electrical Products

11200 88th Avenue
Pleasant Prairie, WI 53158

Phone: 262.942.6500
Web: www.cherrycorp.com

E-Mail: sales@cherrycorp.com
Fax: 262.942.6566

The manufacturer accepts no
liability for errors or non-availability,
and reserves the right to change
specifications without prior notice.

Technical data relates to product
specifications only. Features may
differ from those described.
Only drawings combined with
product specifications shall be
deemed binding.