

Distributed by:




www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 2040196

TAP Series

Dipped Radial Tantalum Capacitors



TAP is a professional grade device manufactured with a flame retardant coating and featuring low leakage current and impedance, very small physical sizes and exceptional temperature stability. It is designed and conditioned to operate to +125°C and is available loose or taped and reeled for auto insertion. The 15 case sizes with wide capacitance and working voltage ranges means the TAP can accommodate almost any application.



Check for up-to-date CV Tables at
<http://www.avx.com/docs/catalogs/tap.pdf>

HOW TO ORDER

TAP

Type

475

Capacitance Code
 pF code: 1st two digits
 represent significant figures,
 3rd digit represents multiplier
 (number of zeros to follow)

M

Capacitance Tolerance
 K = $\pm 10\%$
 M = $\pm 20\%$
 (For J = $\pm 5\%$ tolerance,
 please consult factory)

035

Rated DC Voltage

SCS

Suffix indicating wire form
 and packaging

Capacitance Range (letter denotes case size)

Capacitance		Rated voltage DC (V _R)						
μ F	Code	6.3V	10V	16V	20V	25V	35V	50V
0.1	104						A	A
0.15	154						A	A
0.22	224						A	A
0.33	334						A	A
0.47	474						A	A
0.68	684						A	B
1.0	105				A	A	A	C
1.5	155			A	A	A	A	D
2.2	225		A	A	A	A	B	E
3.3	335	A	A	A	B	B	C	F
4.7	475	A	A	B	C	C	E	G
6.8	685	A	B	C	D	D	F	H
10	106	B	C	D	E	E	F	J
15	156	C	D	E	F	F	H	K
22	226	D	E	F	H	H	K	L
33	336	E	F	F	J	J	M	
47	476	F	G	J	K	M	N	
68	686	G	H	L	N	N		
100	107	H	K	N	N			
150	157	K	N	N				
220	227	M	P	R				
330	337	P	R					

Values outside this standard range may be available on request.

AVX reserves the right to supply capacitors to a higher voltage rating, in the same case size, than that ordered.