

CASIO®

graphic

- 26KB memory
- 900 functions
- Ideal for GCSE and A level
- 21 character x 8 line display
- Data communications with
PC and calculators
- List data function
& list based statistics
- Basic like programming



**DOT
MATRIX**

**PLASTIC
KEYS**

**ICON
MENU**

900 FUNCTIONS
Incl. **381** SCIENTIFIC
FUNCTIONS



FX9750GPLUS

CASIO®

FX9750GPLUS

Suitable for examinations	GCSE, A level & degree 15 plus True algebraic logic	Run	•
Suitable for (ages)		Angle measurements (DEG/RAD/GRA)	•
Operating system		Trigonometrics (SIN/COS/TAN)	•
Icon menu		Hyperbolics	•
Display type	DOT Matrix LCD	Base n (BIN/HEX/DEC/OCT)	•
Display size (characters x lines)	21 x 8 line	Logic operations	•
No. functions	900	Fractions	•
No. scientific functions	381	Logarithms	•
Keypad material	Plastic	Roots & powers	•
Power supply	4 x AAA & CR2032 backup	Exponents	•
		Reciprocal	•
Auto power off		Degrees/minutes/seconds	•
Battery life (hours)	150	Complex numbers	•
Case	Snap cover	Coordinate conversion	•
Total memory	26KB	Combinations & permutations	•
Parentheses	26	Numeric integration & differentiation	•
Communications port	•		
Numeric stack levels	10	Statistics	
Command stack levels	26	Single & paired variable	•
No. keys	50	Regression (linear/LOG/ EXP/power/Qued/CUBIC/ Sinusoidal logistics)	•
Mantissa + EXP	10 + 2	Distributions (NORM/T/ CHI/F/binomial/poisson)	•
Power consumption	0.06w	Test	•
Programming Language	Basic type	Interval	•
Memory reset key	•	Histograms	•
Ambient temperature range	0°C to 40°C		
Dimensions (mm)		Graphing	
Height	25	Graph solve	•
Width	90	Sketch function	•
Depth	183	Graph trace	•
Weight (gram)	215	Dual graph	•
Packaging	Box	Graph to table	•
Main Function Areas		Table to graph	•
Run	•	Dynamic graphing	•
Statistics	•	Simultaneous graphing	•
Matrices	•		
List	•	Programming	
Graphing	•	Sign change	•
Dynamic graphing	•	Function editing	•
Table	•	Backspace	•
Recursions	•	FIX/SCI/ENG	•
Conics	•	Random numbers	•
Equation solver	•	CE marked	•
Programming	•	CE (emc) regulations	EN55022
Financial function	•	Conformity	EN50082-I
PC link	•	Import tariff	8471 2020
Memory usage	•		

Specification Table