


LOC	DIST	REVISIONS 変更				DATE	DWN	APVD
J	—	P	LTR	DESCRIPTION				
			B1	REVISED PER ECO-11-005030		11MAR11	RK	HMR



SECT.
断面 A-A

SECT.
断面 B-B

SECT.
断面 C-C

NOTE;



STRESS RELIEVING
FINISH IS SUBJECT TO CHANGE BY THE TYPE OF
STRESS RELIVING PROCESS
INERT GAS FURNACE- - - -MATTE
ATOMOSPHERIC FURNACE FOLLOWED BY ACID PICKLE- - - -BRIGHT

注:



1. ストレス除去処理
処理法により外観が変わります。
不活性ガス加熱方式---無光沢
大気加熱方式---光沢

TIN PLATING 錫めっき	BRASS THICKNESS 黄銅 板厚 0.32	170384-2
—//—	BRASS THICKNESS 黄銅 板厚 0.32	170384-1
FINISH 仕上	MATERIAL 材質	PART NO. 型番

WIRE RANGE 総合電線断面積
0.3~0.5mm² (AWG#22-20)

INSULATION DIA 被覆外径
1.5~2.2mmφ

DIMENSIONS:
単位: 耗
mm

DWN J.SATO 17MAY2007

MATERIAL

SEE TABLE

FINISH

SEE TABLE

CHK S.MANABE 17MAY2007

APVD S.MANABE 17MAY2007

PRODUCT SPEC
製品規格

APPLICATION SPEC
取付適用規格

WEIGHT

NAME
名称

.250 SERIES RECEPTACLE WITHOUT LATCH

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A4

00779

C-170384

REV B1

CUSTOMER DRAWING

SCALE
尺度 4:1

SHEET 1 OF 1

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT - By -



TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

10以下 ± 0.2

10を超え30以下 ± 0.25

30を超え100以下 ± 0.3

ANGLES ± 3°

