





DESCRIPTION: F-59T TERMINATOR 1/4 WATT 5%
MODEL NUMBER: 25-7100
APPLICATION: TERMINATOR
CRIMP TOOL: N/A
IMPEDANCE: 75 OHMS
FREQUENCY RANGE: 0-750 MHz
MATERIAL: BODY BRASS NICKEL PLATED
RESISTANCE 75Ω 1/4W
RoHS COMPLIANCE: YES
TECHNICAL DETAIL: REFER TO CINCH DOCUMENT P/N 25-0000



cinch
CONNECTIVITY SOLUTIONS
a bel group

RoHS2 2011/65/EU

UNLESS OTHERWISE SPECIFIED

.X ±.3

.XX ±.10

ANGLES ±2°

INTERPRET DRAWING IN
ACCORDANCE WITH ASME
Y14.5-2009

AIM-Cambridge

Title: (CPF59T) F Type Plug Termination for
RG59

Model No. 25-7100

Size A DO NOT SCALE Date: 2015/6/26

Sheet 1 of 1