

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVO
GP	00						
			A	ORIGINAL	03APR2013	CJV	CWR

D

C

B

A

D

C

B

A

- 1


FOR MINI-APPLICATOR AND STRIPPER CRIMPER.
- 2

FOR HAND TOOL USE ONLY.
3. WIRE RANGE OF 24-28, INSULATION RANGE OF .030-.040.
4. GOLD PLATING MAY NOT APPEAR ON CARRIER STRIP. NICKEL UNDERPLATE COVERS ENTIRE CONTACT.
- 5

GOLD PLATING PER MIL-G-45204, NICKEL PLATING PER QQ-N-290.
- 6

PLATED WITH .000050 GOLD ON INSIDE OF LOCALIZED GOLD PLATE AREA, .000050 GOLD ON ZONE 1, ALL OVER .000050 NICKEL UNDERPLATE.
- 7

PLATED WITH .000050 GOLD ON INSIDE OF LOCALIZED GOLD PLATE AREA, GOLD FLASH ON ZONE 1, ALL OVER .000050 NICKEL UNDERPLATE.



STANDARD	7	1	STRIP	2-66505-7
STANDARD	6	2	LOOSE PIECE	66505-8
STANDARD	6	1	STRIP	66505-2
PACKAGING TYPE	FINISH	USE	TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-2009				DWN C. VALENTINE 03APR2013	TE Connectivity			
DIMENSIONS: INCHES				CHK C. ROHDE 03APR2013				
				APVD C. ROHDE 03APR2013	NAME			
				PRODUCT SPEC	SOCKET CONTACT, SIZE 20 DF, 24-28 AWG, W/ .030-.040 DIA INSULATION SUPPORT,			
TOLERANCES UNLESS OTHERWISE SPECIFIED:				APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -				114-10000	A2	00779	C=66505-2	-
1 PLC ± -				WEIGHT	SCALE 10:1			SHEET 1 of 1
2 PLC ± -				CUSTOMER DRAWING	REV A			
3 PLC ± .005								
4 PLC ± -								
ANGLES ± -								
FINISH 5 SEE TABLE								
MATERIAL PHOSPHOR BRONZE								

66505-2