


### MECHANICAL DATA

Dimensions in mm (inches)



### TO-3 Package (TO-204AA)

Pin 1 – Emitter

Pin 2 – Base

Pin 3 – Collector

## HIGH POWER PNP SILICON TRANSISTORS

### DESCRIPTION

Designed for use in Industrial - Military Power Amplifier and Switching Circuit Applications

### ABSOLUTE MAXIMUM RATINGS ( $T_{CASE} = 25^\circ\text{C}$ unless otherwise stated)

		<b>2N6436</b>	<b>2N6437</b>	<b>2N6438</b>
$V_{CB}$	Collector – Base Voltage	100	120	140
$V_{CEO}$	Collector – Emitter Voltage	80	100	120
$V_{EB}$	Emitter – Base Voltage		6.0V	
$I_C$	Collector Current Continuous		25A	
	Peak		50A	
$I_B$	Base Current		10A	
$P_D$	Total Device Dissipation at $T_{case} = 25^\circ\text{C}$		200W	
	Derate above $25^\circ\text{C}$		1.14W/ $^\circ\text{C}$	
$T_{stg}, T_j$	Operating and Storage Temperature Range		–65 to +200 $^\circ\text{C}$	


Semelab Plc reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Semelab is believed to be both accurate and reliable at the time of going to press. However Semelab assumes no responsibility for any errors or omissions discovered in its use. Semelab encourages customers to verify that datasheets are current before placing orders.

**Semelab plc.** Telephone +44(0)1455 556565. Fax +44(0)1455 552612.

E-mail: [sales@semelab.co.uk](mailto:sales@semelab.co.uk) Website: <http://www.semelab.co.uk>

Document Number 3252

Issue 1



2N6436  
2N6437  
2N6438

## THERMAL DATA

$R_{thj-case}$	Thermal Resistance Junction-case	Max	0.875	$^{\circ}\text{C/W}$
----------------	----------------------------------	-----	-------	----------------------

## ELECTRICAL CHARACTERISTICS FOR ( $T_{case} = 25^{\circ}\text{C}$ unless otherwise stated)

Parameter		Test Conditions	Min.	Typ.	Max.	Unit
$I_{CBO}$	Collector Cut Off Current	$V_{CB} = 100\text{V}$ $I_E = 0$ 2N6436			10	
		$V_{CB} = 120\text{V}$ $I_E = 0$ 2N6437			10	
		$V_{CB} = 140\text{V}$ $I_E = 0$ 2N6438			10	
$I_{EBO}$	Emitter Cut Off Current	$V_{EB} = 6\text{V}$ $I_C = 0$			100	$\mu\text{A}$
		$V_{CE} = 90\text{V}$ 2N6436			10	$\mu\text{A}$
		$V_{BE(\text{off})} = -1.5\text{V}$ $T_C = 150^{\circ}\text{C}$			1.0	$\text{mA}$
$I_{CEX}$	Collector Cut Off Current	$V_{CE} = 110\text{V}$ 2N6437			10	$\mu\text{A}$
		$V_{BE(\text{off})} = -1.5\text{V}$ $T_C = 150^{\circ}\text{C}$			1.0	$\text{mA}$
		$V_{CE} = 130\text{V}$ 2N6436			10	$\mu\text{A}$
$I_{CEO}$	Collector Cut off Current	$V_{BE(\text{off})} = -1.5\text{V}$ $T_C = 150^{\circ}\text{C}$			1.0	$\text{mA}$
		$V_{CE} = 40\text{V}$ $I_B = 0$ 2N6436			50	
		$V_{CE} = 50\text{V}$ $I_B = 0$ 2N6437			50	
		$V_{CE} = 60\text{V}$ $I_B = 0$ 2N6438			50	
		$I_C = 50\text{mA}$ $I_B = 0$	2N6436	80		
			2N6437	100		
			2N6438	120		
$h_{FE}^*$	DC Current Gain	$V_{CE} = 2.0\text{V}$ $I_C = 0.5\text{A}$	30			
		$V_{CE} = 2.0\text{V}$ $I_C = 10\text{A}$	20		120	
		$V_{CE} = 2.0\text{V}$ $I_C = 25\text{A}$	12			
$V_{CE(\text{sat})}$	Collector - Emitter Saturation Voltage	$I_C = 10\text{A}$ $I_B = 1.0\text{A}$			1.0	
		$I_C = 25\text{A}$ $I_B = 2.5\text{A}$			1.8	
$V_{BE(\text{sat})}$	Base Emitter Saturation Voltage	$I_C = 10\text{A}$ $I_B = 1.0\text{AV}$			1.8	
		$I_C = 25\text{A}$ $I_B = 2.5\text{A}$			2.5	
$f_T$	Current Gain - Bandwidth Product	$I_C = 1.0\text{A}$ $V_{CE} = 10\text{V}$ $f_{\text{test}} = 10\text{MHz}$	40			MHz
$C_{ob}$	Output Capacitance	$I_E = 0\text{A}$ $V_{CE} = 10\text{V}$ $f = 100\text{kHz}$			700	$\text{pF}$
$t_r$	Rise Time	$V_{CC} = 80\text{V}$ $I_C = 10\text{A}$			0.3	
		$V_{BE(\text{off})} = 6.0\text{V}$ $I_{B1} = 1.0\text{A}$				
$t_s$	Storage	$V_{CC} = 80\text{V}$ $I_C = 10\text{A}$			1.0	
		$V_{BE(\text{off})} = 6.0\text{V}$ $I_{B1} = I_{B2} = 1.0\text{A}$			0.25	

\* Pulse test: Pulse Width  $\leq 300\mu\text{s}$  , Duty Cycle  $\leq 2.0\%$

Semelab Plc reserves the right to change test conditions, parameter limits and package dimensions without notice. Information furnished by Semelab is believed to be both accurate and reliable at the time of going to press. However Semelab assumes no responsibility for any errors or omissions discovered in its use. Semelab encourages customers to verify that datasheets are current before placing orders.