

# 3mm (T1) Package Discrete LED GREEN, 5V

# BIVAR

## 3G X 5V - X


- ◆ Industry Standard 3mm (T1) Package
- ◆ RoHS Compliant
- ◆ Water Clear (C), Diffused (D), and Tinted (T) Lenses
- ◆ Available in Flange (F) and Shouldered (S) Lead Frame Styles
- ◆ 5V Operating Voltage
- ◆ Ideal for Status Indication and Display



Bivar 3mm T1 Package 5V LED is ideal for those applications equipped with regular 5V power supplies such as servers and computer peripherals. Bivar offers water clear LED lens for maximum light output, diffused LED lens for uniform light output, and tinted lens to identify the color of the LED. The Flanged LED is ideal for Panel Mount Clip & Ring assemblies. The Shouldered Lead frame LED is ideal for vertical spacer assemblies without lead bends and also has a built in strain relief feature which is ideal for right angle holder assemblies that require lead bends.

| Part Number | Material | Emitted Color | Peak. Wavelength<br>$\lambda_p$ (nm) TYP. | Lens Appearance | Viewing Angle |
|-------------|----------|---------------|-------------------------------------------|-----------------|---------------|
| 3GC5V-F     | Gap/Gap  | GREEN         | 568nm                                     | Water Clear     | 20°           |
| 3GD5V-F     |          |               |                                           | Green Diffused  | 35°           |
| 3GT5V-F     |          |               |                                           | Green Tinted    | 20°           |
| 3GC5V-S     |          |               |                                           | Water Clear     | 30°           |
| 3GD5V-S     |          |               |                                           | Green Diffused  | 40°           |
| 3GT5V-S     |          |               |                                           | Green Tinted    | 30°           |

## Part Number Designation




Bivar reserves the right to make changes at any time without notice.

# 3mm (T1) Package Discrete LED GREEN, 5V



## Outline Dimensions



Recommended Mounting  
Hole Size =  $\text{Ø}0.032^{+.003}_{-.002}$

### Outline Drawings Notes:

1. All dimensions are in inches [millimeters].
2. Standard tolerance:  $\pm 0.010$ " unless otherwise noted.
3. Tolerance of overall epoxy outline:  $\pm 0.020$ " unless otherwise noted.
4. Epoxy meniscus may extend to 0.060" max.

Bivar reserves the right to make changes at any time without notice.

# 3mm (T1) Package Discrete LED GREEN, 5V



## Absolute Maximum Ratings

T<sub>A</sub> = 25°C unless otherwise noted

|                                                                                  |              |
|----------------------------------------------------------------------------------|--------------|
| Power Dissipation                                                                | / mW         |
| Forward Current ( DC )                                                           | 8 mA         |
| Peak Forward Current <sup>1</sup>                                                | 12 mA        |
| Reverse Voltage                                                                  | 5 V          |
| Operating Temperature Range                                                      | -25 ~ +85°C  |
| Storage Temperature Range                                                        | -30 ~ +100°C |
| Lead Soldering Temperature ( 3 mm from the base of the epoxy bulb ) <sup>2</sup> | 260°C        |

Notes: 1. 10% Duty Cycle, Pulse Width ≤ 0.1 msec.      2. Solder time less than 5 seconds at temperature extreme.

## Electrical / Optical Characteristics

T<sub>A</sub> = 25°C & V<sub>f</sub> = 5V unless otherwise noted

| Part Number | Forward Voltage (V) <sup>1</sup> |     |     | Recommend Forward Current (mA) |     |     | Reverse Current (μA) | Dominant Wavelength (nm) <sup>2</sup> |     |     | Luminous Intensity I <sub>v</sub> (mcd) |     |     | Viewing Angle 2 Θ ½ (deg) |
|-------------|----------------------------------|-----|-----|--------------------------------|-----|-----|----------------------|---------------------------------------|-----|-----|-----------------------------------------|-----|-----|---------------------------|
|             | MIN                              | TYP | MAX | MIN                            | TYP | MAX | MAX                  | MIN                                   | TYP | MAX | MIN                                     | TYP | MAX | TYP                       |
| 3GC5V-F     | /                                | /   | 5.0 | /                              | /   | /   | 100                  | /                                     | /   | /   | /                                       | 40  | /   | 20                        |
| 3GD5V-F     |                                  |     |     |                                |     |     |                      | /                                     | /   | /   | /                                       | 25  | /   | 35                        |
| 3GT5V-F     |                                  |     |     |                                |     |     |                      | /                                     | /   | /   | /                                       | 40  | /   | 20                        |
| 3GC5V-S     | /                                | /   | 5.0 | /                              | /   | /   | 100                  | /                                     | /   | /   | /                                       | 40  | /   | 30                        |
| 3GD5V-S     |                                  |     |     |                                |     |     |                      | /                                     | /   | /   | /                                       | 25  | /   | 40                        |
| 3GT5V-S     |                                  |     |     |                                |     |     |                      | /                                     | /   | /   | /                                       | 40  | /   | 30                        |

Notes: 1. Tolerance of forward voltage : ±0.05V.      2. Tolerance of dominant wavelength : ±1.0nm.

Bivar reserves the right to make changes at any time without notice.

# 3mm (T1) Package Discrete LED GREEN, 5V



## Typical Electrical / Optical Characteristics

$T_A = 25^\circ\text{C}$  unless otherwise noted




Fig. 1 Relative Luminous Intensity vs. Wavelength  
@ 20mA




Fig. 2 Directivity Radiation Diagram





Fig. 3 Relative Luminous Intensity vs. Temperature

Bivar reserves the right to make changes at any time without notice.

# 3mm (T1) Package Discrete LED GREEN, 5V




## Recommended Soldering Conditions



| Recommended Lead Free Wave Soldering Profile                                                       |                                         |
|----------------------------------------------------------------------------------------------------|-----------------------------------------|
| Preheat Temperature: 100°C Max.                                                                    | Peak Temperature: 260°C Max.            |
| Preheat Time: 20 ~ 50 Seconds                                                                      | Solder Time Above 217°C: 5 Seconds Max. |
| Note: Turn off top heater at preheat to prevent the lamp body directly exposed to the heat source. |                                         |

## Packaging and Labeling Plan



|                                 |                       |
|---------------------------------|-----------------------|
| <b>Bivar, Inc.</b>              | MSL 1                 |
| 4 Thomas, Irvine, CA 92618-2593 |                       |
| LOT: XXX.XXXXX.XX               |                       |
|                                 |                       |
| Part: <b>XXXX-XXX-XXX</b>       |                       |
| Quantity: <b>.500</b>           | <b>RoHS Compliant</b> |

Anti-Static Poly Bag with Desiccant  
(500 pcs Max. per Bag)

Bivar reserves the right to make changes at any time without notice.