



NORTON

74	INTRODUCTION
76	INTRODUCTION BY MARKET
84	PRODUCT SELECTION
98	FIBRE DISCS
102	SEMI-FLEXIBLE DISCS
104	FLAP DISCS
110	MULTI-AIR® DISCS
116	NORGRIP® & SOFT-TOUCH® DISCS
128	SELF-ADHESIVE DISCS
132	PLAIN DISCS
134	DOUBLE-SIDED DISCS
136	CUT SHEETS
144	SHEETS
148	ABRASIVE SPONGES & STEEL WOOL
150	ROLLS
164	FILE BELTS
168	PORTABLE BELTS
172	NARROW BELTS
184	WIDE BELTS
186	FLAP WHEELS
192	SPEEDLOK® DISCS
200	SPECIALTIES
	– CARTRIDGE ROLLS
	– SPIRABANDS
	– SLOTTED DISCS
	– SQUARE PADS
	– SANDING STARS
	– CONES
	– FLEXI DISCS
208	TUNGSTEN CARBIDE BURRS
216	ADHESIVE PRODUCTS

**Coated
Abrasives**

The Norton coated abrasive product offering encompasses a complete range of belts, discs, rolls, sheets and flap wheels for all your polishing, welding, maintenance and repair operations needs. This extensive product range includes products designed for all types of application, including heavy stock removal, dimensioning, grinding, deburring, cleaning, blending, polishing and finishing operations.

UNDERSTANDING THE PRODUCT

R	9	8	0
BACKING	PRINCIPAL ABRASIVE	COATED	RANDOM
A - Light Paper	1 - Aluminium Oxide	Odd Number - Openkote	Differentiates different products within the same product group
F - Fibre	2 - Aluminium Oxide	Even number - Closekote	
G - Heavy Paper	3 - Aluminium Oxide		
H - Heavy Paper	4 - Silicon Carbide		
K - Cloth	6 - Emery		
Q - Various (e.g. Screen-bak & Film)	7 - Flint		
R - Cloth	8 - Zirconia Alumina		
S - Combination	9 - SG® - Ceramic Aluminium Oxide		
T - Waterproof Paper			
U - Norax®			
W - Special (Cork)			

BACKING TYPES

Whether paper, cloth, vulcanised fibre or polyester film, the backing must be smooth enough for uniform adhesive coating, strong enough to withstand grinding pressures and flexible enough to conform to contours if necessary.

ABRASIVE BONDS

There are two main types of adhesives in use, one based on animal glue, and the more common based on synthetic heat hardenable resins. The adhesive is applied with a minimum of two bonding applications. The first, or maker, coat adheres the abrasive grain to the backing ensuring proper anchoring and orientation. After drying, or curing, the second, or sizer, coat is applied. The sizer adhesive, united with the maker bond, provides final grain anchoring and the proper total adhesive level for the finished product.

ABRASIVE TYPES

The ideal abrasive grain offers maximum resistance to point wear, yet fractures before serious dulling occurs, thereby satisfying both stock removal and finishing requirements.

SYNTHETIC ABRASIVES

- Aluminium oxide is tough and well adapted to grinding high tensile materials, such as carbon steel, alloy steels, tough bronze and hard woods. Wherever toughness (ability to resist fracturing) is the main consideration, aluminium oxide out performs all other coated abrasive grains
- Silicon carbide is the hardest and sharpest of the minerals used in coated abrasives. Its hardness and sharpness make it the ideal abrasive for sanding non-ferrous metals (aluminium, brass, bronze, magnesium, titanium, etc.), rubber, glass, plastics, fibrous woods, enamel and other relatively soft materials. Silicon carbide is superior to any other abrasive in its ability to penetrate and cut faster under light pressure
- Zirconia alumina has a unique self-sharpening characteristic which gives it long life on rugged stock removal operations. Zirconia alumina is well suited for heavy grinding of metals and planing of wood, because the controlled fracturing of the grain continuously produces sharp, new abrading points
- Ceramic aluminium oxide is a long-lasting, tough, dense abrasive due to its micro structure. The extremely small micron size particles break off during grinding, producing multiple new cutting edges. As it stays sharp, especially when used in medium and high pressure operations, it cuts at a higher rate than other abrasives. Recommended for use on forged and carbon steels, high nickel and cobalt alloys

NATURAL ABRASIVES

- Emery is a natural composite of corundum and iron oxide. The particles are blocky in shape and tend to cut slowly, thereby producing a polishing action on the material being abraded. Used for general maintenance and polishing of metals and in very fine grits for highly technical polishing, such as preparing metallurgical specimens requiring very close tolerances. Emery products are black in colour

DIFFERENTIATION IN THE RANGE

Norton offers the industry's widest selection of coated abrasives to meet every customer requirement. The wide range of abrasive types used in the range are classified into 3 tiers by product shape (Best/ Better/ Good) to help you choose the right product for your specific application.

INNOVATION BEST	Using unparalleled abrasive technology, and extremely high performance abrasive grains, Norton provides innovative product solutions dedicated to improving productivity in all industrial applications	BETTER	The core of the Norton Coated Abrasive offering. These products are designed to give superior performance solutions in all abrasive applications, giving high productivity levels and low total abrasive costs
BEST	These technologically advanced products meet the demands of the most discerning user giving the highest productivity and the longest product life for the lowest operating costs	GOOD	Standard Norton products that give highly durable solutions with good performance levels

Norton offers a diverse range of products that are suitable for all commonly encountered industrial applications. To enable more effective product selection an overview of appropriate products for the main applications is given in the following pages. Pictograms and colours are used to represent the applications and these are repeated with the product details in the main section.

FERROUS 	NON-FERROUS 	STONE 
HARD WOOD 	SOFT WOOD 	SHOE REPAIR 
GLASS 		
PAINT & VARNISH 		

For further information please go to the Technical Information Section at the back of this catalogue.

Norton offers a range of coated abrasive products suitable for all metal applications including cutting, surface preparation and finishing. Norton offers the best abrasive solutions for the most stringent operations in various applications.



METAL WORKING		METAL FINISHING	
APPLICATIONS	SUITABLE PRODUCTS	APPLICATIONS	SUITABLE PRODUCTS
■ Grinding & blending welds	■ Flap discs	■ Finishing of stainless steel	■ NORaX® belts
■ Heavy grinding & deburring	■ Fibre discs	■ Cleaning & finishing	■ Flap wheels
■ Grinding all types of metals	■ Narrow belts	■ Light to heavy duty cleaning	■ BearTex® discs
■ Light to medium deburring	■ SpeedLok® discs		

FERR. & NON-FERR.			METAL																
USAGE KEY			Cut Sheets	Plain Discs	Multi-Air® Discs	Norgrip/Soft-touch® Discs	Self-adhesive	Fibre Discs	Flap Discs	Sheets	Rolls	Handy Rolls	Belts	Flap Wheels	SpeedLok® Discs	Cartridge Rolls	Spirabands	Cones	Flexi Flap Discs
CAP CODE	DESCRIPTION	APPLICATION																	
INNOVATION			BEST																
U 242	NORaX®																		
R929	SG Polyester																		
R980	SG Polyester																		
R880	NZ Polycotton																		
			BEST																
F971	SG Fibre																		
F975	SG Fibre																		
F986	SG Fibre																		
R984	SG Polyester																		
R981	SG Polyester																		
U366	AO Polyester																		
RX22/ R822	NZ Cloth																		
H231	AO Paper																		
A975	AO Paper																		

FERR.
& NON-
FERR.

METAL (CONTINUED)

USAGE KEY

Highly recommended

CAP CODE	DESCRIPTION	APPLICATION	Cut Sheets	Plain Discs	Multi-Air® Discs	Norgrip/Soft-touch® Discs	Self-adhesive	Fibre Discs	Flap Discs	Sheets	Rolls	Handy Rolls	Belts	Flap Wheels	SpeedLok® Discs	Cartridge Rolls	Spirabands	Cones	Flexi Flap Discs
BEST																			
H875	NZ Paper																		
T417	SiC Paper																		
T402	SiC Paper																		
Q132	Film																		
BETTER																			
H835	NZ Paper																		
F861	NZ Fibre																		
F827	NZ Fibre																		
F425	SiC Fibre																		
R847	NZ Polyester																		
R817	NZ Polyester																		
R222	A0 Cloth																		
Q222	A0 Cloth																		
R309	A0 Cloth																		
R427	SiC Cloth																		
R822	NZ Cloth																		
RX22/ R822	NZ Cloth																		
A275	A0 Paper																		
T489	SiC Paper																		
GOOD																			
F293	A0 Fibre																		
F228	A0 Fibre																		
R445	SiC Polyester																		
R230	A0 Cloth																		
R212	A0 Cloth																		
R293	A0 Polyester																		
R265	A0 Cloth																		
R207	A0 Cloth																		
R230	A0 Cloth																		
RV71	A0 Cloth																		
R82A	NZ Cloth																		
G422	SiC Paper																		
A621	Emery Paper																		

FERROUS



NON-FERROUS



In addition to this stock offering, Norton offers a range of made-to-order solutions designed for this application. For more information about made-to-order Coated Abrasive products please refer to the product selection tables on page 84 or contact your local Sales Representative.

Norton leads the development of coated abrasive technology in this market through innovations such as Norton Red Heat R955 with New Generation SG® grain which provides the optimum productivity at the lowest cost. Norton offers a range of products suitable for the most commonly used machines.



APPLICATIONS	SUITABLE PRODUCTS
■ Drum sanders	■ Sheets & rolls
■ Belt sanders	■ Belts
■ Edger sanders	■ Discs
■ Buffer sanders	

HARD WOOD SOFT WOOD WOOD PAINT/ VARNISH			WOOD, FLOOR, VARNISH, PAINT & COMPOSITES											
USAGE KEY			Mult-Air® Norgrip/ Soft-touch® Discs	Plain Discs	Norgrip/ Soft-touch® Discs	Self-Adhesive Discs	Double-sided Discs	Cut Sheets	Sheets	Slitted Rolls	Rotolo® Rolls	Handy Rolls	Belts	Cartridge Rolls
CAP CODE	DESCRIPTION	APPLICATION												
INNOVATION			BEST											
R955	SG Cloth													
			BEST											
A975	SG Paper													
H231	AO Paper													
			BETTER											
R222	AO Cloth													
Q222	AO Cloth													
R309	AO Cloth													
R817	NZ Cloth													
S413	SiC Combination													
S422	SiC Combination													
A275	AO Paper													
H425	SiC Paper													
T402	SiC Paper													
H835	NZ Paper													
			GOOD											
R230	AO Cloth													
G131	AO Paper													
A213	AO Paper													
G422	SiC Paper													
Q421	Film													

HARD WOOD



SOFT WOOD



PAINT & VARNISH



In addition to this stock offering, Norton offers a range of made-to-order solutions designed for this application. For more information about made-to-order Coated Abrasive products please refer to the product selection tables on page 84 or contact your local Sales Representative.

Norton supplies a full range of abrasives to cover the various needs for glass converting & finishing.



MAIN APPLICATIONS	SUITABLE PRODUCTS
▀ Edge grinding	▀ Narrow belts
▀ Edge finishing	▀ Cork belts
▀ Removal of coating after cutting	▀ BearTex® wheels
▀ Windshield logo removal	▀ File narrow belts

GLASS



GLASS

USAGE KEY

 Highly recommended

CAP CODE	DESCRIPTION	APPLICATION	Belts
INNOVATION			BEST
U366	NORaX®		
			BEST
R427	SiC Cloth		
			BETTER
W445	Cork Polyester		
			GOOD
R445	SiC Polyester		

In addition to this stock offering, Norton offers a range of made-to-order solutions designed for this application. For more information about made-to-order Coated Abrasive products please refer to the product selection tables on page 84 or contact your local Sales Representative.



Norton offer a full range of silicon carbide discs dedicated to the main applications for stone and marble finishing.

MAIN APPLICATIONS	SUITABLE PRODUCTS
■ Polishing	■ Plain discs, Norgrip® discs
■ Cleaning & finishing	■ Flap discs

STONE 									
USAGE KEY			Plain Discs	Semi-Flexible Discs	Double-sided Discs	Fibre Discs	Cut Sheets	Portable belts	Rolls
 Highly recommended									
CAP CODE	DESCRIPTION	APPLICATION							
BEST									
Q400	SiC								
BETTER									
F425	SiC Fibre								
H425	SiC Paper								
G422	SiC Paper								
GOOD									
R427	SiC Cloth								

In addition to this stock offering, Norton offers a range of made-to-order solutions designed for this application. For more information about made-to-order Coated Abrasive products please refer to the product selection tables on page 84 or contact your local Sales Representative.

Norton has vast experience of supplying belts for shoe repair application and the products are widely recognised as being the best available in this market.



MAIN APPLICATIONS	SUITABLE PRODUCTS
- Edge chamfering - Edge grinding	- Cones Specialties - Belts

SHOE  SHOE REPAIR				
USAGE KEY  Highly recommended				
CAP CODE	DESCRIPTION	APPLICATION	Cones	Belts
BETTER				
R817	NZ Polyester			
R822	NZ Cloth			

In addition to this stock offering, Norton offers a range of made-to-order solutions designed for this application. For more information about made-to-order Coated Abrasive products please refer to the product selection tables on page 84 or contact your local Sales Representative.

NOTES

This image shows a single sheet of white paper with horizontal blue lines, resembling notebook paper. The lines are evenly spaced and run across the width of the page. There is no text or other markings on the paper.

PRODUCT SELECTION

USAGE KEY

 Stock products

 Made-to-order

PRODUCT CODE	DESCRIPTION	3000	2500	2000	1500	1200	1000	800	600	500	400	360
FIBRE DISCS												
F228	0.6-0.8 Wt Fibre AO											
F293	0.6-0.8 Wt Fibre AO											
F425	0.6-0.8 Wt Fibre SiC											
F827	0.6-0.8 Wt Fibre Zir											
F861	0.8 Wt Fibre ZR/AO											
F975	0.8 Wt Fibre SG											
F971	0.8 Wt Fibre SG											
FLAP DISCS												
R980	X Cotton Heavy Cloth SG											
R880	X Cotton Heavy Cloth Zir											
R265	X Cotton Heavy Cloth AO											
R822	X Cotton Heavy Cloth Zir											
RX22/R822	X Cotton Heavy Cloth SG											
DISCS												
A277	E* Wt Heavy Paper AO											
A275 Soft-Touch®	B Wt Soft Touch® AO											
A275 Norgrip®	B/E* Wt AO											
A975 Soft-Touch®	B Wt Soft Touch® AO											
A975 Norgrip®	B Wt SG/AO											
G131 Norgrip®	E* Wt AO											
G422	E Wt Heavy Paper SiC											
G422 Norgrip®	E Wt SiC											
H822	E Wt Heavy Paper ZR											
H231 Norgrip®	F Wt AO											
H425	E Wt Heavy Paper SiC											
H425 Norgrip®	E Wt SiC											
H835	E Wt Heavy Paper ZR/AO											
Q421	Grid Wt SiC											
Q263	Grid Wt SiC											
R293	X/Y Poly Wt AO/SG											
R445	X/Y Poly Wt SiC											
R473	X Poly Wt Aggreg. SiC											

	320	280	240	220	180	150	120	100	80	60	50	40	36	30	24	20	16	PRODUCT CODE
																		F228
																		F293
																		F425
																		F827
																		F861
																		F975
																		F971
																		R980
																		R880
																		R265
																		R822
																		RX22/R822
																		A277
																		A275 Soft-Touch®
																		A275 Norgrip®
																		A975 Soft-Touch®
																		A975 Norgrip®
																		G131 Norgrip®
																		G422
																		G422 Norgrip®
																		H822
																		H231 Norgrip®
																		H425
																		H425 Norgrip®
																		H835
																		Q421
																		Q263
																		R293
																		R445
																		R473

PRODUCT SELECTION

USAGE KEY

 Stock products

 Made-to-order

PRODUCT CODE	DESCRIPTION	3000	2500	2000	1500	1200	1000	800	600	500	400	360
DISCS (CONTINUED)												
R230	X Cotton Heavy Cloth AO											
R270	X Poly Wt Aggreg. AO											
R275	X - Poly Wt Aggreg. AO											
R287	J Cotton Wt Light Cloth AO											
R296	JJ Cotton Wt Light Cloth SG/AO											
R309	JJ Cotton Wt Light Cloth AO											
R426	J Cotton Wt Light Cloth SiC											
R427	X Cotton Heavy Cloth SiC											
R817	Y Poly Wt Zir											
R823	Y Poly Wt ZR/AO											
R846	Y Poly Wt ZR/AO											
R847	Y Poly Wt Zir											
R922	X Cotton Wt Heavy Cloth SG/AO											
R926	X Cotton Wt Heavy Cloth SG/AO											
R949	X Poly Wt SG/AO											
R984	Y Poly Wt SG											
RX84	Y Poly Wt Delta/AO											
S413	Comb. Paper Wt SiC											
S422	Comb. Paper Wt SiC											
T402	A Wt Waterproof SiC											
CUT SHEETS												
A213	B Wt Light Paper AO											
A275	B Wt Light Paper AO											
A975	B Wt Light Paper SG (Cer)+ AO											
G131	E* Wt Heavy Paper AO											
H231	F Wt Heavy Paper AO											
H425	E Wt Heavy Paper SiC											
H835	E Wt Heavy Paper ZR/AO											
Q421	Grid Wt SiC											
R230	X Cotton Heavy Cloth AO											
R265	X Cotton Heavy Cloth AO											
R287	JJ Cotton Wt Light Cloth AO											

	320	280	240	220	180	150	120	100	80	60	50	40	36	30	24	20	16	PRODUCT CODE
																		R230
																		R270
																		R275
																		R287
																		R296
																		R309
																		R426
																		R427
																		R817
																		R823
																		R846
																		R847
																		R922
																		R926
																		R949
																		R984
																		RX84
																		S413
																		S422
																		T402
																		A213
																		A275
																		A975
																		G131
																		H231
																		H425
																		H835
																		Q421
																		R230
																		R265
																		R287

PRODUCT SELECTION

USAGE KEY

 Stock products

 Made-to-order

PRODUCT CODE	DESCRIPTION	3000	2500	2000	1500	1200	1000	800	600	500	400	360
CUT SHEETS (CONTINUED)												
R309	JJ Cotton Wt Light Cloth AO											
R426	JJ Cotton Wt Light Cloth SiC											
R427	X Cotton Heavy Cloth SiC											
R822	X Cotton Heavy Cloth Zir											
R922	X Cotton Heavy Cloth SG (Ceramic) + AO											
SHEETS												
A213	B Wt Light Paper AO											
A213	C Wt Light Paper AO											
A275	B Wt Light Paper AO											
A413	A Wt Light Paper SiC											
A621	C Wt Light Paper Emery**											
A721	B Wt Light Paper Flint											
K625	J Light Wt Light Cloth Emery**								Very Fine			
Q421	Grid Wt SiC											
Q222	NW: Non Woven Wt AO											
R222	J Wt Light Cloth AO											
T221	C Wt Waterproof SiC											
T402	A Wt Waterproof SiC**											
T417	B/C Wt Waterproof SiC											
T489	B Wt Waterproof SiC											
SLITTED ROLLS												
A213	B Wt Light Paper AO											
A213	C Wt Light Paper AO											
A277	E* Wt Heavy Paper AO											
A455	E* Wt Heavy Paper SiC											
A275	B Wt Light Paper AO											
A275 Rotolo®	B Wt Rotolo® AO											
A275 Norgrip®	B Wt AO											
A621	C Wt Light Paper Emery**											
BD25	D Wt Heavy Paper AO											
BD25 Norgrip®	D Wt AO											

**Special Grading

	320	280	240	220	180	150	120	100	80	60	50	40	36	30	24	20	16	PRODUCT CODE
																		R309
																		R426
																		R427
																		R822
																		R922
																		A213
																		A213
																		A275
																		A413
					4/0													A621
						3/0	2/0	0	1	2	3	4	5	6				A721
	Fine		Medium				Coarse			Very Coarse								K625
																		Q421
																		Q222
																		R222
																		T221
																		T402
																		T417
																		T489
																		A213
																		A213
																		A277
																		A455
																		A275
																		A275 Rotolo®
																		A275 Norgrip®
					4/0													A621
																		BD25
																		BD25 Norgrip®

PRODUCT SELECTION

USAGE KEY

 Stock products

 Made-to-order

PRODUCT CODE	DESCRIPTION	3000	2500	2000	1500	1200	1000	800	600	500	400	360
SLITTED ROLLS (CONTINUED)												
G131	E* Wt Heavy Paper AO											
G422	E Wt Heavy Paper SiC											
H822	E Wt Heavy Paper ZR											
H231	F Wt Heavy Paper AO											
H259	E Wt Heavy Paper AO											
H425	E Wt Heavy Paper SiC											
H835	E Wt Heavy Paper ZR/AO											
Q421	Grid Wt SiC											
Q13x	3mm Film Wt AO											
Q15x	5mm Film Wt AO											
Q222	Non woven Wt AO											
R202	J Cotton Wt AO											
R207	X Cotton Heavy Cloth AO											
R222	J Wt Light Cloth AO											
R230	X Cotton Heavy Cloth AO											
R265	X Cotton Heavy Cloth AO											
R270	X Poly Wt Aggreg. AO											
R275	X Poly Wt Aggreg. AO											
R287	J Cotton Wt Light Cloth AO											
R293	X/Y Polyester Wt AO/SG											
R296	JJ Cotton Wt Light Cloth SG/AO											
R309	JJ Cotton Wt Light Cloth AO											
R426	J Cotton Wt Light Cloth SiC											
R427	X Cotton Heavy Cloth SiC											
R445	X/Y Polyester Wt SiC											
R473	X Poly Wt Aggreg. SiC											
R484	YY Poly Wt SiC											
R817	Y Polyester Wt Zir											
R822	X Cotton Heavy Cloth Zir											
R823	Y Poly Wt ZR/AO											
R82A	X Cotton Heavy Cloth ZR/AO											
R880	X Poly Cotton Wt ZR/AO											

	320	280	240	220	180	150	120	100	80	60	50	40	36	30	24	20	16	PRODUCT CODE
																		G131
																		G422
																		H822
																		H231
																		H259
																		H425
																		H835
																		Q421
																		Q13x
																		Q15x
																		Q222
																		R202
																		R207
																		R222
																		R230
																		R265
																		R270
																		R275
																		R287
																		R296
																		R309
																		R426
																		R427
																		R445
																		R473
																		R484
																		R817
																		R822
																		R823
																		R82A
																		R880

PRODUCT SELECTION

USAGE KEY

 Stock products

 Made-to-order

PRODUCT CODE	DESCRIPTION	3000	2500	2000	1500	1200	1000	800	600	500	400	360	
SLITTED ROLLS (CONTINUED)													
R846	Y Poly Wt ZR/AO												
R847	Y Poly Wt Zir												
R853	YY Poly Wt ZR												
R922	X Cotton Wt Heavy Cloth SG/AO												
R926	X Cotton Wt Heavy Cloth SG/AO												
R949	X Poly Wt SG/A												
R966	Y Poly Wt SG/AO												
R980	Y Poly Wt SG												
R984	Y Poly Wt SG												
RX22	X Cotton Heavy Cloth SG												
RX66	Y Poly Wt Delta/AO												
RX84	Y Poly Wt Delta/AO												
S413	Comb. Paper Wt SiC												
S422	Comb. Paper Wt SiC												
S468	Comb. Paper Wt SiC												
S482	Comb. Paper Wt SiC												
W441	XCotton Wt Heavy Cloth SiC/Cork												
W445	X Poly Wt Cork	No Grit											
BELTS													
A455	E* Wt Heavy Paper SiC												
A277	E* Wt Heavy Paper AO												
G422	E Wt Heavy Paper SiC												
H231	F Wt Heavy Paper AO												
H259	E Wt Heavy Paper AO												
R293	X/Y Poly Wt AO/SG												
R230	X Cotton Heavy Cloth AO												
R265	X Cotton Heavy Cloth AO												
R270	X Poly Wt Aggreg. AO												
R275	X Poly Wt Aggreg. AO												
R287	J Cotton Wt Light Cloth AO												
R293	X/Y Poly Wt AO/SG												
R296	JJ Cotton Wt Light Cloth SG/AO												

	320	280	240	220	180	150	120	100	80	60	50	40	36	30	24	20	16	PRODUCT CODE
																		R846
																		R847
																		R853
																		R922
																		R926
																		R949
																		R966
																		R980
																		R984
																		RX22
																		RX66
																		RX84
																		S413
																		S422
																		S468
																		S482
																		W441
																		W445
																		No Grit
																		A455
																		A277
																		G422
																		H231
																		H259
																		R293
																		R230
																		R265
																		R270
																		R275
																		R287
																		R293
																		R296

PRODUCT SELECTION

USAGE KEY

 Stock products

 Made-to-order

PRODUCT CODE	DESCRIPTION	3000	2500	2000	1500	1200	1000	800	600	500	400	360
BELTS (CONTINUED)												
R309	JJ Cotton Wt Light Cloth AO											
R426	J Cotton Wt Light Cloth SiC											
R427	X Cotton Heavy Cloth SiC											
R445	X/Y Poly Wt SiC											
R473	X Poly Wt Aggreg. SiC											
R484	YY Poly Wt SiC											
R817	Y Polyester Wt Zir											
R822	X Cotton Heavy Cloth Zir											
R823	Y Poly Wt ZR/AO											
R82A	X Cotton Heavy Cloth ZR/AO											
R846	Y Poly Wt ZR/AO											
R847	Y Poly Wt Zir											
R853	YY Poly Wt ZR											
R921	Y Poly Wt SG											
R922	X Cotton Wt Heavy Cloth SG/AO											
R926	X Cotton Wt Heavy Cloth SG/AO											
R929	Poly Wt AO/SG											
R949	X Poly Wt SG/AO											
R966	Y Poly Wt SG/AO											
R980	Y Poly Wt SG											
R981	Y Poly Wt SG/AO											
R984	Y Poly Wt SG											
RX22	X Cotton Heavy Cloth SG											
RX66	Y Poly Wt Delta/AO											
RX84	Y Poly Wt Delta/AO											
S413	Comb. Paper Wt SiC											
S422	Comb. Paper Wt SiC											
S468	Heavy Comb. Wt SiC											
S482	Paper Comb. Wt SiC											
S853	Heavy Comb. Wt ZR											
W441	X Cotton Wt SiC/Cork											
W445	X Poly Wt Cork											

No Grit

320	280	240	220	180	150	120	100	80	60	50	40	36	30	24	20	16	PRODUCT CODE
																	R309
																	R426
																	R427
																	R445
																	R473
																	R484
																	R817
																	R822
																	R823
																	R82A
																	R846
																	R847
																	R853
																	R921
																	R922
																	R926
																	R929
																	R949
																	R966
																	R980
																	R981
																	R984
																	RX22
																	RX66
																	RX84
																	S413
																	S422
																	S468
																	S482
																	S853
																	W441
																	W445

No Grit

PRODUCT SELECTION

USAGE KEY	X3	X4	X5	X10	X15	X16	X20	X22	X30	X35	
											
PRODUCT CODE	I	I	3000	1500	1200	1200	1000	800	500	400	
NORAX BELTS, SHEETS & DISCS											
U142											
U152											
U162											
U234											
U242											
U243											
U254											
U264											
U336											
U366											
U434											
U442											
U454											
U464											
U466											
NORAX SHEETS & DISCS ONLY											
U321											
U331											
U381											


	X40	X45	X65	X70	X80	X90	X100	X110	X200	X210	
	360	320	220	220	180	180	150	150	80	80	PRODUCT CODE
											U142
											U152
											U162
											U234
											U242
											U243
											U254
											U264
											U336
											U366
											U434
											U442
											U454
											U464
											U466
											U321
											U331
											U381

From rapid weld grinding to blending and finishing, Norton has a complete range of high performance fibre discs available in premium performance Norton SG® ceramic aluminium oxide, zirconia alumina, and aluminium oxide abrasives. All fibre discs in the Norton range feature a full resin bond system with heavy duty fibre backing for increased strength, durability and tear resistance.

APPLICATIONS & MARKETS

- Material removal
- Weld grinding & blending
- Light deburring & finishing
- Car manufacturing
- Metal fabrication
- Welding & foundry markets
- Transport markets



BEST	F971 GREENLYTE PLUS		
	FERR. & NON-FERR. 		
	FEATURES	BENEFITS	
	■ SG® ceramic abrasive ■ 0.8mm high strength fibre backing ■ Third layer Supersize with active filler	■ Fastest cut rate & long product life ■ Ideal for blending, edge breaking & weld removal ■ Excellent for use in ship building ■ Resistant to high pressure ■ Resists loading & has low heat generation ■ Ideal for grinding stainless steel & other sensitive metals	
F975 GREENLYTE			
FERR. & NON-FERR. 			
FEATURES		BENEFITS	
■ SG® ceramic abrasive ■ 0.8mm high strength fibre backing		■ Fastest cut rate ■ Suitable for metal grinding, shaping, blending, edge breaking & weld removal ■ Resistant to high pressure ■ Cool cut	

F861 NORZON® PLUS**NORZON
PLUS**FERR.
& NON-
FERR.**FEATURES**

- NorZon® abrasive
- 0.8mm fibre backing
- Third layer Supersize with active filler

BENEFITS

- Excellent cut rate
- Ideal for metal grinding, shaping, blending & weld removal
- Cool cut
- Ideal for heavy construction work & stainless steel grinding
- Resistant to loading
- Ideal for sensitive metal grinding

**F827 NORZON®****NORZON**FERR.
& NON-
FERR.**FEATURES**

- NorZon® abrasive
- 0.8mm fibre backing

BENEFITS

- General purpose
- Ideal for grinding, shaping, blending, edge breaking & weld
- High & regular cut rate
- Good for high metal removal in short time
- Excellent price-performance ratio

**F425**NON-
FERR.

STONE

**FEATURES**

- High performance silicon carbide abrasive
- 0.8mm fibre backing

BENEFITS


- Very good cut rate with low pressure
- Self-sharpening
- Recommended for use on angle grinders

**F293**FERR.
& NON-
FERR.**FEATURES**

- High performance aluminium oxide abrasive
- 0.8mm fibre backing

BENEFITS

- General purpose
- General metal grinding, shaping & polishing
- Good cut rate
- Weld removal



BETTER

GOOD

GOOD

F228

FERR.
& NON-
FERR.





FEATURES	BENEFITS
■ Tough versatile aluminium oxide abrasive	■ Fast initial cut
■ 0.8mm fibre backing	■ Ideal for general purpose metal applications

MAXIMUM OPERATING SPEED

DIA (mm)	MOS (m/s)	MAX RPM
100	80	5300
115	80	13300
125	80	12300
150	80	10200
180	80	8600

■ The maximum peripheral operating speed of a fibre disc is 80m/s. This is communicated on the box label by way of a red stripe, which is a FEPA standard

STANDARD

					<i>NORZON PLUS</i>	<i>NORZON</i>			
DIM DIAxH (mm)	GRIT	PK QTY	BEST		BETTER			GOOD	
			F971	F975	F861	F827	F425	F293	F228
100x16 	36	25		63642368921					
	60	25		63642368923					
115x22 	24	25				69957360048	63642545163	63642547861	07660707354
	36	25	63642568805	63642568819	69957395190	63642539615	63642537161	63642535056	07660707355
	50	25	63642568806	63642568820	69957395191	69957360053		07660705216	07660707356
	60	25	63642568807	63642568821	69957395192	63642539616	63642537239	63642536900	07660707357
	80	25	63642568808	63642568822	69957395193	63642539617	63642548543	07660705214	07660707358
	100	25						07660705213	07660707359
	120	25			69957395194	63642533055	63642512988	07660705212	07660707360
	220	25					63642512989		
125x22 	24	25				63642539619	63642508423	63642547907	07660707366
	36	25	63642568809	63642568823	69957395195	63642536483	63642546187	63642547906	07660707361
	50	25	63642568810	63642568824	69957395196	63642539620		63642547905	07660707362
	60	25	63642568811	63642568825	69957395198	69957360057	63642551570	63642547904	07660707363
	80	25	63642568812	63642568826	69957395199	63642539622	63642507453	63642547903	07660707364
	100	25				63642536484		63642547902	66261153113
	120	25			69957395200	63642533056	63642507454	63642547901	07660707365
	220	25					63642547695		
150x22 	24	25					63642552311		
	36	25					63642536911		
	60	25					63642507448		
	120	25					63642507451		
	220	25					69957351128		

Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole

STANDARD (CONTINUED)

DIM DIAxH(mm)	GRIT	PK QTY	GREEN-ALYTE PLUS		NORZON PLUS	NORZON			
			BEST		BETTER			GOOD	
			F971	F975	F861	F827	F425	F293	F228
180x22 	24	25				63642533062	63642534249	63642533108	07660707367
	36	25	63642568813	63642568827	69957395201	63642533063	69957360039	63642533107	07660707368
	50	25	63642568814	63642568828	69957395202	63642533064		63642535057	07660707369
	60	25	63642568815	63642568830	69957395204	63642533065	69957360040	63642533105	07660707370
	80	25	63642568816	63642568831	69957395206	63642533066	69957360041	63642533104	07660707371
	100	25				63642533067		63642533103	07660707372
	120	25			69957395207	63642533068	63642536718	63642533102	07660707373
	220	25					69957360044		

MOULDED

DIM DIAxH (mm)	GRIT	PK QTY	GREEN-ALYTE PLUS		NORZON PLUS
			BEST		BETTER
			F971	F975	F861
180x22 	36	100	63642568836	63642568832	69957395209
	50	100	63642568837	63642568833	69957395210
	60	100	63642568838	63642568834	69957395212
	80	100	63642568839	63642568835	69957395213
	120	100			69957395214

BACK-UP PADS

AIRCOOL					NYLON				
DIA (mm)	DENSITY	ATTACHMENT	PK QTY		DIA (mm)	DENSITY	ATTACHMENT	PK QTY	
100	Hard	M14	1	69957389886	100	HARD	M10	5	63642535414
115	Hard	M14	1	69957382821		MEDIUM	M10	5	63642535412
	Medium	M14	1	69957389797	115	HARD	M14	5	69957382828
125	Hard	M14	1	69957382823		MEDIUM	M14	5	69957382825
	Medium	5/8	1	63642588240	125	HARD	M14	5	69957382829
	Medium	M14	1	69957389803		MEDIUM	5/8	5	63642588341
178	X Hard	M14	1	63642596383	178	MEDIUM	M14	5	69957382826
	Hard	M14	1	69957382824		HARD	M14	5	69957382830
	Medium	5/8	1	63642588243	178	MEDIUM	5/8	5	63642588345
	Medium	M14	1	69957389804		MEDIUM	M14	5	69957382827

All Norton fibre disc back-up pads comply with ISO 15636 which is the International Worldwide standard for angle grinder pads



SEMI-FLEXIBLE DISCS

Semi-flexible discs are made by coating heavy duty fibre with multiple layers of a special resin bonded abrasive. They can be used in a wide range of applications instead of depressed centre grinding wheels.

APPLICATIONS & MARKETS

- Grinding welds
- Derusting large surfaces
- Cleaning hulls of ships & boats
- Cleaning cows' hooves



BEST	Q200		
	FERR. 		
	FEATURES	BENEFITS	
	■ High concentration of aluminium oxide abrasive ■ Unique disc pattern	■ For use on stainless steel, aluminium & most other metals ■ Resists loading ■ Cooler work area	
	Q400		
	STONE 		
	FEATURES	BENEFITS	
	■ High concentration of sharp silicon carbide abrasive ■ Unique disc pattern	■ For use on marble , granite, concrete, fibreglass & cast iron ■ Suitable for heavy duty industrial applications ■ Longer lasting ■ Resists loading ■ Cooler work area	

Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole

BETTER

CP FLEX

STONE



FEATURES

- Sharp silicon carbide abrasive grain

- Unique disc pattern

BENEFITS

- For use on marble, granite, concrete, fibreglass & cast iron
- Ideal for use in construction markets
- Longer lasting
- Resists loading
- Cooler work area



SPEC CHECK

- Semi-flexible discs should be used on an angle grinder with a hard density back-up pad which has the same diameter as the disc. All semi-flexible discs have a maximum operating speed of 80m/s

CPA DISCS ALUMINIUM OXIDE

			Q200
			BEST
			CONVEX
DIM DIAxH(mm)	GRIT	PK QTY	
127x22 	24	25	07660717653
	36	25	07660717654
	60	25	07660717655
	80	25	07660717656
180x22 	24	25	07660717647
	36	25	07660717648
	60	25	07660717650
	80	25	07660717651

CPS DISCS SILICON CARBIDE

			Q400	CP FLEX
			BEST	BETTER
DIM DIAxH (mm)	GRIT	PK QTY	MOULDED/CONVEX	FLAT
127x22 	16	25		07660707935
	24	25	07660705207	07660707937
	36	25	07660707946	07660707454
	60	25	07660718494	
	80	25	07660707948	
180x22 	16	25	07660705202	07660717646
	24	25	07660705203	07660707931
	36	25	07660705204	07660707933
	60	25	07660705205	07660707934
	80	25	07660705206	
	120	25	07660707943	

BACK-UP PADS

DIA (mm)	DENSITY	ATTACHMENT	PK QTY	NYLON
125	Hard	M14	5	69957382829
180	Hard	M14	5	69957382830

All Norton semi-flexible disc back-up pads comply with ISO 15636 which is the International Worldwide standard for angle grinder pads

Norton flap discs are engineered for multiple applications including light stock removal, blending and finishing, meaning they can help reduce processing times and lower costs. Flap discs have a fast cut and provide a better finish than fibre while having the added benefit of a longer life.

APPLICATIONS & MARKETS

- Stock removal
- Edge chamfering
- Deburring
- Rust/paint removal
- Cleaning & finishing
- Grinding & blending welds



INNOVATION

BEST

R980 X-TREME LIFE BLAZE

FERR.
& NON-
FERR.



SG
BLAZE



FEATURES

- Next generation SG® ceramic abrasive grain
- Heavy polyester cloth
- Improved third layer Supersize coat that gives unique orange colour
- Fibreglass backing

BENEFITS

- Ideal for stainless steel, inconels, chromium cobalt, titanium or other hard-to-grind material
- Xtrem long life
- Promotes a cool & fast cut which gives higher metal removal rates & longer product life



R880 JUMBO

FERR.
& NON-
FERR.



FEATURES

- High performance zirconia alumina abrasive grain
- Heavy backing with improved resistance to wear
- High density disc with extra-long flaps
- Fibreglass backing

BENEFITS

- Highly efficient on stainless & carbon steel
- Best for heavy duty applications
- Up to 30% longer life



SHAPE KEY



Flat



Conical

RX22/R822 TWINSTARFERR.
& NON-
FERR.**FEATURES**

- Premium SG® ceramic aluminium oxide & Norzon® zirconia alumina abrasive blend
- Heavy cotton cloth
- High density disc with extra-large flaps
- Reinforced plastic backing

BENEFITS

- Aggressive stock removal with less pressure, giving a cooler cut
- Achieves a much longer life due to the high density of flaps

**R880 BLUE STAR**FERR.
& NON-
FERR.**FEATURES**

- High performance NorZon® zirconia alumina abrasive grain
- Heavy cloth with improved resistance to wear
- Available with fibreglass or plastic backings

BENEFITS

- Ideal for heavy duty applications

**RX22/R822 NORSTAR**FERR.
& NON-
FERR.**FEATURES**

- Premium SG® ceramic aluminium oxide & NorZon® zirconia alumina abrasive blend
- Heavy cotton cloth
- High content of active filler
- Fiberglass backing

BENEFITS

- Aggressive stock removal with less pressure



R822 NORFIBERFERR.
& NON-
FERR.**FEATURES**

- High performance NorZon® zirconia alumina abrasive grain
- Heavy cotton cloth
- Fibreglass backing

BENEFITS

- Good stock removal

**R822 NORTECH**

FERR.

**FEATURES**

- NorZon® zirconia alumina abrasive grain
- Heavy cotton cloth
- Double flap disc construction
- Plastic backing

BENEFITS

- Aggressive cut

**R822 BDX**

FERR.

**BDX****FEATURES**

- High performance NorZon® zirconia alumina abrasive grain
- Heavy cotton cloth
- Fibreglass backing

BENEFITS

- Good stock removal

**R82A NORTECH 2**


FERR.

**FEATURES**

- Norzon® zirconia alumina & aluminum oxide abrasive blend
- Heavy cotton cloth
- Double flap disc construction
- Plastic backing

BENEFITS

- Aggressive cut

**R265 NORTECH**

FERR.

**FEATURES**

- Durable aluminum oxide abrasive grain
- Heavy cotton cloth
- Double flap disc construction
- Plastic backing

BENEFITS

- Fast initial cut rate especially on carbon steel



GOOD

FIBREGLASS BACKED

			<i>SG BLAZE</i>	<i>JUMBO</i>	<i>BLUE STAR</i>	<i>NORSTAR</i>	<i>NORFIBER</i>	<i>BDX</i>
DIM DIAxH(mm)	GRIT	PK QTY	INNOVATION			BETTER	GOOD	
			BEST		BETTER			
			R980	R880	R880	RX22/R822	R822	R822
 Conical								
115x22	36	10			699573 51380	636425 34666		
	40	10	699573 92030	699573 51401	699573 51385	636425 34667	636425 53075	
	40	200*						636425 15039
	60	10	699573 92028	699573 51402	699573 51386	636425 34668	636425 53076	
	60	200*						636425 15040
	80	10	699573 94106	699573 51403	699573 51387	636425 34669	636425 53077	
	80	200*						636425 49442
	120	10			699573 51388	636425 34670	699573 87295	
	120	200*						636425 15041
125x22	36	10			699573 51391	636425 14934		
	40	10	699573 92031	699573 51404	699573 51392	636425 63571	636425 53079	
	40	160*						636425 50311
	60	10	699573 92097	699573 51405	699573 51393	636425 68611	636425 53080	
	60	160*						636425 50312
	80	10	699573 94108	699573 51406	699573 51394	636425 49404	636425 53081	
	80	160*						636425 15042
	120	10			699573 51395	636425 50474	699573 87300	
	120	160*						636425 15043
180x22	36	10			699573 51396	636425 34671		
	40	10		699573 51407	699573 51397	699573 36664	699573 87302	
	40	60*						662611 79318
	60	10		699573 51408	699573 51398	636425 49405	699573 87303	
	60	60*						662611 79319
	80	10		699573 51409	699573 51399	636425 49406	699573 87304	
	80	60*						662611 79320
	120	10			699573 51400	699573 53208	636425 94667	
	120	60*						699573 53178

*Also available shrink-wrapped in 10

SPEC CHECK

- Conical flap discs are designed to be used at an angle of 15-25°
- For an equivalent finish, always use a flap disc one grit size coarser than with a fibre disc

SHAPE KEY



Flat



Conical

Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole

FIBREGLASS BACKED

			<i>SG BLAZE</i>	<i>JUMBO</i>	<i>BLUE STAR</i>	<i>NORSTAR</i>	<i>NORFIBER</i>	<i>BDX</i>
DIM DIAxH(mm)	GRIT	PK QTY	INNOVATION			BETTER	GOOD	
			BEST		BETTER			
			R980	R880	R880	RX22/R822	R822	R822
 Flat								
115x22	40	200*						636425 27334
	60	200*						636425 27336
	80	200*						636425 27337
	120	200*						699573 53557
125x22	40	10			699573 51424			
	40	160*						636425 27341
	60	10			699573 51425			
	60	160*						636425 27343
	80	10			699573 51426			
	80	160*						636425 27347
	120	10			699573 51427			
	120	160*						699573 53180
180x22	40	60*						699573 53181
	60	60*						699573 53182
	80	60*						699573 53183
	120	60*						699573 53184

* Also available shrink-wrapped in 10

MAXIMUM OPERATING SPEED

DIA (mm)	MOS (m/s)	MAX RPM
115x22	80	13300
125x22	80	12200
180x22	80	8500



Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole

PLASTIC BACKED

			<i>TWINSTAR</i>	<i>BLUE STAR</i>	<i>NORTECH</i>	<i>NORTECH 2</i>	<i>NORTECH</i>
DIM DIAxH(mm)	GRIT	PK QTY	BEST	INNOVATION	GOOD		
			RX22/R822	R880	R822	R82A	R265
			Flat				
115x22	40	10	636425 45568	699573 51411			
	40	200*			662610 39431	636425 53609	662610 39427
	60	10	636425 45570	699573 51412			
	60	200*			662610 39449	636425 53610	662610 39445
	80	10	636425 45571	699573 51413			
	80	200*			662610 39457	636425 53611	662610 39453
	120	10	636425 45573	699573 51414			
	120	200*			662610 39469	636425 53612	662610 39467
125x22	40	10		699573 51416			
	40	160*			636425 88032		
	60	10		699573 51417			
	60	160*			636425 88033		
	80	10		699573 51418			
	80	160*			636425 88031		
	120	10		699573 51419			
	120	160*			699573 53205		
180x22	40	10	636425 45575	699573 51420			
	40	60*			662610 39476	636425 53613	662610 39474
	60	10	636425 45576	699573 51421			
	60	60*			636425 14335	636425 53614	662610 39481
	80	10	636425 45577	699573 51422			
	80	60*			636425 14336	636425 53615	662610 39485
	120	10	636425 82372	699573 51423			
	120	60*			699573 53207	636425 53616	699573 53888

* Also available shrink-wrapped in 10

SPEC CHECK

- For an equivalent finish, always use a flap disc one grit size coarser than with a fibre disc
- Flat flap discs are designed to be used at an angle less than 15°

Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole

MULTI-AIR®

NON
FERR.PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD

MULTI-AIR



FEATURES

- New premium, heat-treated aluminium oxide abrasive

- New unique fibre-reinforced latex paper

- Water based No-Fil®

- No pigment in No-Fil® or bond

- Available in grits P80-800

BENEFITS

- Faster cut rate

- Flexible & tear resistant

- Improved load resistance

- No risk of colour transfer

MULTI-AIR® SOFT-TOUCH®

NON
FERR.PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD

MULTI-AIR



FEATURES

- New premium, heat treated aluminium oxide abrasive

- New unique fibre-reinforced latex paper

- Water based No-Fil®

- No pigment in No-Fil® or bond system

- Flexible foam backing with coloured Norgrip®

- Multi-Air® hole configuration

- Colour coded discs

- Available in grits P320-1500

BENEFITS

- Faster cut rate

- Improved performance

- Flexible & tear resistant

- Improved load resistance

- No risk of colour transfer



- Allows contour sanding without cutting through coating layer

- Maximum dust extraction for a clean work surface & longer life

- For easy recognition of grit size

- Also available in Multi-Air® Plus

ADVANTAGES OF MULTI-AIR PROCESS®




NORTON MULTI-AIR PROCESS®

Universal backing pad fixings to suit most popular machine types

Dust extraction panels

Alignment holes allow accurate location to the backing pad




Adapters to suit Festo sanding machines

Choice of hard, medium or soft backing pads

Waterbased No-Fil® resists clogging during use

Premium aluminium oxide

Dust Extraction System



EXTRACTION HOLES

- 181 holes maximise dust removal for 150mm
- 125 holes maximise dust removal for 125mm

The overall abrasive area is similar to that of conventional discs with traditional 6, 7 or 9 holes dust extraction



FEATURES	BENEFITS
Revolutionary design for maximum vacuum assistance	30% increase in dust extraction; clogging is virtually eliminated
Cutting surface of disc remains clean	Cleaner working environment; less dust & contamination
Highly-engineered back-up pad	35% increase in productivity versus traditional vacuum systems
	No clogging; consistent cut throughout the life of the disc
	Patented design for maximum dust extraction

MULTI-AIR® PLUS KIT



GRIT	TYPE	PK QTY	BEST	
80	Multi-Air® Plus	5	69957395370	
120	Multi-Air® Plus	5		
240	Multi-Air® Plus	5		
320	Multi-Air® Plus	5		
	Multi-Air® Plus Soft-Touch®	3		
400	Multi-Air® Plus	5		
	Multi-Air® Plus Soft-Touch®	3		
	Medium Multi-Air® Back-up Pad	1		

MULTI-AIR®



DIM DIAxH(mm)	GRIT	PK QTY	MULTI-AIR PLUS	MULTI-AIR NORZON	MULTI-AIR
			BEST		BETTER
125x18 	80	100	63642563535		63642563513
	120	100	63642563536		63642563514
	150	100	63642563537		63642563515
	180	100	63642563538		63642563516
	220	100	63642563539		63642563517
	240	100	63642563540		63642563518
	280	100	63642563541		63642563519
	320	100	63642563542		63642563520
	360	100			63642563521
	400	100	63642563543		63642563522
	500	100			63642563523
	600	100			63642563524
	800	100			63642563525
150x18 	80	50		66261181412	
	80	100	63642565916		63642560561
	120	100	63642523429		63642560562
	150	100	63642523430		63642560563
	180	100	63642565920		63642560564
	220	100	63642523434		63642560565
	240	100	63642523435		63642560566
	280	100	63642523436		63642560567
	320	100	63642523437		63642560568
	360	100			63642560569
	400	100	63642565925		63642560570
	500	100			63642560571
	600	100			63642560572
	800	100			63642560573

MULTI-AIR® KIT



GRIT	TYPE	PK QTY	BETTER	
80	Medium Multi-Air® NorZon®	5	63642587576	
120	Multi-Air®	5		
240	Multi-Air®	5		
320	Multi-Air®	5		
400	Multi-Air®	5		
	Multi-Air® Soft-Touch®	3		
500	Multi-Air® Soft-Touch®	3		
800	Multi-Air® Soft-Touch®	3		
	Medium Multi-Air® Back-up Pad	1		

Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole


SOFT-TOUCH® MULTI-AIR®					
DIM DIAxH(mm)	GRIT	COLOUR	PK QTY	MULTI-AIR PLUS	MULTI-AIR
				BEST	BETTER
125x18 	320	Salmon	20	63642563544	63642563526
	400	Yellow	20	63642563545	63642563527
	500	Dark Blue	20		63642563528
	600	Fuchsia	20		63642563529
	800	Turquoise	20		63642563530
	1000	White	20		63642563531
	1500	Green	20		63642563532
150x18 	320	Salmon	20	63642586352	63642560574
	400	Yellow	20	63642586353	63642560575
	500	Dark Blue	20		63642560576
	800	Turquoise	20		63642560577
	1000	White	20		63642560578
	1500	Green	20		63642560579

PRODUCT SELECTION

APPLICATION	GRIT	COLOUR
SOFT-TOUCH DISCS®		
Sanding cataphoretic coats & primer	320	Salmon
Sanding polyurethane primer	400	Yellow
	500	Dark Blue
	600	Fuchsia
Cutting back lacquer before a flush joint	800	Turquoise
Retouching clear coat	1000	White
Before polishing & buffing	1500	Green

SPEC CHECK

- Multi-Air® Soft-Touch® discs are made with a specific soft foam backing with high performance & exceptional long life, directly attached to the abrasive paper
- The foam layer absorbs easily any difference in surface, maintaining an excellent cutting action with a very homogenous, high level finish



Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole

BACK-UP PADS MULTI-AIR PROCESS®

DIM (mm)	DENSITY	ATTACHMENT	PK QTY	
125	Medium	5/16 & M8	1	636425 63533
	Soft	5/16 & M8	1	636425 63534
150	Hard	5/16 & M8	1	076607 19198
	Medium HT	5/16 & M8	1	636425 85872
	Medium	5/16 & M8	1	636425 60580
	Soft	5/16 & M8	1	636425 60605
	Rupes Adapter	M5	1	636425 26648

All Multi-Air Process® back-up pads are packed in individual boxes with Festo adapter M8 & 5/16 bolts & three fibre ring spaces

FOAM INTERFACE PADS MULTI-AIR PROCESS®

DIM (mm)	PK QTY	
125	16	636425 85864
150	12	076607 19359

PRODUCT SELECTION

APPLICATION	DENSITY
BACK-UP PADS	
Heavy duty sanding, best for flattening surfaces or dimensioning	Hard
Scuffing, shaping, sanding & finishing	Medium
For use on filler, primer, paint, clear coat, wood, plaster, composites & metal	
Final sanding, to obtain the best finishes	Soft



Norgrip® and Soft-Touch® discs have a quick release backing that allows quick and easy disc changing, increasing performance by minimising downtime. Soft-Touch® discs also include a foam backing that improves product performance and gives an even longer product life. The foam layer absorbs unevenness in the surface, helping to maintain an excellent cutting action providing a very homogenous, high quality finish.



APPLICATIONS & MARKETS	
■ Preparing primed & painted surfaces	■ Light weld blending & deburring
■ Stripping primer & paint	■ Sanding bare wood
■ Sanding plastic & fibreglass	

BEST

A975 NORTON PRO PLUS

NON FERR.

PAINT/ VARN. & HARD WOOD

FEATURES	BENEFITS
■ New Norton SG® ceramic abrasive blended with premium heat-treated aluminium oxide abrasive	■ Higher & faster cut rate
■ New unique blue fibre-reinforced latex paper	■ Ideal for large surfaces
■ Water based No-Fil®	■ Consistent & uniform scratch pattern
■ No pigment in No-Fil® or bond	■ Combines flexibility with tear resistance
■ Improved performance	■ Resists clogging during use
■ Ideal for large surface areas	■ No risk of colour transfer
■ Available in grits P80-400	■ Extended life
	■ Less downtime

H231

FERR.
& NON
FERR.HARD
WOOD

FEATURES

- High performance aluminium oxide abrasive

- Semi-open / open coat (depending on grit size)

- Very strong, F-weight paper

- Anti-static properties

BENEFITS

- Ideal for roughing, intermediate sanding & finishing of solid wood
- Ideal for floor & furniture applications
- Finer grits ideal for polishing metal, plastics & leathers, smoothing fillers, sanding primers, within vehicle repair markets


- Resists clogging

- High performance

- Excellent surface quality



H835 BLUE FIRE®

FERR.
& NON
FERR.PAINT/
VARN.
& HARD
WOOD

FEATURES

- Latest NorZon® grain design

- High strength paper backing (E-weight)

- Open grain distribution

- Full resin bond system

- Available in grits 40-120


BENEFITS

- Self-sharpening grain
- Improved cut rate
- Extended product life

- Reduces curling & edge chipping
- Tear resistant

- Prevents premature clogging

- Strong grain adhesion



BEST

BETTER

PAINT/
WARN.
HARD
WOOD
& SOFT
WOOD

BENEFITS

- | | |
|---|--|
| <ul style="list-style-type: none"> ■ New premium, heat-treated high performance aluminium oxide abrasive | <ul style="list-style-type: none"> ■ Faster cut rate ■ Improved performance ■ More consistent uniform scratch pattern |
| <ul style="list-style-type: none"> ■ New unique fibre-reinforced latex paper | <ul style="list-style-type: none"> ■ Flexible & tear resistant |
| <ul style="list-style-type: none"> ■ Water based No-Fil® | <ul style="list-style-type: none"> ■ Improved load resistance |
| <ul style="list-style-type: none"> ■ No pigment in No-Fil® or bond | <ul style="list-style-type: none"> ■ No risk of colour transfer |
| <ul style="list-style-type: none"> ■ Available in Soft-Touch® discs with flexible foam backing & coloured Norgrip® | <ul style="list-style-type: none"> ■ Allows contour sanding without cutting through coating layer & easy grit identification |
| <ul style="list-style-type: none"> ■ Available in Norgrip® grits P80-1500 & Soft-Touch® Norgrip® grits 200-1500 | |



NORGRIP® DISCS



			NORTON PRO PLUS		BLUE FIRE 	NORTON PRO
DIM DIAxH(mm)	GRIT	PK QTY	BEST		BETTER	
			A975	H231	H835	A275
 76	240	50				636425 69718
	320	50				636425 69731
	400	50				636425 69719
	500	50				636425 69720
	600	50				636425 69721
	800	50				636425 69723
 76	80	50				636425 85133
	120	50				636425 85145
	150	50				636425 85148
	180	50				636425 85150
	220	50				636425 85153
	240	50				636425 85156
	280	50				636425 85161
	320	50				636425 69699
	360	50				636425 85165
	400	50				636425 85169
	500	50				699573 89051
	600	50				699573 89052
	800	50				636425 85172

Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole

Coated Abrasives

NORTON

NORGRIP® DISCS (CONTINUED)



			NORTON PRO PLUS		BLUE FIRE	NORTON PRO
DIM DIAxH(mm)	GRIT	PK QTY	BEST		BETTER	
			A975	H231	H835	A275
125 	36	100		662611 76734		
	40	25			699573 50908	
	60	25		636425 16174	699573 50915	
	80	50		636425 16175	699573 50916	
	120	50		636425 16176	699573 50919	
	180	100		636425 37389		
	240	100		699573 60184		
	320	100		636425 37390		
125x8 	80	100				699573 51501
	100	100				699573 51503
	120	100				699573 51506
	150	100				699573 51508
	180	100				699573 51509
	240	100				699573 51510
	320	100				699573 51882
	400	100				636425 91163
150 	600	100				699573 51511
	36	100		636425 51458		
	40	25		636425 31875	699573 90933	
	50	100		699573 60119		
	60	25		636425 19158	699573 90940	
	80	50		636425 46787	699573 91248	636425 85184
	100	100		636425 31872		636425 85186
	120	50		636425 31871	699573 91249	636425 69701
	150	100		699573 60170		636425 69702
	180	100		636425 36755		636425 85190
	220	100				636425 85194
	240	100		636425 46797		636425 85197
	280	100				636425 85199
	320	100		636425 36677		636425 69704
	360	100				636425 85205
	400	100				636425 85214
	500	100				636425 85217
	600	100				636425 85220
	800	100				636425 85223

NORGRIP® DISCS (CONTINUED)						
			NORTON PRO PLUS		BLUE FIRE	NORTON PRO
DIM DIAxH(mm)	GRIT	PK QTY	BEST		BETTER	
			A975	H231	H835	A275
150x14	36	100		69957351529		
	40	25		66261026066	69957391250	
	60	25		69957382764	69957391255	
	80	50	63642527655	66261026069	69957391256	63642557950
	100	100		66261026070		63642586135
	120	50	63642527659	66261026071	69957391257	63642557954
	150	100	63642527657	66261026072		63642586141
	180	100	63642527661	69957351530		63642586142
	220	100	63642527662			63642586143
	240	100	63642527666	69957351531		63642557955
	280	100	63642527667			63642586144
	320	100	63642527669	69957351532		63642557959
	360	100				63642586148
	400	100	63642527670			63642557962
	500	100				63642586150
	600	100				63642557964
	800	100				63642584990
150x18	40	25		63642550341	69957391258	
	60	25		63642536740	69957391260	
	80	50	63642527612	63642536741	69957391261	63642557968
	100	100		63642568763		63642585059
	120	50	63642565918	63642546779	69957391262	63642557969
	150	100	63642565919	63642546781		63642557970
	180	100	63642527633	63642546834		63642585064
	220	100	63642565921			63642585065
	240	100	63642565922	63642568766		63642585067
	280	100	63642565923			63642585069
	320	100	63642565924			63642557973
	360	100				63642585078
	400	100	63642527647			63642557974
	500	100				63642557975
	600	100				63642585073
	800	100				63642585074

Dimensions Key: DIM = Diameter, DIA = Diameter, H = Hole

NORGRIP® DISCS (CONTINUED)



DIA (mm)	GRIT	PK QTY	NORTON PRO PLUS		BLUE FIRE	NORTON PRO
			BEST		BETTER	
			A975	H231	H835	A275
203 	40	25			69957391263	
	60	25			69957391268	
	80	50			69957391269	63642585236
	100	100				63642585242
	120	50			69957391272	63642585243
	150	100				63642585244
	180	100				63642585245
	220	100				63642585246
	240	100				63642585248
	280	100				63642585249
	320	100				63642585250
	360	100				63642585251
	400	100				63642585252



SOFT-TOUCH® DISCS				NORTON PRO	
DIM DIAxH(mm)	GRIT	COLOUR	PK QTY	BETTER	
				A275	
150x14 	220	Red	20	63642557535	
	240	Electric Blue	20	63642557538	
	280	Grey	20	63642557541	
	320	Salmon	20	63642557543	
	360	Pink	20	63642557545	
	400	Yellow	20	63642557546	
	500	Dark Blue	20	63642557548	
	600	Fuchsia	20	63642557550	
	800	Turquoise	20	63642557551	
	1000	White	20	63642557556	
	1500	Green	20	63642557559	
150x18 	220	Red	20	63642557561	
	240	Electric Blue	20	63642557563	
	280	Grey	20	63642557564	
	320	Salmon	20	63642557565	
	360	Pink	20	63642557567	
	400	Yellow	20	63642557569	
	500	Dark Blue	20	63642557570	
	600	Fuchsia	20	63642557572	
	800	Turquoise	20	63642557571	
	1000	White	20	63642557573	
	1500	Green	20	63642557574	

SPEC CHECK

- Norton Pro Soft-Touch® discs are made with a specific soft foam backing with high performance & exceptional long life, directly attached to the abrasive paper
- The foam layer absorbs easily any difference in surface, maintaining an excellent cutting action with a very homogenous, high quality finish



Dimensions Key: DIA = Diameter, H = Hole

PRODUCT SELECTION

APPLICATION	GRIT	COLOUR
SOFT-TOUCH DISCS®		
Sanding of filler before primer	220	Red
	240	Electric Blue
Sanding of cataphoretic primer	280	Grey
	320	Salmon
Sanding of polyurethane primer	360	Pink
	400	Yellow
	500	Dark Blue
	600	Fuchsia
Cutting back lacquer before a flush joint	800	Turquoise
Retouching clear coat	1000	White
Before polishing & buffing	1500	Green



PRODUCT SELECTION

ATTACHMENT TYPE	MACHINE
BACK-UP PADS	
M14	Electrical angle grinder
5/8	Electrical & pneumatic grinders (US tools)
M8	Festo orbital sander
5/16	Other orbital sanders
M6	Mirka or CP orbital sander
M5	Rupes orbital sander

FEATURES	BENEFITS
■ Different densities, available in most popular perforations/dust hole patterns	■ Applies to a full range of applications with optimal dust extraction
■ New back plate technology	■ Heavy duty design
	■ Long life
■ Attachments for different tools	■ Adapts to all common orbital sanders
■ Easy-peel technology	■ Longer life of gripping layer
■ Colour coding of foam layer	■ Easy & quick hardness identification



BACK-UP PADS

DENSITY	COLOUR	APPLICATION
Hard	Black	Heavy duty sanding, best for flattening surfaces or dimensioning
Medium	Blue	Scuffing, shaping, sanding & finishing. For use on filler, primer, paint, clear coat, wood, plaster, composites & metal
Soft	Light Blue	Final sanding, to obtain the best finishes



Packed in clear individual display box including: safety recommendations, product information, mounting instructions, versatile attachment system (FESTO M8 and standard 5/16) and allen wrench

BACK-UP PADS NORGRIP®



DIA (mm)	DENSITY	ATTACHMENT	PK QTY	
76 	Medium	5/16	6	699573 96544
	Medium	M6	6	699573 50736
115 	Medium	M14	3	699573 50743
125 	Medium	5/16	3	699573 50739
125 	Medium	M14	3	699573 50744
150 	Medium	M14	3	636425 67812
150 	Medium	5/16 & M8	3	636425 84885
150 	Hard	5/16 & M8	3	636425 84830
	Medium	5/16 & M8	3	636425 84832
	Soft	5/16 & M8	3	636425 84834
150 	Hard	5/16 & M8	3	636425 84883
	Medium	5/16 & M8	3	636425 84884
	Soft	5/16 & M8	3	636425 84835
150 	Medium	5/16 & M8	3	636425 84842
203 	Medium	M5	1	699573 71442

WHAT IS NORGRIP® DUO?

NORGRIP®

- A universal attachment system for both Norgrip® & self-adhesive discs provides the maximum flexibility of use & the optimal results during finishing
- The Norgrip® Duo combines an innovative design of gripping structures in the shape of flat-top mushrooms which provide a very uniform finish, while allowing both self-adhesive & Norgrip® discs to be used on this unique system

NORGRIP® DUO



NORGRIP® STANDARD



BACK-UP PADS NORGRIP® DUO



DIA (mm)	DENSITY	ATTACHMENT	PK QTY	
33 	Medium	5/16	6	636425 67811
76 	Medium	5/16	6	636425 67810

Dimensions Key: DIA = Diameter

HAND PAD NORGRIP®



DIA (mm)	DENSITY	PK QTY	
125 	Medium	10	636425 96411
150 	Medium	10	636425 96414
	Soft	6	636425 96416



FOAM INTERFACE BACK-UP PADS NORGRIP®



DIA (mm)	PK QTY	
76 	10	699573 94589
150 	10	076607 07383
150 	10	699573 94590
150 	10	076607 19360



SPEC CHECK

- Specially designed to give optimal results with very fine grit abrasives, the Norton foam interfaces easily conforms to contours. These are specifically developed for the finishing operation to reduce any risk of scratching
- Norgrip® discs can be used with the Norgrip® hand pad for manual application

CONVERSION INTERFACES

DIA (mm)	PK QTY	NORGRIP® TO NORGRIP® DUO
76 	12	636425 67847
150 	12	636425 67842
150 	12	636425 67848
150 	12	636425 67850



SPEC CHECK

- Convert a standard Norgrip® back-up pad into a Norgrip® Duo & reduce the time needed for back-up pad changes. Norgrip® Duo back-up pads can be used with both Norgrip® & Self-adhesive discs. They can be used with all types of Norton abrasives



SELF-ADHESIVE DISCS

Norton Premium quality self-adhesive discs can be securely fixed onto suitable back-up pads. The Norton Pro A275 self-adhesive discs are supplied on convenient dispenser rolls of 100 discs.

APPLICATIONS & MARKETS

- Preparing primed & painted surfaces
- Stripping primer & paint
- Sanding plastic & fibre-glass
- Light weld blending & deburring
- Finishing metal



A275 NORTON PRO		NORTON PRO
BETTER	NON FERR. PAINT/VARN. HARD WOOD & SOFT WOOD 	
	FEATURES	BENEFITS
	■ New premium, heat-treated high performance aluminium oxide abrasive	■ Faster cut rate ■ Improved performance ■ More consistent uniform search pattern
	■ New unique fibre-reinforced latex paper	■ Flexible & tear resistant
	■ Water based No-Fil®	■ Improved load resistance
	■ No pigment in No-Fil® or bond	■ No risk of colour transfer
	■ Supplied in roll form with 100 discs per roll & 6 rolls in a dispenser box ■ Available in grits 80-800	■ Convenient, easy to store & merchandise

SPEC CHECK

- Dispenser for convenient & easy storage of A275 self-adhesive disc rolls

63642542772



T402 BLACK ICE

BLACKice

FERR.

PAINT/
VARN.

BETTER

FEATURES

- Premium, ultra fine silicon carbide abrasive
- Advanced resin bond system
- Advanced, A-Weight waterproof paper backing design
- Supplied in rolls of 400 discs

BENEFITS

- Best finish in wet clear-coat repair applications
- Longer life in wet applications
- Waterproof
- Ultimate flexibility & waterproof performance
- Convenient & easy to store



SELF-ADHESIVE DISCS

			NORTON PRO	BLACKice
DIA (mm)	GRIT	PK QTY	BETTER	
			A275	T402
38 	1500	400		636425 34470
	2000	400		699573 60371
	2500	400		636425 61155
125 	80	6x100	662611 31464	
	100	6x100	662611 31463	
	120	6x100	662611 31462	
	150	6x100	662611 31461	
	180	6x100	662611 31460	
	220	6x100	662611 31459	
	240	6x100	662611 31458	
	280	6x100	662611 31457	
	320	6x100	662611 31456	
	400	6x100	662611 31454	
	500	6x100	662611 31453	
	600	6x100	662611 31452	
	800	6x100	662611 31451	
125 	80	6x100	662611 31498	
	100	6x100	662611 31497	
	120	6x100	662611 31496	
	150	6x100	662611 31495	
	180	6x100	662611 31494	
	220	6x100	662611 31493	
	240	6x100	662611 31492	
	280	6x100	662611 31491	

Dimensions Key: DIA = Diameter

SELF ADHESIVE DISCS (CONTINUED)

			NORTON PRO	BLACKICE
DIA (mm)	GRIT	PK QTY	BETTER	
			A275	T402
125 	320	6x100	66261131490	
	400	6x100	66261131488	
	500	6x100	66261131487	
	600	6x100	66261131486	
	800	6x100	66261131485	
150 	80	6x100	66261131481	
	100	6x100	66261131480	
	120	6x100	66261131479	
	150	6x100	66261131478	
	180	6x100	66261131477	
	220	6x100	66261131476	
	240	6x100	66261131475	
	280	6x100	66261131474	
	320	6x100	66261131473	
	400	6x100	66261131471	
	500	6x100	66261131470	
	600	6x100	66261131469	
	800	6x100	66261131468	
150 	80	6x100	66261131515	
	100	6x100	66261131514	
	120	6x100	66261131513	
	150	6x100	66261131512	
	180	6x100	66261131511	
	220	6x100	66261131510	
	240	6x100	66261131509	
	280	6x100	66261131508	
	320	6x100	66261131507	
	400	6x100	66261131505	
	500	6x100	66261131504	
	600	6x100	66261131503	
	800	6x100	66261131502	

SPEC CHECK

- Designed to be used by hand with the maximum flexibility and versatility, the 33mm double-sided sanding block has two sides with different hardness: one for cutting, one for finishing

Pack quantity 12 63642567819



Dimensions Key: DIA = Diameter

BACK-UP PADS SELF-ADHESIVE DISCS



DIA (mm)	DENSITY	ATTACHMENT	PK QTY	
125 	Medium	5/16	3	699573 96546
150 	Medium	5/16 & M8	3	636425 94551
150 	Medium	5/16 & M8	3	636425 94552

WHAT IS NORGRIP® DUO?



- A universal attachment system for both Norgrip® & self-adhesive discs provides the maximum flexibility of use & the optimal results during finishing
- The Norgrip® Duo combines an innovative design of gripping structures in the shape of flat-top mushrooms which provide a very uniform finish, while allowing both self-adhesive & Norgrip® discs to be used on this unique system

NORGRIP® DUO

NORGRIP® STANDARD

BACK-UP PADS NORGRIP® DUO



DIA (mm)	DENSITY	ATTACHMENT	PK QTY	
33 	Medium	5/16	6	636425 67811
76 	Medium	5/16	6	636425 67810

CONVERSION INTERFACES



DIA (mm)	PK QTY	SELF-ADHESIVE TO NORGRIP® DUO
150 	6	636425 67849
150 	6	636425 67851



SPEC CHECK


- Convert a self-adhesive back-up pad into a Norgrip® Duo & reduce the time needed for back-up pad changes. Norgrip® Duo back-up pads can be used with both Norgrip® & Self-adhesive discs. They can be used with all types of Norton abrasives

PLAIN DISCS

Norton offers a range of plain sanding discs to suit all the most commonly encountered applications.

APPLICATIONS & MARKETS

- Preparing primed & painted surfaces
- Stripping primer & paint
- Sanding plastic & fibreglass
- Light weld blending & deburring
- Finishing metal



BETTER

H425

STONE

SOFT WOOD

FEATURES	BENEFITS
■ Silicon carbide abrasive	■ High cut rate
■ Strong E-weight paper	■ For dry applications only
	■ Ideal for use on stone surfaces

GOOD

Q421 SCREEN-BAK®

PAINT/
VARN/
HARD
WOOD

SOFT
WOOD

FEATURES	BENEFITS
■ Silicon carbide abrasive on an open mesh backing	■ Extreme resistance to loading
	■ Long life
	■ Waterproof

GOOD

G422

FERR.

PAINT/
VARN.

STONE




FEATURES

- Silicon carbide abrasive
- Close coat
- Strong E-weight paper

BENEFITS

- Good cutting action
- Good performance
- Economy product
- Suitable for sanding marble, stone, wood, filler & intermediate sanding of lacquer



PLAIN DISCS

DIM DIAxH (mm)	GRIT	PK QTY	BETTER	GOOD	
			H425	Q421	G422
115x22 	220	100			63642551721
	400	100			63642524135
	600	100			63642547674
125 	220	100			63642592893
	320	100			63642592892
	400	100			63642592891
150x12 	36	100	63642546553		
	40	100	69957360199		
	50	100	63642546525		
	60	100	63642546527		
	80	100	63642546529		
	100	100	69957360218		
185x12 	36	100	63642546551		
	40	100	63642546533		
	50	100	63642546535		
	60	100	63642546537		
	80	100	63642546539		
	100	100	63642546541		
185x22 	120	100	63642546543		
	36	100	63642546559		
	40	100	63642546546		
	50	100	63642546547		
	60	100	63642546548		
	80	100	63642546549		
406 	100	100	63642546550		
	60	10		66261120519	
	80	10		63642536521	
	100	10		66261120517	
	120	10		66261120516	
	150	10		63642536524	
	180	10		63642515105	
	220	10		63642552254	
	320	10		63642551671	


Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole

DOUBLE-SIDED DISCS

Norton offers a full range of double-sided discs designed to meet all commonly encountered applications. Double-sided discs have abrasive on both sides.

APPLICATIONS & MARKETS

- Floor sanding



BETTER

H835 BLUE FIRE®

PAINT/
VARN.
& HARD
WOOD



FEATURES

- Latest NorZon® grain design
- High strength paper backing (E-weight)
- Open grain distribution
- Full resin bond system

BENEFITS

- Self-sharpening grain
- Improved cut rate
- Extended product life
- Reduces curling & edge chipping
- Tear resistant
- Prevents premature clogging
- Strong grain adhesion



H425

SOFT
WOOD



STONE



FEATURES

- Extremely sharp silicon carbide abrasive
- Strong E-weight paper

BENEFITS

- Ideal for use on stone surfaces
- High cut rate
- For dry applications only



Coated
Abrasives



S413

PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD

FEATURES

- Very strong combination backing
- Sharp silicon carbide abrasive
- Very open grain distribution

BENEFITS

- High tear resistance
- Very high cutting action for rough floor sanding applications
- Long life
- Aggressive cut & clog resistant

S422

PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD

FEATURES

- Very strong combination backing
- Sharp silicon carbide abrasive

BENEFITS

- High tear resistance
- Very high cutting action on hard wood

DOUBLE-SIDED DISCS


			BLUE FIRE 			
DIM DIAxH(mm)	GRIT	PK QTY	BETTER			
			H835	H425	S413	S422
425x30 	16	25			66261033840	
	20	25			66261033842	
	24	25			63642534134	
	30	25			66261033843	
	36	25		63642534436		66261033844
	40	25		66261033845		
	50	25		66261033846		
	60	25	69957351116	66261032342		
	80	25	69957351117	66261032341		
	100	25	69957351118	63642532881		
	120	25	69957351119	63642532882		

Dimensions Key: DIM = Dimensions, DIA = Diameter, H = Hole

Norton offers a full range of cut sheets for hand and machine use, providing a range of efficient, user-friendly abrasive solutions. The extended range of dimensions and grits complies with all commonly encountered applications.

APPLICATIONS & MARKETS

- Flatten sharp edges & large surface areas
- Deburring
- Removing sanding scratches



BETTER

A275 NORTON PRO

NON FERR.

PAINT/VARN.
HARD WOOD
& SOFT WOOD

FEATURES	BENEFITS
■ New premium, heat-treated high performance aluminium oxide abrasive	■ Faster cut rate
■ New unique fibre-reinforced latex paper	■ Improved performance
■ Water based No-Fil®	■ More consistent uniform scratch pattern
■ No pigment in No-Fil® or bond	■ Flexible & tear resistant
■ Available in grits 80-1000	■ Improved load resistance
	■ No risk of colour transfer



BETTER

H425

STONE

SOFT
WOOD

FEATURES

- Silicon carbide abrasive
- Strong E-weight paper backing

BENEFITS

- Ideal for use on stone surfaces
- High cut rate
- For dry applications only



H835 BLUE FIRE®


FERR.
& NON
FERR.PAINT/
VARN.
& HARD
WOOD

FEATURES

- Latest Norzon® grain design
- High strength paper backing (E-weight)
- Open grain distribution
- Full resin bond system
- Available in grits 40-120

BENEFITS

- Self-sharpening grain
- Improved cut rate
- Extended product life
- Reduces curling & edge chipping
- Tear resistant
- Prevents premature clogging
- Strong grain adhesion



GOOD

G131

HARD
WOOD
& SOFT
WOOD

FEATURES


- Aluminium oxide abrasive
- E-weight paper backing

BENEFITS

- Good performance
- Economy product



PAPER SHEETS

			NORTON PRO		
DIM WxL(mm)	GRIT	PK QTY	BETTER		GOOD
			A275	H425	G131
93x230 	36	50			69957352150
	40	50			69957352151
	50	50			69957352152
	60	50			69957352153
	80	50			69957352154
	100	50			69957352155
	120	50			69957352159
	150	50			69957352158
	180	50			69957352157
	220	50			69957352156
115x280 	80	50	63642588214		
	100	50	63642588216		
	120	50	63642588217		
	150	50	63642588218		
	180	50	63642588221		
	220	50	63642588222		
	240	50	63642588223		
	280	50	63642588224		
	320	50	63642588225		
	400	50	63642588226		
	500	50	63642588227		
	600	50	63642588228		
	1000	50	63642514399		
115x280 	36	50			69957352138
	40	50			69957352139
	50	50			69957352137
	60	50			69957352128
	80	50			69957352140
	100	50			69957352141
	120	50			69957352146
	150	50			69957352145
	180	50			69957352144
	220	50			69957352142
203x478 	40	25		63642519223	
	60	25		63642519224	
	80	25		63642516181	
	100	25		63642519225	

Dimensions Key: DIM = Dimensions, W = Width, L = Length

NORGRIP® SHEETS



			NORTON PRO	BLUE FIRE
DIM WxL(mm)	GRIT	PK QTY	BETTER	
70x125 	80	100	A275 63642558002	H835
	100	100	63642585263	
	120	100	63642585272	
	150	100	63642558005	
	180	100	63642585274	
	220	100	63642585281	
	240	100	63642585284	
	280	100	63642585286	
	320	100	63642558006	
	360	100	63642585291	
	400	100	63642585294	
	500	100	63642569777	
	600	100	63642569669	
	800	100	63642569670	
70x198 	40	25		69957390890
	60	25		69957390892
	80	50		69957390896
	80	100	63642585468	
	100	100	63642585475	
	120	50		69957390901
	120	100	63642585477	
	150	100	63642585479	
	180	100	63642585481	
	220	100	63642585492	
	240	100	63642585493	
	280	100	63642585494	
	320	100	63642585495	
	360	100	63642585496	
	400	100	63642585497	
	500	100	63642585498	



NORGRIP® SHEETS (CONTINUED)



			NORTON PRO	BLUE FIRE
DIM WxL(mm)	GRIT	PK QTY	BETTER	
			A275	H835
70x420 	40	25		69957390902
	60	25		69957390905
	80	50		69957390909
	80	100	63642585549	
	100	100	63642585551	
	120	50		69957390910
	120	100	63642585555	
	150	100	63642585558	
	180	100	63642585561	
	220	100	63642585566	
	240	100	63642585568	
	280	100	63642585573	
	320	100	63642585576	
	360	100	63642585578	
	400	100	63642585579	
80x133 	40	25		69957390920
	60	25		69957390922
	80	50		69957390923
	80	100	63642585306	
	100	100	63642585317	
	120	50		69957390925
	120	100	63642585319	
	150	100	63642585322	
	180	100	63642585323	
	220	100	63642585326	
	240	100	63642585328	
	280	100	63642585329	
	320	100	63642585331	
	360	100	63642585337	
	400	100	63642585345	
	500	100	63642585349	

Dimensions Key: DIM = Dimensions, W = Width, L = Length

NORGRIP® SHEETS (CONTINUED)



			NORTON PRO	BLUE FIRE 
DIM WxL(mm)	GRIT	PK QTY	BETTER	
			A275	H835
81x153 	40	25		69957390884
	60	25		69957390886
	80	50		69957390885
	80	100	63642585372	
	100	100	63642585376	
	120	50		69957390873
	120	100	63642585377	
	150	100	63642585378	
	180	100	63642585383	
	220	100	63642585384	
	240	100	63642585399	
	280	100	63642585400	
	320	100	63642585402	
	360	100	63642585403	
	400	100	63642585406	
93x180 	500	100	63642585407	
	40	25		69957390927
	60	25		69957390930
	80	50		69957390931
	80	100	63642585409	
	100	100	63642585412	
	120	50		69957390932
	120	100	63642585422	
	150	100	63642585424	
	180	100	63642585428	
	220	100	63642585431	
	240	100	63642585438	
	280	100	63642585442	
	320	100	63642585446	
	360	100	63642585454	
	400	100	63642585458	
	500	100	63642585461	

NORGRIP® SHEETS (CONTINUED)



			NORTON PRO	BLUE FIRE
DIM WxL(mm)	GRIT	PK QTY	BETTER	
			A275	H835
100x150 	40	25		69957391019
	60	25		69957391020
	80	50		69957391023
	80	100	69957391028	
	120	50		69957391025
	120	100	69957391030	
	150	100	69957391033	
	180	100	69957391034	
	220	100	69957391037	
	240	100	63642576688	
	280	100	69957351543	
	320	100	69957351544	
	360	100	69957351545	
	400	100	69957351546	
	500	100	69957351547	
115x230 	40	25		69957390911
	60	25		69957390915
	80	50		69957390917
	80	100	63642585506	
	100	100	63642585507	
	120	50		69957390918
	120	100	6364258012	
	150	100	63642585508	
	180	100	6364258013	
	220	100	63642585511	
	240	100	6364258014	
	280	100	63642585517	
	320	100	63642585533	
	360	100	63642585536	
	400	100	63642585538	
	500	100	63642585543	

PLAIN SANDING BLOCK NORGRIP®



	DIM WxL(mm)	PK QTY		
	70x125	15	07660705180	

Dimensions Key: DIM = Dimensions, W = Width, L = Length

PERFORATED SANDING BLOCKS NORGRIP®



	DIM WxL(mm)	PK QTY	BETTER
	70x198 	1	69957384977
	70x125 	1	07660740445
	70x400 	1	07660719282
	115x230 	1	07660719281
	81x153 	1	07660719284

PERFORATED SANDING BLOCK ACCESSORIES

	PK QTY	BETTER
FLEXIBLE 4 METRE PIPE	1	69957371450



Norton offers a wide range of paper, cloth & waterproof sheets for use in all commonly encountered industrial applications.

APPLICATIONS & MARKETS

- Metal sanding
- Bare wood sanding
- Sanding between coats
- Scale & rust removal
- Scouring & light deburring



BEST

T402/T417 BLACK ICE®

FERR.

BLACKice

FEATURES	BENEFITS
■ Premium, ultra fine silicon carbide abrasive	■ Best finish in wet clear-coat repair applications
■ Advanced resin bond system	■ Waterproof
	■ Longer life in wet applications
■ Advanced, A-weight waterproof paper backing design	■ Ultimate flexibility & waterproof performance

BETTER

T489

FERR.

FEATURES	BENEFITS
■ Silicon carbide abrasive	■ Advanced product
■ Waterproof paper backing	■ Flexible

A275 NORTON PRO

NON
FERR.PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD

FEATURES

- Premium heat-treated aluminium oxide abrasive blend

- Fibre-reinforced latex, B-weight paper

- Water based No-Fil® anti-loading third layer

- No pigments in No-Fil® or bonding system

BENEFITS

- Long lasting, fast cut rate

- Tear resistant
- Can be used wet
- Suitable for use on primer, paint filler & coating sanding (for automotive & transport applications)

- Good finish
- Resists loading & extends life
- Can be used for composite & gel coat sanding (for marine market, etc.)

- No risk of colour transfer
- Ideal for wooden furniture preparation



R222

FERR.
& NON
FERR.PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD

FEATURES

- Aluminium oxide abrasive

- J-weight cloth backing

BENEFITS

- Flexible product



Q222

FERR.
& NON
FERR.PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD

FEATURES

- Aluminium oxide abrasive

- Non-woven cotton backing

BENEFITS

- Waterproof

- Tear resistant
- Polyvalent product



BETTER

GOOD

A213

HARD
WOOD
& SOFT
WOOD

FEATURES	BENEFITS
■ Aluminium oxide abrasive	■ Aggressive cutting action for all dry sanding applications
■ C-weight paper backing	■ Designed for heavy & light duty hand sanding

A621

FERR.
& NON
FERR.

FEATURES	BENEFITS
■ Natural Emery abrasive	■ Smooth abrasive cut
■ Paper backing	■ Gives very fine surface finishing

WATERPROOF SHEETS

			BLACKICE	
DIM WxL(mm)	GRIT	PK QTY	BEST	BETTER
			T402/T417	T489
230x280 	60	50		63642532956
	80	50	66261021180	63642532988
	100	50	66261021182	63642532989
	120	50	66261021183	63642532990
	150	50	66261021184	63642532991
	180	50	66261021185	63642532957
	220	50	66261021186	63642532992
	240	50	66261021187	63642532993
	280	50	66261021188	63642532994
	320	50	66261021189	63642532995
	360	50	66261021190	63642532996
	400	50	66261021191	63642532997
	500	50	66261021192	63642532998
	600	50	66261021193	63642532999
	800	50	66261021195	63642533000
	1000	50	66261021196	63642533001
	1200	50	66261021197	63642533002
	1500	50	63642534713	
	2000	50	63642534719	
	2500	50	63642565497	

Dimensions Key: DIM = Dimensions, W = Width, L = Length

PAPER SHEETS

			NORTON PRO		
DIM WxL(mm)	GRIT	PK QTY	BETTER	GOOD	
			A275	A213	A621
230x280 	36	25		63642538960	
	40	25		63642536385	
	50	50		63642536386	
	60	50		63642536387	
	80	50		69957360388	
	80	100	63642558015		
	100	100	63642585256	69957360389	
	120	100	63642558016	69957360390	
	150	100	63642586145	69957360391	
	180	100	63642558017	63642531774	66261101267
	220	100	63642586139	63642536411	66261101265
	240	100	63642558018	69957360394	
	280	100	63642585742		66261101263
	320	100	63642586132	69957360396	
	360	100	63642586133		
	400	100	63642586134	63642539112	
	500	100	63642586136		66261101261
	600	100	63642586137		66261101260
	800	100	63642586138		
	1000	100			66261101259
	1200	100			66261101258

CLOTH SHEETS

DIM WxL(mm)	GRIT SIZE	PK QTY	BETTER	
			R222	Q222
230x280 	36	25	63642531775	
	40	25	63642531776	69957360506
	50	25	63642531777	
	60	25	63642531778	63642536405
	80	50	63642531779	63642536407
	100	50	63642531780	63642536408
	120	50	63642531781	63642536410
	150	50	63642531782	63642536413
	180	50	63642531783	63642531773
	220	50	63642531785	63642563323
	240	50	63642531786	
	280	50	63642531788	
	320	50	63642531789	
	400	50	63642531790	
	600	50	63642534613	

Abrasive sanding sponges are designed for use on a wide variety of materials including wood, paint and metal. Their flexible nature means they can be used on curved, contoured and flat surfaces.

APPLICATIONS & MARKETS

- Light stock removal
- Sanding contours & intricate shapes
- Finishing
- Removing minor defects
- Clear coat sanding
- Base coat sanding
- Scuffing primer
- Shaping filler



BETTER

SPONGES

FERR. & NON FERR.

PAINT/VARN. HARD WOOD & SOFT WOOD

GLASS

FEATURES	BENEFITS
■ Multi-purpose	■ Can be used wet or dry
■ Flexible	■ Conform to surface shapes & contours providing a uniform finish ■ Can reach areas inaccessible to sandpaper sheets
■ Washable	■ Can be reused, giving added product life

STEEL WOOL

PAINT/VARN. & SOFT WOOD

FEATURES	BENEFITS
■ Made from strands of ultra-fine steel filaments	■ For use on wood, paint, metal, stone, marble & glass ■ Can be used with a chemical stripper ■ Ideal for cleaning & fine finishing

SOFT-TOUCH CONTOUR PADS 1 SIDED

DIM LxWxH(mm)	GRIT	FINISH GENERATED*	PK QTY	BETTER
140x115x6	60	180/120	20	636425 50599
	100	400/320	20	636425 50601
	180	600/500	20	636425 50602
	220	1000/800	20	636425 50603
	280	1500/1200	20	636425 50604

*Generates a finer finish than conventional coated abrasive products

FLEXIBLE FINISHING PADS 2 SIDED

DIM LxWxH(mm)	GRIT	PK QTY	BETTER
123x98x12,5	60	60	076607 17578
	60	250	076607 19341
	100	60	076607 05187
	100	250	076607 19342
	180	60	076607 05188
	180	250	076607 19343

FLEXIBLE SANDING SPONGES 4 SIDED

DIM LxWxH(mm)	GRIT	PK QTY	BETTER
100x66x26	60	60	076607 17579
	60	250	076607 19344
	100	60	076607 05189
	100	250	076607 19345
	180	60	076607 05190
	180	250	076607 19346

STEEL WOOL

WEIGHT	GRADE	PK QTY	BETTER
1Kg	0000	12	636425 93149
1Kg	000	12	636425 93151
1Kg	00	12	636425 93153
1Kg	0	12	636425 93154
1Kg	1	12	636425 93155
500g	Very Coarse	18	636425 93156

Dimensions Key: DIM = Dimensions, L = Length, W = Width, H = Height

A275 NORTON PRO

NON
FERR.PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD

FEATURES

- Fibre-reinforced latex, B-weight paper
- Premium heat-treated aluminium oxide abrasive blend

- Water based No-Fil® anti-loading third layer

- No pigments in No-Fil® or bonding system

BENEFITS

- Tear resistant
- Can be used wet
- Suitable for use on primer, paint filler & coating sanding (for automotive & transport applications)
- Long lasting, fast cut rate
- Good finish
- Resists loading & extends life
- Can be used for composite & gel coat sanding (for marine market, etc.)
- No risk of colour transfer
- Wooden furniture preparation



ROTOLO FOAM® ROLLS A275

PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD

FEATURES

- A275 Norton Pro premium abrasive paper
- Special No-Fil® coating
- Flexible foam backing
- Water-resistant
- 25m long roll of pre-cut sheets
- Packed in innovative dispenser box

BENEFITS

- Excellent for fine sanding with high finishing level
- Reduces clogging
- Ideal for use on round edges, contours & curves without breaking through the paint surface. Easy gripping
- Washable
- Easy to use & economical
- Easy to handle, protected against dust



H425

HARD
WOOD
& SOFT
WOOD

FEATURES

- Strong E-weight paper
- Silicon carbide abrasive

BENEFITS

- Ideal for floor sanding
- Good tear resistance
- High cut rate



BETTER

R817 NORZON®**NORZON**HARD
WOOD
& SOFT
WOOD**FEATURES**

- Heavy polyester cloth
- 100% NorZon® abrasive
- Open grain distribution

BENEFITS

- High tear resistance
- Long lasting cutting edges of NorZon® brings long life in floor sanding applications
- Reduces clogging

**R309**FERR.
& NON
FERR.HARD
WOOD**FEATURES**

- Super flexible cotton cloth
- Premium aluminium oxide abrasive
- Semi-open grain distribution

BENEFITS

- Ideal for contour & profile sanding
- Long life in wood & metal applications
- For reduced clogging in wood applications

**HANDY ROLLS R222**FERR.
& NON
FERR.HARD
WOOD
& SOFT
WOOD**FEATURES**

- J-weight cloth backing
- Aluminium oxide abrasive
- Dispenser unit

BENEFITS


- Ideal for sanding profiled surfaces & round steel parts
- Can be torn into strips
- For general purpose maintenance applications
- Ideal for deburring & derusting metal
- For easy storage
- Protects product
- Eliminates waste

**R222**FERR.
& NON
FERR.PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD**FEATURES**

- J-weight cotton cloth
- Aluminium oxide abrasive

BENEFITS

- Flexible product
- General purpose product for hand sanding of wood & metal



Q222

FERR.
& NON
FERR.HARD
WOOD
& SOFT
WOOD

FEATURES

- Non woven backing
- Aluminium oxide abrasive

BENEFITS

- Flexible & tear resistant
- Ideal for manual sanding



S413

HARD
WOOD
& SOFT
WOOD

FEATURES

- Very strong combination backing
- Sharp silicon carbide abrasive
- Very open grain distribution

BENEFITS

- High tear resistance
- Very high cutting action for rough floor sanding applications
- Long life
- Aggressive cut & clog resistant



S422

HARD
WOOD
& SOFT
WOOD

FEATURES

- Very strong combination backing
- Sharp silicon carbide abrasive

BENEFITS

- High tear resistance
- Very high cutting action on hard wood



HANDY ROLLS R212

FERR.
& NON
FERR.



FEATURES

- J-weight cloth backing
- Aluminium oxide abrasive
- Dispenser unit

BENEFITS

- Flexible product
- For general purpose maintenance applications
- For easy storage
- Protects product
- Eliminates waste



G131

PAINT/
VARN.
HARD
WOOD
& SOFT
WOOD




FEATURES

- E-weight backing
- Aluminium oxide abrasive

BENEFITS

- Economy product for sanding wood, paint & plaster
- Good performance




R230

FERR.



HARD
WOOD
& SOFT
WOOD



FEATURES

- Strong cloth backing
- High performance aluminium oxide abrasive
- Open grain distribution

BENEFITS

- Multi-purpose product ideal for floor sanding, grinding metal & sanding wood
- High cutting rate
- Reduced clogging



Dimensions Key: DIM = Dimensions, W = Width, L = Length

PAPER ROLLS

			NORTON PRO		
DIM WxL	GRIT	PK QTY	BEST	BETTER	
			H231	A275	H425
70mmx25M	40	2			
	60	2			
	80	2			
70mmx50M	120	2		69957380784	
	150	2		69957380785	
	180	2		69957380788	
	220	2		69957380790	
	240	2		69957380792	
	280	2		69957380794	
	320	2		69957380795	
	400	2		69957380797	
93mmx50M	40	2			66261020827
	60	2			66261020828
	80	2			66261020829
	100	2			66261020830
	120	2			66261020831
	150	2			66261020860
100mmx50M	40	2			66261020775
	60	2			66261020817
	80	2			66261020818
	100	2			66261020819
	120	2		63642591123	66261020820
	150	2		69957391073	66261020857
	180	2		63642591124	
	220	2		63642590924	
	240	2		63642590927	
	280	2		63642591648	
	320	2		63642591649	
	400	2		69957391077	
115mmx25M	40	2			69957391083
	60	2			69957391087
	80	2			69957391093
115mmx50M	40	2			66261020832
	60	2			63642528366
	80	2			66261020766
	100	2			66261020833
	120	2		69957380761	66261020825
	150	2		69957380765	63642528375
	180	2		69957380767	66261020861
	220	2		69957380769	66261020849
	240	2		69957380777	
	280	2		69957380778	
	320	2		69957380779	
	400	2		69957380781	

PAPER ROLLS (CONTINUED)

				NORTON PRO		
DIM WxL	GRIT	PK QTY	BEST	BETTER		GOOD
			H231	A275	H425	G131
120mmx50M	40	2				66261020822
	50	2				66261020826
	60	2	63642539189			66261020823
	80	2	63642539187			66261020834
	100	2	63642539185			66261020821
	120	2	63642539183			66261020824
	150	2	63642539181			66261020859
	180	2	63642546049			66261020865
150mmx50M	60	1	63642546050			
	80	1	69957361785			
	100	1	63642546054			
	120	1	69957361838			
	150	1	63642546058			
200mmx50M	36	1			63642557681	
	40	1			69957361909	
	50	1			69957352812	
	60	1	63642524137		63642527466	
	80	1	69957349019		63642557682	
	100	1	69957383109		63642557683	
	120	1	63642531933		63642552702	
254mmx50M	36	1			63642539191	
	40	1			63642559644	
	50	1			63642539194	
	60	1	63642548181		63642534759	
	80	1	63642548182		63642539198	
	100	1	63642551354		63642539200	
	120	1	63642551287		63642539203	
	150	1	63642548226			

Dimensions Key: DIM = Dimensions, W = Width, L = Length

NORGRIP® ROLLS



			NORTON PRO
DIM WxL	GRIT	PK QTY	BETTER
			A275
75mmx25M	120	2	69957391149
	150	2	69957391151
	180	2	69957391152
	220	2	69957391153
	240	2	69957391155
	280	2	69957391156
	320	2	69957391157
	400	2	69957391159
115mmx25M	120	2	69957391218
	150	2	69957391219
	180	2	69957391220
	220	2	69957391221
	240	2	69957391222
	280	2	69957391223
	320	2	69957391224
	400	2	69957391225

CLOTH ROLLS

			NORZON				
DIM WxL	GRIT	PK QTY	BETTER				GOOD
			R817	R309	R222	Q222	R230
50mmx50M	40	5			63642512909		
	60	5			63642540086		
	80	5			63642539135		
	100	5			63642539136		
	120	5			63642559727		
	150	5			63642539208		
	180	5			63642539137		
	220	5			63642512916		
	240	5			63642512917		
	320	5			63642512918		
	400	5			63642512919		
100mmx50M	36	1			63642536826		
	40	1			63642536559		
	50	1			63642540090		
	60	1		69957385334	63642560979		
	80	1		63642555261	63642531852	63642546066	
	100	1		69957385335	63642531854	63642546067	
	120	1		69957385336	63642531855	63642546068	
	150	1		69957384617	63642545861	63642546069	
	180	1		69957385337	63642531856		
	240	1			63642531857		
	320	1			63642545865		
	400	1			63642545867		
118mmx50M	60	1				63642536712	
	80	1				63642536713	
	100	1				63642546337	
	120	1				63642546338	
	150	1				63642546339	
	180	1				63642539178	
	220	1				63642539207	
120mmx50M	60	1		69957385339			
	80	1		63642555659			
	100	1		69957385340			
	120	1		63642555601			
	150	1		69957385341			
	180	1		69957388153			

Dimensions Key: DIM = Dimensions, W = Width, L = Length

CLOTH ROLLS (CONTINUED)

			NORZON				
DIM WxL	GRIT	PK QTY	BETTER				GOOD
			R817	R309	R222	Q222	R230
200mmx50M	24	1	63642547001				63642570720
	36	1	63642558103				63642553144
	40	1	69957397909				63642539742
	50	1	63642514307				63642539743
	60	1	63642547002				69957378387
	80	1	63642509321				63642516233
	100	1	63642514310				63642539744
254mmx50M	24	1	63642514311				63642570897
	36	1	63642514312				63642570772
	40	1	63642514313				63642557004
	50	1	63642514314				63642564506
	60	1	63642514315				63642564507
	80	1	69957363146				63642564508
	100	1	69957396296				63642507353
430mmx50M	50	1			63642539141		
	60	1			63642539142		
	80	1			63642539143		
	100	1			63642539144		
	120	1			63642539145		
	150	1			63642539146		
	180	1			63642539147		
	240	1			63642539148		

SPEC CHECK

- R222 handy rolls are designed for manual applications. The high flexibility of the cloth in combination with the wide grit range, from coarse to fine, provides an excellent tool for a variety of applications including deburring, rust removal & finishing metal
- Handy rolls are packaged in a protective, convenient dispenser which eliminates costly waste & permits neat, easy storage



HANDY ROLLS

DIM WxL	GRIT	PK QTY	BETTER R222	GOOD R212
25mmx25M 	40	1	63642531849	
	50	1	63642531850	
	60	1	63642531823	69957351243
	80	1	63642531820	69957351244
	100	1	63642531815	69957351246
	120	1	63642531811	69957351247
	150	1	63642531808	69957351248
	180	1	63642531805	69957351249
	220	1	63642531802	69957351250
	240	1	63642531799	69957351251
	280	1	63642540084	
	320	1	63642531796	69957351252
	400	1	63642531793	69957351253
	600	1	63642560206	
38mmx25M 	36	1	63642536432	
	40	1	63642531828	
	50	1	63642531826	
	60	1	63642531824	69957350654
	80	1	63642531821	69957350657
	100	1	63642531817	69957350658
	120	1	63642531812	69957350659
	150	1	63642531809	69957350660
	180	1	63642531806	69957350661
	220	1	63642531803	69957350662
	240	1	63642531800	69957350663
	280	1	63642536425	
	320	1	63642531797	69957350664
	400	1	63642531794	69957350665
	600	1	63642539150	
50mmx25M 	36	1	63642536433	
	40	1	63642531829	
	50	1	63642531827	
	60	1	63642531825	69957351254
	80	1	63642534758	69957351255
	100	1	63642531818	69957351256
	120	1	63642531814	69957351259
	150	1	63642531810	69957351260
	180	1	63642531807	69957351265
	220	1	63642531804	69957351266
	240	1	63642531801	69957351267
	280	1	63642536426	
	320	1	63642531798	69957351270
	400	1	63642531795	69957351272
	600	1	63642534757	

Dimensions Key: DIM = Dimensions, W = Width, L = Length

PRODUCT SELECTION

APPLICATION	GRIT	COLOUR
ROTOLO® FOAM ROLLS		
Sanding of body filler	120	Apple Green
	150	Orange
	180	Purple
Sanding of finishing filler	220	Red
	240	Electric Blue
Sanding cataphoretic coats & primer	280	Grey
	320	Salmon
Sanding polyurethane primer	360	Pink
	400	Yellow
	500	Dark Blue
	600	Fuchsia
Cutting back lacquer before a flush joint	800	Turquoise
Retouching clear coat	1000	White
Before polishing & buffing	1500	Green

ROTOLO® FOAM ROLLS

				NORTON PRO
DIM WxL	GRIT	PK QTY	COLOUR	BETTER
115mmx25M 	120	2	Apple Green	636425 35316
	150	2	Orange	636425 57584
	180	2	Purple	636425 57599
	220	2	Red	636425 57600
	240	2	Electric Blue	636425 57602
	280	2	Grey	636425 57604
	320	2	Salmon	636425 57606
	360	2	Pink	636425 57607
	400	2	Yellow	636425 57608
	500	2	Dark Blue	636425 57611
	600	2	Fuchsia	636425 57612
	800	2	Turquoise	636425 57613
	1000	2	White	636425 57616
	1500	2	Green	636425 57617

COMBINATION ROLLS

DIM WxL	GRIT	PK QTY	BETTER	
			S413	S422
203mmx50M	16	1	636425 12552	
	20	1	699573 52814	
	24	1	636425 12551	636425 39280
	30	1	636425 39278	636425 39283
	36	1	636425 13423	636425 39286
	40	1		636425 39289
	50	1		636425 39292
	60	1		636425 39295
	80	1		636425 39298
	100	1		636425 39300
254mmx50M	20	1	636425 46061	
	24	1	636425 46062	636425 51621
	30	1	636425 46064	636425 52435
	36	1	636425 13425	636425 52436
	40	1		636425 52603
	60	1		636425 45975
	80	1		699573 91160
	100	1		636425 47622
	120	1		699573 91161

FILM ROLLS

DIM WxL	GRIT (micron)	PK QTY	BEST
			Q132
100mmx50M	60	1	699573 97708
	40	1	699573 97701
	30	1	699573 97711
	15	1	699573 97693

All film rolls have a 76mm cross-slotted core

SPEC CHECK

- Rotolo® Foam pre-cut sheets, conveniently packaged in a roll form, are ideal for fine sanding on round edges, contours & curves, providing an outstanding finish on primers & top coats. The secret of Rotolo® Foam lies in the combination of Norton Pro A275 sanding paper & the special foam backing
- To ease product recognition, box labels are colour-coded to a specific grit size. The colour-coding follows the Norton Pro grit colour-coding system



Dimensions Key: DIM = Dimensions, W = Width, L = Length

NOTES

This image shows a single sheet of white paper with horizontal blue lines, similar to standard notebook paper. The lines are evenly spaced and run across the width of the page. There are no margins, text, or other markings on the paper.

FILE BELTS

Norton offers a range of file belts designed to perform on intricate shapes and contours.

APPLICATIONS & MARKETS

- Light deburring & blending
- Spot repairs
- General clean-up & finishing



INNOVATION

BEST

R929 SG®

FERR. & NON FERR.

SG

FEATURES	BENEFITS
■ X-weight polyester cloth	■ Extremely durable even on aggressive applications
■ Premium SG® abrasive	■ Excellent at low & medium pressure
■ High content of active filler	■ Cool cut
	■ Ideal for heat sensitive metals

BETTER

R822 NORZON®

FERR. & NON FERR.

NORZON

FEATURES	BENEFITS
■ X-weight cotton cloth	■ Durable
■ NorZon® abrasive	■ Aggressive & consistent cut
	■ Long life
	■ Ideal for stainless steel

GOOD

R230

FERR.
& NON
FERR.



HARD
WOOD
& SOFT
WOOD



FEATURES

- X-weight cotton cloth
- Aluminium oxide abrasive
- Open grain distribution

BENEFITS

- Multi-purpose product for metal & wood
- Good cutting rate
- Reduced clogging



R427

NON
FERR.



GLASS



STONE



FEATURES

- X-weight cotton cloth
- Silicon carbide abrasive

BENEFITS

- For dry grinding of glass & stone



FILE BELTS						
			SG	NORZON		
DIM WxL(mm)	GRIT	PK QTY	INNOVATION	BETTER	GOOD	
			BEST			
			R929	R822	R230	R427
10x330	40	50		63642548975		
	60	50		63642523079		
	80	50		69957336537		
	120	50		63642546799		
13x454	40	50			63642539671	
	60	50			63642539672	
	80	50			63642553323	
	120	50			63642553324	
13x457	40	50	69957350639	69957353159		
	60	50	69957350640	63642539824		
	80	50	69957350642	63642539833		
	120	50	69957350643	63642539840		
13x610	60	50	69957350646	63642539830		
	80	50	69957350647	63642539838		
	120	50	69957350648	63642539845		
15x330	40	50		63642552139		
	60	50		63642512882		
	80	50		63642552140		
	120	50		63642508195		
20x480	40	50	69957350650	63642508505		
	60	50	69957350651	63642552708		
	80	50	69957350652	63642539683		
	120	50	69957350653	63642552710		
20x520	60	50		63642551962		
	80	50		63642539684		
	120	50		63642547831		
30x533	60	20		63642538963		63642538954
	80	20		63642538964		
	120	20		63642514027		63642538955
	180	20				63642538957

Dimensions Key: DIM = Dimensions, W = Width, L = Length

NOTES

This image shows a single sheet of white paper with horizontal blue lines, similar to standard notebook paper. The lines are evenly spaced and run across the width of the page. There are no margins, text, or other markings on the paper.

Norton offers portable belts in a variety of sizes, designed to fit the most common types of machine. Portable belts are designed for all metal and wood working applications.

All Norton belts are supplied with butt joints for easy mounting and smoother work.

APPLICATIONS & MARKETS

- Surface grinding & finishing of all metals
- Blending welds
- Sanding & finishing wood
- Floor sanding



BETTER

R82A

FERR. & NON FERR.

FEATURES	BENEFITS
■ X-weight cotton cloth	■ For dry applications only
■ A blend of aluminium oxide & NorZon® abrasives	■ For visibly improved performance
■ Open grain distribution	■ Reduced clogging

W445

GLASS

FEATURES	BENEFITS
■ Polyester cloth	■ To be used wet or dry
■ Cork grain	■ Ideal for final finishing of glass edges

R427

NON
FERR.

STONE



GLASS



FEATURES

- X-weight cotton cloth
- Silicon carbide abrasive

BENEFITS

- Can be used for dry applications only
- Ideal for grinding glass & stone



R230


NON
FERR.HARD
WOOD
& SOFT
WOOD

FEATURES

- Strong cloth backing
- Aluminium oxide abrasive
- Open grain distribution

BENEFITS

- Multi-purpose product ideal for sanding wood & grinding metal
- Good cutting rate
- Reduced clogging on loading material such as wood & aluminium



PORTABLE BELTS

DIM WxL(mm)	GRIT	PK QTY	BETTER		GOOD	
			R82A	W445	R427	R230
75x457	40	20				63642538877
	60	20				63642539426
	80	20				63642539422
	120	20				63642539415
75x533	40	20				63642546289
	50	20				63642546278
	60	20				63642546257
	80	20				63642534248
	100	20				63642546273
	120	20				63642530701
75x604	60	20			63642539437	
	120	20			63642539434	
	180	20			63642545905	
	320	20			63642539433	
	CORK	20		63642539439		

Dimensions Key: DIM = Dimensions, W = Width, L = Length

PORTABLE BELTS (CONTINUED)						
DIM WxL(mm)	GRIT	PK QTY	BETTER		GOOD	
			R82A	W445	R427	R230
75x610	40	20				636425 46472
	50	20				636425 53063
	60	20				636425 46473
	80	20				636425 67329
	100	20				636425 45869
	120	20				636425 46476
100x552	40	20				636425 46291
	60	20				636425 46260
	80	20				636425 46249
	120	20				636425 46234
100x560	40	20				636425 46292
	50	20				636425 46281
	60	20				636425 46262
	80	20				636425 46250
	100	20				636425 49847
	120	20				636425 46235
100x610	36	20				636425 29801
	40	20	699573 50514			636425 46295
	50	20				636425 46283
	60	20	699573 50515			636425 60145
	80	20	699573 50516			636425 29798
	100	20				636425 46242
	120	20	699573 50517			636425 29797
100x620	40	20				636425 46457
	50	20				636425 46285
	60	20				636425 34465
	80	20				636425 29799
	100	20				636425 34770
	120	20				636425 46452
100x915	60	20				636425 45873
	80	20				636425 45875
	120	20				636425 34768
110x620	40	20				636425 30702
	60	20				636425 30700
	80	20				636425 30699
	120	20				636425 46238

Dimensions Key: DIM = Dimensions, W = Width, L = Length

NOTES

[illegible]

SPEC CHECK

- All Norton belts are supplied with butt joints for easy mounting & smoother work



A wide selection of sizes and grits for most dimensioning, intermediate grinding and polishing applications.

APPLICATIONS & MARKETS

- Grinding & deburring
- Heavy stock removal
- Blending, dimensioning & shaping
- Finishing
- Polishing



INNOVATION
BEST

U366 NORaX®

FERR.
& NON
FERR.



GLASS



NORaX
EXPERIMENTAL CONSUMABLES

FEATURES

- Polyester cloth
- Special multi-layer abrasive product
- Aluminium oxide abrasive

BENEFITS

- Generates a high quality finish
- Can be used wet
- Very long life & good cutting rate
- Increases productivity
- Grit X5 is ideal for final finishing of glass edges



U242 NORaX®

FERR.
& NON
FERR.



NORaX
EXPERIMENTAL CONSUMABLES


FEATURES

- Flexible cotton backing
- Special multi-layer abrasive products
- Aluminium oxide abrasive

BENEFITS

- Ideal for finishing operations when used with soft contact wheels
- Very long life & good cutting rate with reduced heat generation
- Increases productivity
- Multiple operations can be completed in one step, shortening application time
- Generates a high quality finish



NORaX
ENGINEERED ABRASIVES**ENGINEERED ABRASIVES**

INNOVATION
BEST

R929 SG®

SG

FERR.
& NON
FERR.

FEATURES

- Polyester cloth
- Premium SG® abrasive
- High content of active filler

BENEFITS

- Stiff backing for demanding operations
- Excellent cut rate at low & medium pressure
- Cooler cut



R955 RED HEAT

NORTON SG
REDHEATHARD
WOOD

FEATURES

- Very strong polyester backing
- SG® ceramic abrasive
- High quality product

BENEFITS

- Extra long life & tear resistant
- Time saving
- Unmatched cut rate with optimum resistance to wear, ideal for professional floor sanding
- Best for use on hard wood & large jobs
- Less belt changes



R984 SG®

SG

FERR.



FEATURES

- Heavy polyester backing
- SG® abrasive
- Requires hard contact wheel

BENEFITS

- Long life at medium to high pressure operations
- Very stiff backing for high pressure work on high powered machines
- Gives long life & high cut rate



BEST

H231

FERR.
& NON
FERR.HARD
WOOD
& SOFT
WOOD

FEATURES

- Very strong, F-weight paper
- High performance aluminium oxide abrasive
- Semi-open/open grain distribution

BENEFITS

- High performance & easy to mount
- Ideal for roughing, intermediate sanding & finishing
- Finer grits are ideal for polishing metal & plastic
- Resists clogging
- Excellent surface quality
- Less dust generated for an improved working environment



BETTER

R817 NORZON®

FERR.
& NON
FERR.HARD
WOOD

SHOE



FEATURES

- Heavy polyester cloth
- 100% NorZon® abrasive
- Open grain distribution

BENEFITS

- Stiff tear resistant backing
- Long lasting cutting edges of NorZon® brings long life even at high pressure
- Recommended for grinding soft materials like aluminium, plastic, rubber or leather
- Very good performance on hard wood



W445

GLASS



FEATURES

- Polyester cloth
- Cork grain

BENEFITS

- Tear resistant
- Better performance when used wet
- For final finishing of glass edges



R847 NORZON®**NORZON**FERR.
& NON
FERR.**FEATURES**

- Heavy polyester cloth
- NorZon® abrasive

BENEFITS

- Strong backing for high pressure work, especially in coarse grits
- For better performance use a hard contact wheel
- Long lasting cutting edges of NorZon® brings long life even at high pressure
- Very good metal removal on all steels including stainless steels

**R822 NORZON®****NORZON**FERR.
& NON
FERR.**FEATURES**

- X-weight cotton cloth
- NorZon® abrasive

BENEFITS

- Stiff backing for backstand grinding
- Long lasting

**R309**FERR.
& NON
FERR.HARD
WOOD
& SOFT
WOOD**FEATURES**

- Very flexible stretch resistant cotton cloth
- Premium aluminium oxide abrasive
- Semi-open grain distribution

BENEFITS

- Gives maximum durability
- Ideal for contour sanding on wood
- For use with a soft contact wheel
- For finishing metal parts when high flexibility is required
- Reduced clogging



R445

FERR.
& NON
FERR.

GLASS



FEATURES

- Heavy to medium weight polyester cloth
- Silicon carbide abrasive

BENEFITS

- Standard cloth for wet applications
- For use on glass, titanium or cast iron
- Ideal for use on stainless steel, especially for finer final finishing



R230

NON
FERR.HARD
WOOD
& SOFT
WOOD

FEATURES

- Strong cloth backing
- Aluminium oxide abrasive
- Open grain distribution

BENEFITS

- Multi-purpose Economy product ideal for sanding wooden floors & grinding metal
- Good cutting rate
- Reduced clogging



R293

FERR.
& NON
FERR.HARD
WOOD
& SOFT
WOOD

FEATURES

- Heavy polyester cloth
- Premium aluminium oxide
- Contains a small amount of SG® abrasive
- Active filler

BENEFITS

- Good performance
- Improved grain adhesion
- For use on metal & wood edgings
- For extended product life
- Improved life on metal applications



R265

FERR.
& NON
FERR.

FEATURES

- Heavy cotton cloth
- Premium aluminium oxide abrasive

BENEFITS

- For semi-finishing operations
- Standard general purpose cloth for metal application





The new SG generation

R980 belts are made-to-order

Please contact your local Sales or Customer Service Representative for more information

CLOTH BELTS FOR SHOE REPAIR

			NORZON
DIM WxL(mm)	GRIT	PK QTY	BETTER
			R817
40x1480	24	10	63642530673
40x1500	24	10	63642539381
	80	10	63642530691
40x1650	24	10	63642536454
	60	10	63642530675
	80	10	63642530677
	100	10	63642530676
	120	10	63642531859
50x4000	180	10	
	240	10	
	320	10	
	400	10	
100x1480	24	10	63642519730
100x1650	24	10	63642528483


CLOTH BELTS FOR GLASS

			NORAX		
DIM WxL(mm)	GRIT	PK QTY	INNOVATION	BETTER	GOOD
			BEST		
			U366	W445	R445
100x3350	60	10			63642546593
	80	10			63642546594
	100	10			63642530703
	120	10			63642546597
	150	10			63642546599
	180	10			63642546600
	220	10			63642546602
	240	10			63642546603
	320	10			63642546605
	400	10			63642546616
	CORK	10		63642546035	
	X5	10	63642518504		

Dimensions Key: DIM = Dimensions, W = Width, L = Length

CLOTH BELTS FOR FLOOR SANDING

			REDHEAT	NORZON	
DIM WxL(mm)	GRIT	PK QTY	INNOVATION	BETTER	GOOD
			BEST		
			R955		R230
200x750	24	5	699573 45034		
	24	10		699573 50608	636425 21182
	36	5	699573 45033		
	36	10		636425 15116	699573 49006
	40	5	699573 45032		
	40	10		636425 45940	699573 49007
	50	5	699573 45031		
	50	10		636425 39652	699573 53999
	60	5	699573 45030		
	60	10		636425 45918	699573 49010
	80	5	699573 45029		
	80	10		636425 52057	699573 49014
	100	5	699573 45028		
	100	10		699573 56000	699573 49394
	120	10			636425 58814



NORaX
ENGINEERED ABRASIVES

NORaX® is the innovative coated abrasive technology from Norton. The innovation lies in the abrasive layer: a multi layer coating of abrasive is engineered into a 3D pattern.

These patterns give a controlled contact surface between the abrasive and the part optimising the belt performance.

For more information about NORaX® belts and to discuss made-to-order solutions please contact your local Sales or Customer Service Representative

Dimensions Key: DIM = Dimensions, W = Width, L = Length

CLOTH BELTS FOR METAL

			SG	NORAX	SG	NORZON	NORZON		
DIM WxL(mm)	GRIT	PK QTY	INNOVATION		BEST	BETTER			GOOD
			BEST						
			R929	U242	R984	R822	R847	R309	R293 & R265
50x2000	24	10							63642548478
	36	10	69957350787			63642546222			63642546943
	40	10	69957350790			63642547270			63642551489
	50	10	69957350792			63642546218			63642551490
	60	10	69957350793			63642546210			63642546878
	80	10	69957350794			63642546212			
	120	10	69957350795			63642516010			
	180	10							63642539459*
	240	10							63642539460*
	X65	10		69957350546					
	X45	10		69957350545					
	X30	10		69957350544					
50x2500	40	10							63642540013
	50	10							63642540014
	60	10							63642540015
	80	10							63642547985
50x4000	X65	10		69957350534					
	X45	10		69957350533					
	X30	10		69957350532					
	180	10						69957384495	
	240	10						69957350781	
	320	10						69957384496	
	400	10						69957389829	
75x2000	36	10	69957350796		63642539813	63642539386	63642539811		63642547942
	40	10	69957350797			63642539388			63642564728
	50	10	69957350798		63642539814	63642538998	63642551710		63642548110
	60	10	69957350799			63642539389	63642552549		63642548528
	80	10	69957350800			63642538999			63642548275
	120	10	69957350801			63642539002			
	X65	10		69957350543					
	X45	10		69957350542					
	X30	10		69957350536					
	180	10							63642545883*
	240	10							63642520882*
75x2500	36	10	69957350882		63642529802	63642546092			63642546130
	40	10	69957350883			63642546094			63642546874
	50	10	69957350884		63642520891	63642546095			63642551506
	60	10	69957350888			63642546097			63642551507
	80	10	69957350898			63642546099			63642548275
	120	10				63642539026			

*R265 product

CLOTH BELTS FOR METAL (CONTINUED)

			SG	NORAX	SG	NORZON			
DIM WxL(mm)	GRIT	PK QTY	INNOVATION		BEST	BETTER			GOOD
			BEST						
			R929	U242	R984	R822	R847	R309	R293
75x3000	36	10				63642546224			63642551509
	50	10				63642546220			
	60	10							63642546202
	80	10				63642539320			
100x920	36	10							63642551335
	40	10							63642548306
	50	10							63642551533
	60	10				63642546216			63642548307
	80	10				63642546214			63642551544
	100	10				63642539383			63642551546
	120	10							63642551547
	150	10							63642551548
	180	10							63642551549
100x1000	40	10	69957350903			63642547284			63642521817
	50	10	69957350904			63642538971			
	60	10	69957350905			63642538973			63642551375
	80	10	69957350906			63642538975			
	100	10				63642538977			
	120	10	69957350907			63642536388			
100x2000	36	10	69957350802						
	40	10	69957350804						
	60	10	69957350805						
	80	10	69957350806						
	120	10	69957350807						
100x3000	36	10				63642547294			63642548109
	40	10							63642551511
	60	10				63642539038			63642548447
150x2000	36	10	69957350809			63642539008			
	40	10	69957350812			63642539010			
	60	10	69957350813			63642539014			
	80	10	69957350815			63642539016			

Dimensions Key: DIM = Dimensions, W = Width, L = Length

PAPER BELTS FOR WOOD

DIM WxL(mm)	GRIT	PK QTY	BEST
			H231
120x7000	60	10	63642539496
	80	10	63642539497
	100	10	63642539498
	120	10	63642539499
120x7100	60	10	63642539500
	80	10	63642539501
	100	10	63642539502
	120	10	63642539503
120x7200	60	10	63642539543
	80	10	63642539544
	100	10	63642539545
	120	10	63642539546
120x8000	60	10	63642539568
	80	10	63642539567
	100	10	63642539566
	120	10	63642539565
150x7000	60	10	63642539504
	80	10	63642539548
	100	10	63642539549
	120	10	63642539550
150x7100	60	10	63642546316
	80	10	63642539551
	100	10	63642539552
	120	10	63642539553
150x7200	60	10	63642539505
	80	10	63642539554
	100	10	63642539555
	120	10	63642539556



WIDE BELTS

Available in a range of sizes, suitable for finishing wood and metal.


APPLICATIONS & MARKETS

Metal Working

- Plate dimensioning
- Slag grinding
- Machining & deburring

Wood Working

- Intermediate sanding
- Planing & dimensioning



BEST

H231

HARD WOOD & SOFT WOOD

FERR. & NON FERR.

FEATURES	BENEFITS
■ Very strong, F-weight paper	■ High performance & easy mounting
■ High performance aluminium oxide abrasive	■ Ideal for roughing, intermediate sanding & finishing of solid wood
	■ Ideal for furniture applications
■ Semi-open/open grain distribution	■ Finer grits ideal for polishing metal, plastics leather & smoothing fillers
	■ Resists clogging
■ Anti-static properties	■ Excellent surface quality
	■ Less dust generated for an improved working environment

Coated
Abrasives

NORTON

WIDE BELTS

DIM WxL(mm)	GRIT	PK QTY	BEST
			H231
930x1525	60	10	69957337156
	80	10	69957337157
	100	10	69957337158
	120	10	69957337159
	150	10	69957337160
	180	10	69957337161
930x1900	60	10	69957337166
	80	10	69957337167
	100	10	69957337168
	120	10	69957337169
	150	10	69957337170
	180	10	69957337172
1120x1900	60	10	69957372835
	80	10	69957337515
	100	10	69957337516
	120	10	69957337517
	150	10	69957337518
	180	10	69957337519
1120x2150	60	10	63642568246
	80	10	69957337538
	100	10	69957337539
	120	10	69957337540
	150	10	69957337541
	180	10	69957337542
1350x2620	60	10	69957337795
	80	10	69957337796
	100	10	69957337797
	120	10	69957337798
	150	10	69957337799
	180	10	69957337800

Dimensions Key: DIM = Dimensions, W = Width, L = Length

FLAP WHEELS

Designed to deliver a consistent finish with a uniform rate of cut, flap wheels have a continual rate of wear which exposes new abrasive. Their construction also makes them ideal for sanding contours and uneven surfaces.

APPLICATIONS & MARKETS

- Metal fabrication
- Blending welds
- Deburring
- Cleaning & finishing



BETTER

R822 NORZON®

FERR. & NON FERR.  

FEATURES	BENEFITS
■ NorZon® abrasive	■ Long lasting cutting edges of NorZon®
■ Heavy cotton cloth	



GOOD

R207

FERR. & NON FERR.  

FEATURES	BENEFITS
■ Aluminium oxide abrasive	■ Unique manufacture technique provides low dust generation
■ Highly resistant backing	■ Consistent cut rate with ability to leave a very good finish
	■ Good life & cut rate in comparison to competition



FLANGE MOUNTED MAXIMUM OPERATING SPEED

DIA(mm)	MAX RPM
100	8000
150	5800
165	5500
200	4500
250	3500
300	2800
350	2500
400	2200

FLANGE MOUNTED

DIM DIAxWxB (mm)	GRIT	PK QTY	GOOD
			R207
100x25x25	40	1	636425 47168
150x25x25	50	2	636425 46718
	60	2	636425 63719
	80	2	636425 46728
	100	2	636425 46734
	120	2	636425 46740
	150	2	636425 46746
	180	2	636425 46749
150x50x25	40	1	636425 46719
	50	1	636425 46717
	60	1	636425 46712
	80	1	636425 46729
	100	1	636425 46735
	120	1	636425 46741
	150	1	636425 46747
	180	1	636425 46750
165x25x32	40	2	636425 47170
	60	2	636425 46711
	80	2	636425 46730
	100	2	636425 46736
	120	2	636425 46742
	150	2	636425 22957
	180	2	636425 19738
165x50x32	50	1	636425 46716
	60	1	636425 61961
	80	1	636425 46731
	120	1	636425 46743
	150	1	636425 45893
	180	1	636425 46751
	320	1	636425 45894

Dimensions Key: DIM = Dimensions, DIA = Diameter, W = Width, B = Bore

FLANGE MOUNTED (CONTINUED)

DIM DIAxWxB (mm)	GRIT	PK QTY	GOOD
			R207
200x25x35	60	2	636425 47173
	80	2	636425 47175
	100	2	636425 47174
	120	2	636425 47176
200x50x35	50	1	636425 46715
	80	1	636425 46732
	100	1	636425 46738
	120	1	636425 46744
	150	1	636425 46748
	240	1	636425 46720
250x50x35	50	1	636425 46714
	80	1	636425 46733
	100	1	636425 46739
	120	1	636425 46745
	150	1	636425 46753
	240	1	636425 39771

SPINDLE MOUNTED RECOMMENDED OPERATING SPEED

DIM DIAxWxS(mm)	RECOMMENDED MINIMUM RPM	RECOMMENDED OPTIMUM RPM	RECOMMENDED MAXIMUM RPM
30x15x6	12000	16500	25500
30x20x6	12000	16500	25500
40x20x6	9600	12500	19100
50x20x6	7000	10000	15300
50x30x6	7000	10000	15300
60x15x6	6300	8300	12700
60x30x6	6300	8300	12700
60x40x6	6300	8300	12700
80x50x6	4800	6200	9600



SPINDLE MOUNTED

			NORTON	
DIM DIAxWxS (mm)	GRIT	PK QTY	BETTER	GOOD
			R822	R207
22x10x3	80	10		63642539934
	120	10		63642539935
	150	10		63642533081
30x10x6	60	10		63642545207
	80	10		63642537371
	100	10		63642513147
	120	10		63642552728
	150	10		63642512892
	240	10		63642545208
30x15x6	60	10		63642513148
	80	10		63642561466
	100	10		63642547339
	120	10		63642551593
	150	10		63642547340
	240	10		63642547341
	320	10		63642513149
40x15x6	40	10		63642539937
	60	10		63642533099
	80	10		63642533098
	100	10		63642533095
	120	10		63642533094
	150	10		63642533092
	240	10		69957360895
40x20x6	40	10		63642539938
	60	10		63642546771
	80	10		63642546768
	120	10		63642546760
	150	10		63642533091
	240	10		63642539939
	320	10		63642539940
50x20x6	40	10		63642546774
	60	10		63642531870
	80	10		63642533097
	100	10		63642531864
	120	10		63642546759
	150	10		63642569202
	240	10		63642546724
	320	10		63642539942

Dimensions Key: DIM = Dimensions, DIA = Diameter, W = Width, B = Bore, S = Spindle

SPINDLE MOUNTED (CONTINUED)

DIM DIAxWxS (mm)	GRIT	PK QTY	BETTER	GOOD
			R822	R207
50x30x6	40	10		63642539943
	60	10		63642534251
	80	10		63642561879
	100	10		63642546765
	120	10		63642531863
	150	10		63642531860
	320	10		63642546725
60x15x6	40	10		63642546773
	60	10		69957360901
	80	10		63642546767
	100	10		63642546764
	120	10		63642546758
	150	10		69957360902
	240	10		69957360903
60x20x6	320	10		63642539945
	40	10		63642536738
	60	10		63642531869
	80	10		63642531866
	100	10		63642546763
	120	10		63642531862
	150	10		63642559975
60x30x6	240	10		63642539770
	40	10	63642539952	63642536737
	60	10	63642536547	63642531868
	80	10	63642539953	63642531865
	100	10		63642546762
	120	10		63642531861
	150	10		63642560343
80x30x6	240	10		63642546694
	320	10		63642546727
	40	10	63642539954	69957360911
	60	10	63642539955	63642531867
	80	10	63642536548	63642533096
	100	10		69957364103
	120	10		63642534250
80x50x6	150	10		63642562580
	240	10		63642545895
	40	10		69957360914
	60	10		63642559718
	80	10		69957360916
	120	10		69957360917
	150	10		63642539947
80x50x6	240	10		63642539948

Dimensions Key: DIM = Dimensions, DIA = Diameter, W = Width, S = Spindle

NOTES

This image shows a single sheet of white paper with horizontal blue lines. The lines are evenly spaced and run across the width of the page. There are no margins, text, or other markings on the paper.

The tool-free fastening systems make fast work of disc changes to maximise productivity and minimise downtime. They can be used on contours as well as flat surfaces.

APPLICATIONS & MARKETS

- Weld blending
- Light deburring & finishing
- Blending



INNOVATION
BEST

R980 X-TREME LIFE BLAZE

SG
BLAZE

FERR. 

FEATURES

- 100% premium SG® abrasive
- 3rd layer Supersize with active filler
- 3 ply polyester backing

BENEFITS

- High metal removal rate, even at medium pressure
- Cool cutting
- Best part cut & finish on stainless steel, inconels, chromium cobalt or titanium
- Exceptionally longer life, durability & aggressiveness



F986 GREENLYTE PLUS

GREENLYTE
PLUS

FERR. & NON FERR.  

FEATURES

- SG® abrasive
- Heavy fibre backing

BENEFITS

- High metal removal rate & long life
- Sharpness throughout the life of the disc
- Tear resistant with reduced edge wear



R981 SG®

SG

FERR.
& NON
FERR.

FEATURES

- SG® abrasive
- Heavyweight backing

BENEFITS

- Aggressive cutting
- High & fast stock removal on hard & soft metals
- Extended durability



MX DISCS

FERR.
& NON
FERR.

FEATURES

- Unique construction of multiple layers of cotton fibre
- Suitable for medium to light removal, deburring & finishing

BENEFITS

- Excellent cushioned grinding action
- Have the ability to grind & finish in one action
- Can increase productivity by reducing the number of process steps



MINI-FLEXI FLAP DISCS

FERR.
& NON
FERR.

FEATURES

- R822 NorZon® flexible cloth
- 50mm nylon backing
- Incorporated quick change system (TR)
- Available in grit range 40 to 80

BENEFITS

- Longer life with excellent finish
- Ideal for working on small, difficult to access & contoured surfaces
- Quick & easy to change
- Blending & finishing in one operation



BEST

BEST

MINI FLAP DISCS

FERR.
& NON
FERR.

FEATURES

- R822 NorZon® cloth
- 50mm/75mm nylon backing
- Incorporated quick change system (TR)
- Available in grit range 40 to 80

BENEFITS

- High stock removal
- Fast cutting capacity
- Long life
- Ideal for working on small, difficult to access areas
- Quick & easy to change
- Blending & finishing in one operation



BETTER

NORZON® PLUS

FERR.
& NON
FERR.

FEATURES

- Zirconia alumina abrasive with grinding aid
- Heavyweight backing

BENEFITS

- High stock removal with a cool cutting action
- Extended durability



R822 NORZON®

FERR.
& NON
FERR.

FEATURES

- NorZon® abrasive
- Heavy cotton cloth

BENEFITS

- Long lasting cutting edges especially on stainless steel
- Durable & hardwearing



SPEC CHECK

- For greater flexibility in contoured applications use a holder one size smaller than the diameter of the disc, e.g. use a 38mm holder with a 50mm disc

GOOD

R230FERR.
& NON
FERR.**FEATURES**

- High performance aluminium oxide
- Double layer cloth backing
- Open-coat grain distribution

BENEFITS

- Multi-purpose Economy product ideal for grinding ferrous metals
- Flexibility for contour grinding
- Reduced clogging

**RV71**FERR.
& NON
FERR.**FEATURES**

- High performance aluminium oxide
- Strong cotton laminated backing
- Open-coat grain distribution

BENEFITS

- Multi-purpose Economy product ideal for general purpose applications
- Durability for edge wear & fray resistance
- Reduced clogging

**PRODUCT SELECTION****MAXIMUM OPERATING SPEED (RPM)**

DIA (mm)	STAINLESS	ALUMINIUM	MID STEEL	TITANIUM	GLASS	COMPOSITES
38	20000	20000	30000	9000	9000	15000
50	15000	15000	20000	7000	7000	10000
75	10000	10000	15000	4500	4500	8000

ATTACHMENTS/BACK-UP PADS**TS - Type 2 - SL2**

Turn on/turn off system using a metal to metal fixing on pad (TS) with spindle

**TR - Type 3 - SL3**

Roll-on/roll off system using a nylon threaded male button on pad (TR) with spindle



SPEEDLOK® DISCS TR ATTACHMENT (Type 3 – SL3)


DIA (mm)	GRIT	PK QTY	<i>SG BLAZE</i>		<i>SG CERAMIC</i>	<i>NORZON PLUS</i>	<i>NORZON</i>	<i>ALOX</i>	
			INNOVATION	BEST		BETTER		GOOD	
			BEST						
			R980	F986	R981	PLUS	R822	R230	RV71
25	60	50					636425 56393	636425 60853	
38	36	50			636425 61013	636425 87423	636425 60879	636425 60856	636425 86622
	50	50				636425 87424			636425 86626
	60	50			636425 56536	636425 87425	636425 60880	636425 60857	636425 86628
	80	50			636425 61014	636425 87426			636425 86629
	120	50				636425 87427		636425 60859	636425 86631
	180	50							636425 86633
50	36	50	636425 97039	636425 56449	636425 61015	636425 56405	636425 60882	636425 60860	636425 86683
	50	50	636425 97045	636425 87282		636425 87202			636425 86685
	60	50	636425 97050	636425 56453	636425 61016	636425 56407	636425 56396	636425 09739	699573 89332
	80	50	636425 97052	636425 87285		636425 87207	636425 60884	636425 60862	636425 86687
	120	50		636425 87286	662611 37752	636425 87208	636425 60885	636425 71044	636425 86689
	180	50							636425 86691
	240	50							636425 86694
	320	50							636425 86695
75	36	50	636425 97053	636425 56546	636425 56433	636425 87245	636425 60886	636425 56363	636425 86723
	50	50		636425 87290		636425 87246	699573 89465		636425 86728
	60	50	636425 97060	636425 56548	636425 61020	636425 56411	636425 60887	636425 56364	636425 86731
	80	50		636425 87291	636425 61021	636425 87247	636425 60888		636425 86733
	120	50		636425 87292	636425 60851	636425 87248		636425 56366	636425 86735
	180	50							636425 86738

SPEEDLOK® SPECIALIST DISCS TR ATTACHMENT (Type 3 – SL3)


DIA (mm)	GRADE	PK QTY	BEST		
			MX DISCS	MINI FLEXI-FLAP DISCS	MINI FLAP DISC
50	XCRS	10	636425 88003	662611 80889	662611 80892
	COA	10	636425 88004	662611 80890	662611 80893
	MED	10	699573 82847	662611 80891	662611 80894
	FINE	10			
75	XCRS	10	636425 88005		636425 27476
	COA	10	636425 88007		662611 80904
	MED	10	699573 82850		636425 27482
	FINE	10			

Dimensions Key: DIA = Diameter

SPEEDLOK® DISCS TS ATTACHMENT (Type 2 – SL2)



DIA (mm)	GRIT	PK QTY	SG BLAZE	GREEN GLAZE PLUS	SG CERAMIC	NORZON PLUS	NORZON	ALOX	
			INNOVATION BEST	BEST		BETTER		GOOD	
			R980	F986	R981	PLUS	R822	R230	RV71
25	36	50				63642586745		63642518967	63642586540
	50	50				63642587410		63642526221	63642586564
	60	50				63642587411	63642556392	63642513099	63642586572
	80	50				63642587412		63642513100	63642586574
	120	50				63642587414		63642513101	63642586576
	180	50							63642586578
38	36	50			63642556415	63642587396	63642549604	63642556327	63642586583
	50	50			63642518312	63642587397	66261138622	66261176553	63642586587
	60	50			63642556418	63642587398	63642549607	63642556357	63642586596
	80	50			63642565569	63642587383	63642549606	63642522262	63642586607
	120	50			63642539851	63642587416		63642556296	63642586608
	180	50							63642586609
	240	50							63642586611
	320	50							63642586617
50	36	50	69957390698	63642518444	63642556423	63642556399	63642549747	63642539847	63642586651
	40	50						63642513105	
	50	50	69957390699		63642549746	63642587194	69957360306	63642522261	63642586654
	60	50	69957390700	63642556445	63642556425	63642556403	63642549748	63642539853	63642586656
	80	50			66261137775	63642587203	63642549749	63642523148	63642586660
	120	50			63642587266	63642587204	66261115917	63642539856	63642586671
	180	50							63642586675
	240	50							63642586680
75	36	50	69957390702	63642556455	63642556427	63642587209	63642549605	63642556360	63642587722
	50	50	69957390703		63642539859	63642587210	69957360307	69957387062	63642586697
	60	50		63642556545	63642556428	63642556408	63642539858	63642556361	63642586699
	80	50			63642587275	63642587214	69957360313	63642520884	63642586705
	120	50			63642519733	63642587217		63642556362	63642586708
	180	50							63642586712
	240	50							63642586715
	320	50							63642586718



SPEEDLOK® KIT TR ATTACHMENT (Type 3 – SL3)



TYPE	DIA (mm)	GRIT/GRADE DENSITY	PK QTY	
GREENLYTE PLUS F986	50	36	2	
	50	60	2	
SG® CERAMIC R981	50	36	2	
	50	60	2	
NORZON® PLUS	50	36	2	
	50	60	2	
NORZON® R822	50	36	2	
	50	60	2	
	50	80	2	
R230	50	36	2	
	50	60	2	
	50	80	2	
	50	120	2	
ALOX RV81	50	36	2	
	50	60	2	
SURFACE BLENDING BEARTEX®	50	Coarse	2	
	50	Fine	2	
	50	Very Fine	2	
UNITIZED	50	Fine	1	
STRIPPA	50	Coarse	1	
RUBBER BACK-UP PAD	50	Medium	1	

SPEEDLOK® KIT TS ATTACHMENT (Type 2 – SL2)



TYPE	DIA (mm)	GRIT/GRADE DENSITY	PK QTY	
GREENLYTE PLUS F986	50	36	2	
	50	50	2	
SG® CERAMIC R981	50	36	2	
	50	50	2	
NORZON® PLUS	50	36	2	
	50	50	2	
	50	80	2	
	50	120	2	
ALOX PLUS RV81	50	36	2	
	50	60	2	
ALOX RV71	50	36	2	
	50	60	2	
	50	80	2	
	50	120	2	
SURFACE BLENDING BEARTEX®	50	Coarse	2	
	50	Medium	2	
	50	Very Fine	2	
RUBBER BACK-UP PAD	50	Medium	1	

Dimensions Key: DIA = Diameter

BACK-UP PADS TR ATTACHMENT (Type 3 – SL3)

DIA (mm)	DENSITY	PK QTY	RUBBER WITH SPINDLE	PLASTIC HOLDER M14	RUBBER HOLDER M14	ADAPTOR
25	Medium	1	636425 56628			
38	Medium	1	636425 56629			
50	Medium	1	076607 17817			
	Hard	1	636425 86931			
75	Medium	1	636425 56631		636425 87305	
	Blue	1		636425 57133		
1/4-M14		1				636425 87997

BACK-UP PADS TS ATTACHMENT (Type 2 – SL2)

DIA (mm)	DENSITY	PK QTY	RUBBER WITH SPINDLE
25	Medium	1	076607 18963
38	Medium	1	076607 07032
50	Medium	1	636425 01157
	Hard	1	636425 86926
75	Medium	1	076607 07384
	Hard	1	636425 86932



Boasting an outstanding selection of shapes, sizes and grains, the new coated ‘Specialties’ range can be used in general purpose applications as well as more specific problematic applications. They are ideal for grinding and blending intricately shaped and contoured components, or for high speed, accurate grinding.

APPLICATIONS & MARKETS

- Metal
- Wood
- Recesses
- Contours
- Corners
- Angles



GOOD

FERR. & NON FERR.

FEATURES

■ Available in straight or tapered shapes

BENEFITS

- Straight rolls wear to the shape required
- Tapered shape is especially suited for use on contoured parts
- For sanding & polishing channels, fillets, recesses, radii, small contours & the bottom of dead-end holes

CARTRIDGE ROLLS STRAIGHT ZPE				
DIM BSxLxB(mm)	GRIT	MANDREL CODE	PK QTY	GOOD
5x19x2,4	120	CRM2	100	636425 87344
	80	CRM4	100	636425 56660
6x25x3,2	120	CRM4	100	636425 56667
	80	CRM5	100	636425 56674
6x38x3,2	120	CRM5	100	636425 56677
	150	CRM5	100	636425 56678
8x38x3,2	80	CRM5	100	636425 56680
10x25x3,2	80	CRM4	100	636425 56812
	120	CRM4	100	636425 56685

Dimensions Key: DIM = Dimensions, BS = Base, L = Length, B = Bore

KITS

To help you select the correct product, the cartridge roll kit contains 122 pieces of the most popular shapes, sizes & grits

■ 122 Piece Cartridge Roll Kit

63642557136



CARTRIDGE ROLLS STRAIGHT ZPE (CONTINUED)

DIM BSxLxB(mm)	GRIT	MANDREL CODE	PK QTY	GOOD
				R230
10x38x3,2	60	CRM5	100	63642556687
	80	CRM5	100	63642556689
	120	CRM5	100	63642556691
13x25x3,2	80	CRM4	100	63642556690
	120	CRM4	100	63642556692
13x38x3,2	60	CRM5	100	66261181251
	80	CRM5	100	63642556694
	120	CRM5	100	63642556696
16x38x4,8	80	CRM7	100	63642556697
19x25x4,8	80	CRM6	100	63642556698
	120	CRM6	100	63642556700
19x50x4,8	60	CRM8	100	69957386966
	80	CRM8	100	63642556701

CARTRIDGE ROLLS TAPERED - ZSPI

DIM BSxLxB(mm)	GRIT	MANDREL CODE	PK QTY	GOOD
				R230
10x25x3,2	60	CRM4	100	63642556703
13x38x3,2	80	CRM5	100	63642556733
	120	CRM5	100	63642556734
19x25x4,8	80	CRM6	100	63642556735
19x38x3,2	80	CRM5	100	63642556738
19x38x4,8	80	CRM7	100	63642556739
	120	CRM7	100	63642586866

CARTRIDGE ROLLS MANDRELS - ML

DIM BSxL(mm)	MANDREL CODE	PK QTY	
2,4x25	CRM2	1	63642587107
3,2x13	CRM3	1	63642587120
3,2x19	CRM4	1	63642556790
3,2x25	CRM5	1	63642556791
4,8x19	CRM6	1	63642556789
4,8x25	CRM7	1	63642556793
4,8x38	CRM8	1	63642556794

BETTER

SPIRABANDS

FERR. & NON FERR.

PAINT/VARN. HARD WOOD & SOFT WOOD

GLASS

FEATURES	BENEFITS
■ Selection of sizes & grades	■ An excellent blending & deburring tool
■ Strong construction	■ Aggressive cut
■ Use with a rubber holder	■ Forgiving finish
■ Easy to fit	■ Can reduce downtime

SPIRABANDS zSB

			NORZON	
DIM DIAxW(mm)	GRIT	PK QTY	BETTER	GOOD
			R822	R265
10 x10	80	100	63642536539	
10x20	80	100	63642539862	
13x25	50	100	63642528507	
	80	100	63642528508	
15x10	80	100	63642539863	
15x30	50	100	63642528509	
	80	100	63642528496	
22x20	36	100	63642539865	
	50	100	63642528497	
	60	100	63642539866	
	80	100	63642539867	
	150	100		63642539868
25x25	36	100	63642528510	
	50	100	63642528511	
	80	100	63642528512	
30x30	36	100	63642566870	
	50	100	63642535053	
	60	100	63642545925	
	80	100	63642545926	
	150	100		63642536540
45x30	36	100	63642528498	
	50	100	63642528514	
	60	100	63642545928	
	80	100	63642528515	
51x25	80	100	63642528518	
60x30	36	100	63642536541	
	50	100	63642539765	
	60	100	63642539874	
	80	100	63642539766	
100x40	80	100	63642539768	

Dimensions Key: DIM = Dimensions, DIA = Diameter, W = Width

SPIRABAND MANDRELS

DIM DIAxW(mm)	PK QTY	
10x10x6	10	07660707917
10x20x6	10	07660717573
13x25x6	10	07660705185
15x10x6	10	07660717629
15x30x6	10	07660705182
19x25x6	10	07660717567
22x20x6	10	63642562578
25x25x6	10	07660705183
30x20x6	10	07660717630
30x30x6	10	07660707918
38x25x6	10	07660717568
45x30x6	10	07660705196
51x25x6	10	07660705184
60x30x6	10	07660717631



OVERLAP SLOTTED DISCS

FERR.
& NON
FERR.

FEATURES

- Aluminium oxide abrasive

BENEFITS

- For rapid aggressive grinding, deburring, blending, finishing & polishing.
- Ideal for use on cylinder walls, inside diameters of tubes, frontal & bottom areas of recesses, & for chamfering drilled or stamped holes



SLOTTED DISCS zosDs

DIA (mm)	ATTACHMENT	GRIT	PK QTY	BEST
				R228/R230
38	MM32-4 8 PLY	60	10	636425 86870
		120	10	636425 86869
50		60	10	636425 86871
		120	10	636425 86886
75	MM20-4	60	10	636425 86954
		120	10	636425 86960
100		60	10	636425 86981
		120	10	636425 86983

For slotted disc mandrels, please refer to the following page

BEST

SQUARE PADS

FERR. & NON FERR.

FEATURES	BENEFITS
■ Unique construction	■ Corners wear down consistently, continually exposing fresh abrasive ■ Grinds almost as fast as hard wheels but they are much smoother & easier to control ■ For quick blending of difficult to access channels, fillets, corners, or spotting flat surfaces



SQUARE PADS ZSPs				
DIA (mm)	ATTACHMENT	GRIT	PK QTY	BEST
38	MM32-4 8 PLY	60	10	R228/R230
	MM32-4 8 PLY	120	10	63642587008
50	MM32-4 8 PLY	60	10	63642587010
	MM32-4 8 PLY	120	10	63642587014
75	MM20-4	60	10	63642587018
	MM20-4	120	10	63642587021
				63642587022

MANDRELS SLOTTED DISCS & SQUARE PADS				
DIA (mm)	ATTACHMENT	PK QTY	MANDREL	
6	MM20-4	1	63642587142	
6	MM32-4	1	63642587136	
6	MM48-4	1	63642587135	



Dimensions Key: DIA = Diameter

SANDING STARS WITH SPINDLE

FERR.
& NON
FERR.

FEATURES

- Flexible
- Wide selection of aluminium oxide abrasive grits
- Range of sizes

BENEFITS

- Ideal for deburring & polishing difficult to access metal applications
- Achieves the desired finish
- Can be used on small scale as well as large applications



SANDING STARS WITH SPINDLE

DIA (mm)	GRIT	PK QTY	BEST
			RV52
40	80	10	63642587026
	120	10	63642587034
	240	10	63642587036
	320	10	63642587037
60	80	10	63642587038
	120	10	63642587040
	240	10	63642587042
	320	10	63642587046
80	80	10	63642587050
	120	10	63642587064
	240	10	63642587068
	320	10	63642587070
100	80	10	63642587074
	120	10	63642587076
	240	10	63642587077
	320	10	63642587093



BETTER

CONES

FERR.
& NON
FERR.

SHOE

FEATURES	BENEFITS
■ Available in varying heights & diameters	■ Ideal for use on irregular shaped components such as curves, or recesses
■ Mounted on expanded rubber drums	■ Easy fitting
■ Used for grinding, deburring & polishing	■ Useful for repair work in the shoe industry

CONES zco			
DIM BxLxDG(mm)	GRIT	PK QTY	BETTER
			R822
20x14x63	36	100	662611 76761
	50	100	662611 76657
	80	100	662611 76656
	120	100	662611 76540
29x22x30	50	100	636425 13692
36x22x60	36	100	636425 20987
	50	100	636425 36572
	80	100	636425 45922
	120	100	662611 76703
50x20x40	40	100	636425 36708
64x16x31	40	100	636425 47686
82x38x40	40	100	636425 46300
85x34x45	40	100	636425 46211

CONE HOLDERS ML(zco)		
DIM BxLxDG(mm)		
20x14x63		076607 40439
36x22x63		076607 40441

Dimensions Key: DIM = Dimensions, DIA = Diameter, B = Bore, L = Length, DG = Degree

FLEXI DISCS

NORZON

FERR.
& NON
FERR.

FEATURES

- Premium NorZon® grain
- Flexible cloth backing
- Angular flap disc construction
- Available in grit range 40, 60, 80

BENEFITS

- Remove material quickly & effectively
- Adapt to contours & improved finish
- Increased flexibility in use



FLEXI DISCS FLD FXSF

			NORZON
			GOOD
DIA (mm)	GRIT	PK QTY	R822
115	40	10	636425 44276
	60	10	636425 44277
	80	10	636425 44278
127	40	10	662611 77415
	60	10	662611 77416
	80	10	662611 77417



TUNGSTEN CARBIDE BURRS

Innovative technology is now used in the range in the form of the new “Dtech” cutting edges, as well as the introduction of the new high performance Xtrem products. This new extended line of carbide burrs covers a variety of toothings and cutting shapes giving them optimum adaptation to the key characteristics of various application materials.

APPLICATIONS & MARKETS

- Weld removal
- Chamfering
- Weld preparation
- Deburring
- Aerospace
- Automotive
- Shipbuilding
- Foundry
- Aviation



BEST

XTREM

FERR.
& NON
FERR.

FEATURES	BENEFITS
■ TiAlN (Titanium aluminium nitride) coating	■ Better sliding characteristics for improved removal of chippings ■ Less wear of toothing ■ Less heat build up ■ Reduction of cutting pressure due to improved lubrication ■ Ideal for use on the hardest, Xtrem materials
■ Tungsten carbide head	■ Capable of being used at high speeds & at high temperatures
■ Skip flute design	■ Long life
■ Wide variety of cuts available	■ Sharp cutting edges for improved productivity & longer product life
■ Wide variety of shapes available	■ Suitable for many different applications

BETTER

STANDARD

FERR.
& NON
FERR.

FEATURES	BENEFITS
■ Tungsten carbide head	■ Capable of being used at high speeds & at high temperatures
■ Skip flute design	■ Long life
■ Wide variety of cuts available	■ Sharp cutting edges for improved productivity & longer product life
■ Wide variety of shapes available	■ Suitable for many different applications

Coated
Abrasives

PRODUCT SELECTION

USAGE KEY

 Highly recommended

 Recommended


CUT STYLE

D
DOUBLE CUTDTECH
DOUBLE CUT
EXTRAALU
ALUMINIUM
SPECIALDF*
FINE
DOUBLE CUTBC*
CHIP
BREAKERS*
SIMPLE

QUALITIES

Universal cutting style. Fast material removal. Smooth finish. Granular chip break.

Better stock removal. Stronger tooth formation (decreased tooth wedge angle). Longer tool life. Reduced chipping.

For deburring of aluminium alloys & plastic wide tooth formation. Easy chip flow.

Granular chip break. Fine finish applications. Use on heat treated & tough alloy steel.

General purpose deburring.

General purpose application produces scratch free surface.

XTREM

Steel



Hardened steel



Stainless steel



Cast iron



Titanium



Nickel



Copper/copper alloys



Aluminium



Plastics



STANDARD

Steel



Hardened steel



Stainless steel



Cast iron



Titanium



Nickel



Copper/copper alloys



Aluminium



Plastics




Cement



*Made-to-order


PRODUCT SELECTION



*Made-to-order

DIMENSIONS & DESCRIPTION OF THE BURR

A	16,0	x	25,0	6x65	DTECH
Shape	Diameter of the head		Length of the head	Diameter of the shank & overall length of the burr (OL)	Cut style
	D1		L1	D2 + L2	



RECOMMENDED OPERATING SPEEDS (RPM)

MATERIAL TYPE					
	3mm	6mm	10mm	12mm	16mm
Steel	60000-90000	45000-90000	30000-40000	22500-30000	18000-24000
Tempered steel	60000-90000	30000-45000	19000-30000	15000-22500	12000-18000
Stainless steel	60000-90000	30000-45000	19000-30000	15000-22500	12000-18000
Casting	45000-90000	22500-60000	15000-40000	11000-30000	9000-24000
Titanium	60000-90000	30000-45000	19000-30000	15000-22500	12000-18000
Nickel	60000-90000	30000-45000	19000-30000	15000-22500	12000-18000
Copper & copper alloys	45000-90000	22500-60000	15000-40000	11000-30000	9000-24000
Aluminium	30000-90000	15000-70000	10000-50000	7000-38000	6000-30000
Plastics	30000-90000	15000-70000	10000-50000	7000-38000	6000-30000
Cement	60000-90000	30000-45000	19000-30000	15000-22500	12000-18000

SKIP FLUTE GEOMETRY



Skip flute
geometry

All Norton Carbide Burrs have what is known as skip flute geometry, which means products are more precise and have improved cutting characteristics. This also gives greater strength and improved removal of chips.



Conventional
"centred" geometry

ADVANTAGES OF XTREM

Standard

XTREM

Material removed 0 200 400 600 800 1000 1200 1400 1600 1800

Tool: **Standard**: Shape F-12x25 6x70 Norton DTECH cut

Xtrem: Shape F-12x25 6x70 Norton XTREM DTECH cut




Workpiece: Mild Steel

SPEC CHECK

- For more information about these products as well as made-to-order capabilities, please refer to the Tungsten Carbide Burrs Catalogue




Dimensions Key: DIM = Dimensions, D¹ = Head Diameter, L¹ = Head Length, D² = Shank Diameter, L² = Shank Length

TUNGSTEN CARBIDE BURRS					
				XTREM	
PRODUCT SHAPE	SUB SHAPE	DIM D ¹ xL ¹ xD ² xL ² (mm)	PK QTY	BEST	BETTER
				XTREM	STANDARD
A CYLINDER 	D	3x13x3x38	1		636425 86518
	D	6x19x6x50	1	699573 83214	601576 38141
	D	8x19x6x65	1		601576 38143
	ALU	10x19x6x65	1	699573 83216	601576 38195
	D		1	699573 83215	601576 38144
	D	10x25x6x162	1		636425 35764
	ALU	12x25x6x70	1	699573 83220	636425 86517
	D		1	699573 83219	076607 07808
	D	16x25x6x70	1		601576 38148
B CYLINDER WITH END CUT 	D	3x13x3x38	1		601576 38140
	D	6x19x6x50	1	636425 95182	636425 86641
	D	8x19x6x65	1		076607 07804
	D	8x19x6x175	1		636425 35757
	ALU	10x19x6x65	1	699573 83228	076607 39845
	D		1	699573 83223	601576 38145
	DTECH		1	699573 83227	076607 39844
	D	12x19x6x65	1	636425 95184	
	ALU	12x25x6x70	1	699573 83232	636425 86623
	D		1	699573 83229	601576 38147
	DTECH		1	699573 83230	601576 38174
	D	16x25x6x70	1		601576 38190
C BALL NOSED CYLINDER 	D	3x13x3x38	1	636425 95185	636425 86710
	D	6x13x6x162	1		636425 35773
	D	6x19x6x50	1	699573 83234	601576 38150
	D	8x19x6x65	1		601576 38151
	ALU	10x19x6x65	1	699573 83239	601576 38182
	D		1	699573 83236	601576 38152
	DTECH		1	699573 83238	076607 39841
	D	12x19x6x65	1		601576 38153
	ALU	12x25x6x70	1	699573 83278	076607 07846
	D		1	699573 83241	601576 38154
	DTECH		1	699573 83277	601576 38175
	D	16x25x6x70	1		601576 38191
D BALL 	D	3x2,5x3x75	1		636425 35794
	D	3x2,7x3x38	1		636425 86859
	D	6x5x6x150	1		636425 35770
	D	6x5,4x6x50	1		601576 38166
	D	8x7,2x6x52	1		601576 38167
	D	10x9x6x53	1	699573 83279	076607 07832
	D	12x10,8x6x55	1	699573 83281	699573 83148

Dimensions Key: DIM = Dimensions, D¹ = Head Diameter, L¹ = Head Length, D² = Shank Diameter, L² = Shank Length

TUNGSTEN CARBIDE BURRS (CONTINUED)

PRODUCT SHAPE	SUB SHAPE	DIM D ¹ xL ¹ xD ² xL ² (mm)	PK QTY	XTREM	
				BEST XTREM	BETTER STANDARD
E OVAL 	D	3x6x3x38	1		636425 86891
	D	6x10x6x50	1		636425 86892
	D	10x16x6x60	1		601576 38159
	D	12x22x6x67	1		601576 38162
F BALL NOSED TREE 	D	3x12,7x3x75	1		699573 90247
	D	3x13x3x38	1		636425 86953
	D	6x16x6x50	1	699573 83296	636425 86955
	ALU	10x19x6x65	1	699573 83300	636425 86951
	D	10x19x6x65	1	699573 83299	601576 38170
	ALU	12x25x6x70	1	699573 83303	601576 38181
	D	12x25x6x70	1	699573 83301	601576 38171
	DTECH	12x25x6x70	1	699573 83302	601576 38179
	D	12x25x8x70	1		601576 38172
	D	16x25x6x70	1		636425 86952
G TREE 	D	3x13x3x38	1		601576 38163
	D	6x16x6x50	1	699573 83305	601576 38164
	D	10x19x6x65	1	699573 83307	601576 38165
	D	12x25x6x70	1	699573 83310	076607 07829
H FLAME 	D	8x19x6x65	1		601576 38160
	D	12x32x6x77	1	699573 83312	636425 87971
L BALL NOSED CONE 	D	6x16x5x50	1		601576 38156
	ALU	6x16x6x50	1		636425 87095
	D		1	699573 83313	
	D	8x19x6x69	1		636425 87104
	D	10x27x6x75	1		636425 87100
	ALU	12x30x6x75	1	699573 83325	636425 87101
	D		1	699573 83320	636425 87102
	DTECH	12x30x6x75	1	699573 83321	636425 87067
	D	16x33x8x78	1		636425 87103
M CONE 	D	3x11x3x38	1		636425 87134
	D	3x11,7x3x75	1		636425 35767
	D	6x19x6x50	1	699573 83326	636425 87137
	D	6x25x6x50	1		636425 87138
	D	10x16x6x65	1		636425 87133
	D	12x22x6x70	1	699573 83328	601576 38149

XTREM BURR KITS

				XTREM
KIT	SHAPE	DIM D ¹ xL ¹ xD ² xL ² (mm)	PK QTY	BEST
D	B	10x19x6x65	1	699573 85143
	B	12x25x6x70	1	
	C	10x19x6x65	1	
	C	12x25x6x70	1	
	L	12x30x6x75	1	
	E	10x16x6x60	1	
	G	10x19x6x65	1	
	G	12x25x6x70	1	
	D	12x10,8x6x55	1	
	F	12x25x6x70	1	
DTECH	B	10x19x6x65	1	699573 85141
	B	12x25x6x70	1	
	C	10x19x6x65	1	
	C	12x25x6x70	1	
	L	12x30x6x75	1	
	E	10x16x6x60	1	
	G	10x19x6x65	1	
	G	12x25x6x70	1	
	D	12x10,8x6x55	1	
	F	12x25x6x70	1	
ALU	B	12x25x6x70	1	699573 85142
	C	12x25x6x70	1	
	L	12x30x6x75	1	
	D	12x10,8x6x55	1	
	F	12x25x6x70	1	



STANDARD BURR KITS

KIT	SHAPE	DIM D ¹ xL ¹ xD ² xL ² (mm)	PK QTY	BETTER
				STANDARD
D	A	3x13x3x38	1	07660708056
	B	3x13x3x38	1	
	M	3x11x3x38	1	
	C	3x13x3x38	1	
	L	3x8x3x38	1	
	H	3x8x3x38	1	
	E	3x6x3x38	1	
	G	3x13x3x38	1	
	D	3x2,7x3x39	1	
	F	3x13x3x38	1	
DTECH	A	10x19x6x65	1	07660739870
	A	12x25x6x70	1	
	C	10x19x6x65	1	
	C	12x25x6x70	1	
	L	12x30x6x75	1	
	E	10x16x6x60	1	
	G	10x19x6x65	1	
	G	12x25x6x70	1	
	D	12x10,8x6x55	1	
	F	12x25x6x70	1	



Norton tape has been designed to extremely high standards. It's adhesive strength and flexibility makes sure it conforms easily to contours and irregular surfaces, helping to save time.



MASKING TAPE		
FEATURES	BENEFITS	
■ Rubber solvent based adhesive	■ Good adhesion on all surfaces ■ Excellent resistance to paint & thinners ■ Easy to remove leaving no adhesive residue	
	■ Conforms to most surfaces ■ Compatible with most common paints & lacquers ■ Can be removed without ripping ■ Can be torn by hand	
■ Saturated paper backing		

SPEC CHECK

PRODUCT	TEMPERATURE/TIME	APPLICATION
Premium Quality	Up to 100°C/30 min	Automotive
Medium Quality	Up to 80°C/30 min	Automotive-Building
General Purpose	60°C	Building

Dimensions Key: DIM = Dimensions, W = Width, T = Thickness, L = Length

MASKING TAPE

DIM WxL	PK QTY	BEST	BETTER	GOOD
		PREMIUM QUALITY	MEDIUM QUALITY	GENERAL PURPOSE
19mmx50M	48	699573 94601	699573 94605	699573 94617
25mmx50M	36	699573 94602	699573 94609	699573 94619
38mmx50M	24	699573 94603	699573 94611	699573 94623
50mmx50M	24	699573 94604	699573 94614	699573 94631

INSULATION TAPE

DIM WxL	PK QTY	COLOUR	BETTER
15mmx10M	20	Assorted	076607 17713
	200	Black	076607 17710
19mmx10M	40	Black	076607 17712
19mmx33M	20	Black	699573 71415



DOUBLE-SIDED FOAM TAPE

DIM WxTxL	PK QTY	BETTER
15x0,8mmx3M	20	076607 17722
6x0,8mmx10M	8	636425 49885
12x0,8mmx10M	8	076607 07953
19x0,8mmx10M	8	636425 65984
25x0,8mmx10M	8	076607 17747

ANTI-SLIP TAPE

DIM WxL	COLOUR	PK QTY	BETTER	
			NORTH EUROPE	SOUTH EUROPE
18mmx3M	BLACK	2	69957350098	69957349024
	CLEAR	2	69957350100	69957349551
36mmx3M	BLACK	1	69957350097	69957349023
	CLEAR	1	69957350099	69957349150
50mmx33M	BLACK	1	69957349030	69957349030

Anti-slip tape packaging is language specific. **North Europe:** UK, Germany, France, Netherlands, Poland.
South Europe: France, Italy, Spain, Portugal.

SPEC CHECK

- Clear rolls: for indoor use
- Black rolls: for indoor & outdoor use
- Anti-slip rolls: Applied to floors to help prevent slips & falls.
 Suitable for use on smooth, slippery surfaces.
 Not to be used on surfaces that are continuously wet, such as swimming pools; where motorised vehicles operate; where there is a high concentration of oil; on porous materials such as untreated wood



Dimensions Key: W = Width, L = Length