

URSF05G49-1P,URSF05G49-3P,URSF05G49-5P


LOW POWER SWITCHING AND CONTROL APPLICATIONS

- Repetitive Peak Off-State Voltage: $V_{DRM} = 400V$
Repetitive Peak Reverse Voltage : $V_{RRM} = 400V$
- Average On-State Current : $I_T (AV) = 500mA$
- Reduce a Quantity of Parts and Manufacturing Process Because of Built-in RGK : $R_{GK} = 1k\Omega, 2.7k\Omega, 5.1k\Omega$ (Typ.)

MAXIMUM RATINGS


CHARACTERISTIC	SYMBOL	RATINGS	UNIT
Repetitive Peak Off-State Voltage and Repetitive Peak Reverse Voltage	V_{DRM} V_{RRM}	400	V
Non-Repetitive Peak Reverse Voltage (Non-Repetitive<5ms, $T_j = 0\sim 125^\circ C$)	V_{RSM}	500	V
Average On-State Current (Half Sine Waveform)	$I_T (AV)$	500	mA
R.M.S On-State Current	$I_T (RMS)$	800	mA
Peak One Cycle Surge On-State Current (Non-Repetitive)	I_{TSM}	9 (50Hz) 10 (60Hz)	A
I^2t Limit Value	I^2t	0.4	A^2s
Critical Rate of Rise of On-State Current (Note 1)	di / dt	10	$A / \mu s$
Peak Gate Power Dissipation	P_{GM}	0.1	W
Average Gate Power Dissipation	$P_{G(AV)}$	0.01	W
Peak Forward Gate Voltage	V_{FGM}	3.5	V
Peak Reverse Gate Voltage	V_{RGM}	-5	V
Peak Forward Gate Current	I_{GM}	125	mA
Junction Temperature	T_j	-40~125	$^\circ C$
Storage Temperature Range	T_{stg}	-40~125	$^\circ C$

Unit: mm



Weight: 0.2 g

EQUIVALENT CIRCUIT




NOTE 1: di / dt Test condition
 $i_G = 5mA$, $t_{gw} = 10\mu s$,
 $t_{gr} \leq 250ns$

ELECTRICAL CHARACTERISTICS (Ta = 25°C)







CHARACTERISTIC		SYMBOL	TEST CONDITION	MIN	TYP.	MAX	UNIT
Repetitive Peak Off-State Current and Repetitive Peak Reverse Current		I_{DRM} I_{RRM}	$V_{\text{DRM}} = V_{\text{RRM}} = \text{Rated}$	—	—	10	μA
Peak On-State Voltage		V_{TM}	$I_{\text{TM}} = 1\text{A}$	—	—	1.5	V
Gate Trigger Voltage		V_{GT}	$V_{\text{D}} = 6\text{V}, R_{\text{L}} = 100\Omega$	—	—	0.8	V
Gate Trigger Current	URSF05G49-1P	I_{GT}		250	700	1000	μA
	URSF05G49-3P			100	250	400	
	URSF05G49-5P			50	160	250	
Holding Current	URSF05G49-1P	I_{H}	$I_{\text{TM}} = 500\text{mA}, V_{\text{D}} = 6\text{V}$	—	—	6	mA
	URSF05G49-3P			—	—	3	
	URSF05G49-5P			—	—	2	
Resistor Between Gate and Cathode	URSF05G49-1P	R_{GK}	—	700	1000	1300	Ω
	URSF05G49-3P			1890	2700	3510	
	URSF05G49-5P			3570	5100	6630	
Critical Rate of Rise of Off-State Voltage	URSF05G49-1P	d_v / dt	$V_{\text{DRM}} = \text{Rated}, \text{Exponential Rise}$	—	200	—	V / μs
	URSF05G49-3P			—	70	—	
	URSF05G49-5P			—	40	—	
Turn-On Time		t_{gt}	$V_{\text{D}} = \text{Rated}, i_{\text{G}} = 5\text{mA}$	—	—	1.5	μs
Thermal Resistance		$R_{\text{th (j-a)}}$	Junction to Ambient	—	—	70	$^{\circ}\text{C} / \text{W}$







Note: Thermal Resistance Test Condition
Use 0.6×30×30mm Alumina Plate





MARK



NUMBER	TYPE	MARK
* 1	URSF05G49-1P	PB
	URSF05G49-3P	PC
	URSF05G49-5P	PD







RESTRICTIONS ON PRODUCT USE

000707EAA

- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc..
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.