




REVISONS		1-0431		SH 1
REV	DESCRIPTION	DWN	APPROVED	DATE
K	REVISED PER ECO 16361	L.M.	<i>Amc</i>	9/4/07

DASH NO	FIG	CABLES ACCOMMODATED	ASSEMBLE PER
-1	1	RG-58	TAI-101
-U1		ESSEX 621-715	
-2		RG-59	
-U2			
-2A		BELDEN 8279	
-U2A			
-2B		W.E.CO. 730A	
-U2B			
-3		RG-223	
-U3			
-3A		RG-55	
-U3A			
-4		RG-122	
-U4		BELDEN 8218	
-5		RG-174	
-U5		RG-187	
-5A		RG-196	
-U5A			
-5B		HEWLETT-PACKARD 8120-1107	
-U5B			
-21		RG-303	
-U21			
-22		RG-180	
-U22			
-34		BELDEN 8228	
-U34			
-36		MICRODOT 275-3991	
-U36		AMPEX 616-569	
-41		RG-304	
-U41		BELDEN 9248	
-44		BRAND-REX B749	
-U44		GORE C06C032	
-63		734A AT & T	
-U63			
-086	2	RG-405	TAI-130
-U086			
-141		RG-402	
-U141			



-1 SHOWN



RECOMMENDED
PANEL CUTOUT
SCALE: 4/1

4. EXAMPLE OF COMPLETE PART NUMBER:

U PL122 -086
"U" DESIGNATES 75 OHM IMPEDANCE OMIT FOR 50 OHM IMPEDANCE VERSION
DASH NUMBER (CABLE GROUP)
BASIC PART NUMBER

3. 50 AND 70 OHM COAXIAL PUSH-ON TYPE BULKHEAD CABLE PLUG, BNC STYLE

△ MAXIMUM PANEL THICKNESS: .187 (REMOVE SPACER)

1. FINISH: TFS-1A (NICKEL)

RED INDICATES ORIGINAL

QTY	DESCRIPTION		PART NUMBER		ITEM
TOL UNLESS SPECIFIED .XX ± .02 .XXX ± .010 .XXXX ± .0005 ANGLES ±	TROMPETER ELECTRONICS, INC.		PL122/UPL122		
DWN L.M. 4-23-07	MATERIAL	CODE IDENT	DRAWING NO.	REV	
CHK <i>AM</i> 6/22/07		14949	1-0431	K	
ENGR	SCALE 4/1	DATE 8/14/74	SHEET 1C		
APPR <i>AM</i> 8/31/07					

NEXT ASSY