


REV.	DATE	DESCRIPTION
A	11/24/99	MODIFY BACK CAP
B	05/08/07	UPDATE DRAWING FORMAT, REVISE BODY AND FERRULE DIMENSIONS



NOTE:

1. CRIMPED FERRULE HEX CRIMP SIZE .151"
2. CONTACT PIN TO SOLDER.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex			
8						DRAWN	G.R.S.	05/08/07					
7						CHECKED			PART DESCRIPTION SMB R/A CRIMP PLUG (FOR RG–316U/D CABLE)				
6	HEAT SHRINK TUBE			1		ISSUED							
5	COVER	BRASS	NICKEL	1		SHEET	1 OF 1						
4	FERRULE	COPPER	NICKEL	1			PART NO.		142188				
3	CONTACT PIN	BER. COPPER	GOLD	1									
2	INSULATOR	TEFLON	NATURAL	1			DWG. NO.		142188.DWG				
1	BODY	BRASS	NICKEL	1			REV. B						SIZE A
	DESCRIPTION	MATERIAL	FINISH	QTY			C:/142/142188.DWG						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[142188](#)