

IGBT

TRENCHSTOP™ IGBT4 Low Power Chip
IGC189T120T8RL

Data Sheet

Industrial Power Control

Table of Contents

Features and Applications.....	3
Mechanical Parameters.....	3
Maximum Ratings	4
Static and Electrical Characteristics	4
Further Electrical Characteristics	5
Chip Drawing.....	6
Revision History	7
Relevant Application Notes	7
Legal Disclaimer	8

TRENCHSTOP™ IGBT4 Low Power Chip

Features:


- 1200V trench & field stop technology
- Low switching losses
- Positive temperature coefficient
- Easy paralleling

Recommended for:

- Low / medium power modules

Applications:

- Low / medium power drives



Chip Type	V_{CE}	I_{Cn}	Die Size	Package
IGC189T120T8RL	1200V	200A	13.62mm x 13.87mm	Sawn on foil

Mechanical Parameters

Die size		13.62 x 13.87	mm ²
Emitter pad size		See chip drawing	
Gate pad size		1.31 x 0.81	
Area total		188.91	
Silicon thickness		115	μm
Wafer size		200	mm
Maximum possible chips per wafer		125	
Passivation frontside		Photoimide	
Pad metal		3200nm AlSiCu	
Backside metal		Ni Ag – system To achieve a reliable solder connection it is strongly recommended not to consume the Ni layer completely during production process	
Die bond		Electrically conductive epoxy glue and soft solder	
Wire bond		Al, ≤500μm	
Reject ink dot size		Ø 0.65mm; max. 1.2mm	
Storage environment (<6 months)	for original and sealed MBB bags	Ambient atmosphere air, temperature 17°C – 25°C	
	for open MBB bags	Acc. IEC 62258-3; Section 9.4 Storage Environment.	

Maximum Ratings

In general, from reliability and lifetime point of view, the lower the operation junction temperature and/or the applied voltage, the greater the expected lifetime of any semiconductor device.

Parameter	Symbol	Value	Unit
Collector-emitter voltage, $T_{vj}=25^{\circ}\text{C}$	V_{CE}	1200	V
DC collector current, limited by $T_{vj\text{ max}}^1$	I_C	-	A
Pulsed collector current, t_p limited by $T_{vj\text{ max}}^2$	$I_{C,puls}$	600	A
Gate-emitter voltage	V_{GE}	± 20	V
Junction temperature	T_{vj}	$-40 \dots +175$	$^{\circ}\text{C}$
Operating junction temperature	$T_{vj\text{ op}}$	$-40 \dots +150$	$^{\circ}\text{C}$
Short circuit data ^{1/2/3} $V_{GE}=15\text{V}$, $V_{CC}=800\text{V}$, $T_{vj}=150^{\circ}\text{C}$	t_{sc}	10	μs

Static Characteristics (tested on wafer), $T_{vj}=25^{\circ}\text{C}$

Parameter	Symbol	Conditions	Value			Unit
			min.	typ.	max.	
Collector-emitter breakdown voltage	$V_{(BR)CES}$	$V_{GE}=0\text{V}$, $I_C=1\text{mA}$	1200	-	-	V
Collector-emitter saturation voltage	V_{CEsat}	$V_{GE}=15\text{V}$, $I_C=60\text{A}$	1.11	1.19	1.27	
Gate-emitter threshold voltage	$V_{GE(th)}$	$I_C=7.4\text{mA}$, $V_{GE}=V_{CE}$	5.3	5.8	6.3	
Zero gate voltage collector current	I_{CES}	$V_{CE}=1200\text{V}$, $V_{GE}=0\text{V}$	-	-	2.6	μA
Gate-emitter leakage current	I_{GES}	$V_{CE}=0\text{V}$, $V_{GE}=20\text{V}$	-	-	120	nA
Integrated gate resistor	r_G		-	3.5	-	Ω

Electrical Characteristics ²

Parameter		Symbol	Conditions	Value			Unit
				min.	typ.	max.	
Collector-emitter saturation voltage	$T_{vj}=25^{\circ}\text{C}$	V_{CEsat}	$V_{GE}=15\text{V}$, $I_C=200\text{A}$	1.55	1.8	2.05	V
	$T_{vj}=150^{\circ}\text{C}$			-	2.1	-	
Input capacitance		C_{ies}	$V_{CE}=25\text{V}$, $V_{GE}=0\text{V}$, $f=1\text{MHz}$ $T_{vj}=25^{\circ}\text{C}$	-	14000	-	pF
Reverse transfer capacitance		C_{res}		-	500	-	

¹ Depending on thermal properties of assembly.

² Not subject to production test - verified by design/characterization.


³ Allowed number of short circuits: <1000; time between short circuits: >1s.

Further Electrical Characteristics

Switching characteristics and thermal properties are depending strongly on module design and mounting technology and can therefore not be specified for a bare die.

Application example	FS200R12KT4R_B11	Rev. 2.1
---------------------	------------------	----------

Chip Drawing



E = Emitter

G = Gate

T = Test pad do not contact

Bare Die Product Specifics

Test coverage at wafer level cannot cover all application conditions. Therefore it is recommended to test all characteristics which are relevant for the application at package level, including RBSOA and SCSOA.

Description

AQL 0.65 for visual inspection according to failure catalogue

Electrostatic Discharge Sensitive Device according to MIL-STD 883

Revision History

Revision	Subjects (major changes since last revision)	Date
2.0	Final data sheet	09.09.2016

Relevant Application Notes

--	--

Published by
Infineon Technologies AG
81726 München, Germany
© Infineon Technologies AG 2016.
All Rights Reserved.

IMPORTANT NOTICE

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples, hints or any typical values stated herein and/or any information regarding the application of the product, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

In addition, any information given in this document is subject to customer's compliance with its obligations stated in this document and any applicable legal requirements, norms and standards concerning customer's products and any use of the product of Infineon Technologies in customer's applications.

The data contained in this document is exclusively intended for technically trained staff. It is the responsibility of customer's technical departments to evaluate the suitability of the product for the intended application and the completeness of the product information given in this document with respect to such application.

For further information on the product, technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies office (www.infineon.com).

Please note that this product is not qualified according to the AEC Q100 or AEC Q101 documents of the Automotive Electronics Council.

WARNINGS

Due to technical requirements products may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies office.

Except as otherwise explicitly approved by Infineon Technologies in a written document signed by authorized representatives of Infineon Technologies, Infineon Technologies' products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury.

www.infineon.com