

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

43915-1106

Status:

Active

Overview:

Mini-Fit Sr.™

Description:

10.00mm Pitch Mini-Fit Sr.™ Header, Dual Row, Vertical, 6 Circuits, 2.36mm PCB Thickness, Tin (Sn) Plating

Documents:

3D Model

Drawing (PDF)

Product Specification PS-42815-001 (PDF)

Test Summary TS-42815-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

43915

Application

Power, Wire-to-Board

Overview

Mini-Fit Sr.™

Product Name

Mini-Fit Sr.™

Physical

Breakaway

No

Circuits (Loaded)

6

Circuits (maximum)

6

Color - Resin

Black

Durability (mating cycles max)

30

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Number of Rows

2

Orientation

Vertical

PC Tail Length

5.10mm

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

2.40mm

Packaging Type

Tray

Pitch - Mating Interface

10.00mm

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Polarized to Mating Part

Yes

Polarized to PCB

Yes

Shrouded

Fully

Stackable

No

Surface Mount Compatible (SMC)

No

Temperature Range - Operating

-40°C to +105°C

Termination Interface: Style

Through Hole




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

43915Series

Mates With

43914 Mini-Fit Sr.™ Receptacle Housing

Electrical

Current - Maximum per Contact	50A
Voltage - Maximum	600V

Solder Process Data

Duration at Max. Process Temperature (seconds)	8
Lead-free Process Capability	SMC & Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	265

Material Info

Reference - Drawing Numbers

Product Specification	PS-42815-001, RPS-42815-001, RPS-42815-011, RPS-42815-012, RPS-42815-013, RPS-42815-014, RPS-42815-015
Sales Drawing	SD-43915-002
Test Summary	TS-42815-001

This document was generated on 03/30/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

43915-1106