


8				7			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION			
COPYRIGHT 20				20			
BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.							
PART NUMBER		REV	FIRST USED	POWER UNIT	FEED TYPE	DESCRIPTION	
1852343-1		B	122500-1	LEADMAKER	AIR FEED	CUTS CARRIER	
1852343-2		B	565435-5	BENCH MODEL K	AIR FEED	CUTS CARRIER	
1852343-3		B	354500-1	BENCH MODEL G	AIR FEED	CUTS CARRIER	
1852343-6		B	122500-1	LEADMAKER	AIR FEED	CONTINUOUS CARRIER	
7-1852343-7		A	-	-	-	SPARE PARTS	


- △ RECOMMENDED SPARE PARTS
- △ GREASE LIGHTLY
- △ GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE
- △ CRIMP HEIGHTS FOR 1949164-1 ONLY; MAX CMA=11,094 WHEN RUNNING 16-12AWG, ADDITIONAL SHIMS WILL BE REQUIRED TO OBTAIN CRIMP HEIGHT.
- △ CRIMP HEIGHTS FOR 1949165-1 ONLY; MAX CMA=9,960 WHEN RUNNING 16-14AWG, ADDITIONAL SHIMS WILL BE REQUIRED TO OBTAIN CRIMP HEIGHT.
- △ DO NOT INSTALL SHIMS IN APPLICATOR BEFORE SHIPPING. BAG & SHIP SEPARATELY WITH APPLICATOR.

*** WARNING**
ON INSTALLATION, SET WIRE DISC TO LARGEST WIRE SIZE SETTING. USE OF SETTINGS BELOW MIN. REQUIRED CRIMP HEIGHT SETTING WILL CAUSE DAMAGE TO CRIMP TOOLING.



TERMINAL NAME: SEALCO PIN & SOCKET					
TYCO PN	SEALCO PN	SEALCO TERMINAL - AMP CRIMP SPECS			
1949164-1	NDF-1				
1949165-1	NDM-1				
-	-	CRIMP HEIGHT	WIRE SIZE	REF SETTING	
-	-	.118±.002[3.00±0.05mm]	10AWG	B3	
-	-	.118±.002[3.00±0.05mm]	12 & 14AWG	A9	
-	-	.108±.002[2.74±0.05mm]	(2)14AWG	C8	
-	-	.102±.002[2.59±0.05mm]	12AWG	D9	
-	-	CRIMP	SIZE	TYPE	RANGE
-	-	WIRE	.160 [4.06mm]	F	16-10 AWG
-	-	INSUL	-	-	-
WIRE STRIP LENGTH	TERM APPL SPEC	FEED	APPLICATOR INSTRUCTIONS		SET UP GAGE
.243 - .258	NONE	.828	408-8040 & 408-8490		458637-1

ADDITIONAL CRIMP HEIGHTS		
CRIMP HEIGHT	WIRE SIZE	REF SETTING
.092±.002[2.34±0.05mm]	14AWG	E0
.086±.002[2.18±0.05mm]	16AWG	F2
.109±.002[2.77±0.05mm]	10AWG	C8
.109±.002[2.77±0.05mm]	12 & 14AWG	C4
.099±.002[2.51±0.05mm]	(2)14AWG	E3
.093±.002[2.36±0.05mm]	12AWG	F2
.083±.002[2.11±0.05mm]	14AWG	F2
.080±.002[2.03±0.05mm]	16AWG	F2



6 6 6	-	-	-	-	-	469367-4	SHIM	6	122
	-	-	-	-	-	469367-3	SHIM	6	121
	-	-	-	-	-	469367-2	SHIM	6	120
-	-	-	-	-	-	469367-1	SHIM	6	119
-	-	-	REF	-	-	692655-6	AIR FEED VALVE ASSEMBLY		118
-	-	-	-	-	-	461062-1	FEED FINGER ASSEMBLY		117
-	-	-	REF	-	..	455749-1	GUARD WINDOW		116
-	-	-	REF	-	..	679532-1	INSERT, GUARD		115
3 3	-	-	-	-	-	371178	WASHER		113
-	-	-	-	-	-	3-21001-5	SCR, SKT HD CAP 3/8-16 X 1.000		111
-	-	-	-	-	-	459610-1	MOUNT, FEED BRACKET		110
-	-	-	-	-	-	21024-8	WASHER, SPRG LOCK, REG 3/8		109
-	-	-	-	-	-	692655-7	AIR FEED VALVE ASSEMBLY		108
-	-	-	-	-	-	461690-3	SPACER, AIR FEED		107
-	-	-	REF	-	-	24024-2	VALVE, SHUT OFF		106
-	-	-	-	-	-	692655-5	AIR FEED VALVE ASSEMBLY		105
-	-	-	-	-	-	461065-1	ASSEMBLY, AIR FEED		104
-	2	2	2	2	-	4-21000-2	SCR, SKT HD CAP 10-32 X 1.750		103
-	2	2	2	2	-	1-21000-6	SCR, SKT HD CAP 4-40 X .625		98
-	2	2	2	2	-	1-21002-4	SCR, BTN SKT HD CAP 4-40 X .375		97
-	-	-	-	-	-	189807-3	FENCE		96
-	-	-	-	-	-	318563-1	GUARD, FRONT CHIP		89
-	-	-	-	-	-	4088040	SF APPL INST 408-8040		72
-	-	-	-	-	-	217238-1	GENERAL INSTRUCTION PKG		71
-	2	2	2	2	-	21024-2	WASHER, SPRG LOCK, REG NO 4		68
-	-	-	-	-	-	461264-5	PLATE, IDENTIFICATION		67
-	2	2	2	2	-	21017-2	SCREW, DRIVE		66
-	-	-	-	-	-	21009-2	SCR, SET, SELF LOCKING 1/4-20 X .250		63
-	-	-	-	-	-	22733-8	SCR, BHSC, SELF-LOCKING, 8-32 X .375		60
-	-	-	-	-	-	2-22603-0	SCR, HEX HD CAP 8-32 X .312		59
-	-	-	-	-	-	3-694433-1	FEED PAWL		56
-	4	4	4	4	-	2-21002-2	SCR, BTN SKT HD CAP 8-32 X .500		54
-	2	2	2	2	-	2-21000-8	SCR, SKT HD CAP 8-32 X .625		53
-	-	-	-	-	-	21018-5	NUT, HEX, REG 6-32		52
-	-	-	-	-	-	811242-2	BUMPER, HOLD DOWN		51
-	-	-	-	-	-	690753-1	SPACER, TONKER		50
-	-	-	-	-	-	1633399-1	APPL., BASIC AIR FEED SUB ASSY		46
-	-	-	-	-	-	690191-1	PLUG,NYLON		45
-	-	-	-	-	-	1-455673-5	RAM, SIDE FEED		44
-	-	-	-	-	-	7-21002-9	SCR, BTN SKT HD CAP 5/16-24 X 1.00		41
-	-	-	-	-	-	690125-1	SHIM SUB-ASSY		39
-	-	-	-	-	-	469367-8	SHIM		38
-	-	-	-	-	-	879103-4	FINE ADJUST HEAD ASSEMBLY		37
-	-	-	-	-	-	3-690786-4	TERMINAL SUPPORT		34
-	3	3	3	3	-	21024-5	WASHER, SPRG LOCK, REG NO 10		32
-	-	-	-	-	-	7-21000-6	SCR, SKT HD CAP 10-32 X .312		31
-	-	-	-	-	-	21989-8	SCR, SKT HD SHLDR 3/16 DIA X .250		30
-	-	-	-	-	-	1633091-6	ASSEMBLY, STRIP GUIDE		29
-	2	2	2	2	-	5-21006-6	SCR, SET, CUP POINT 10-32 X .750		28
-	2	2	2	2	-	1-22284-0	SPRING, COMPRESSION		27
-	-	-	-	-	-	356835-1	LEVER, DRAG RELEASE		26
-	-	-	-	-	-	240792-1	DRAG, TERMINAL		25
-	-	-	-	-	-	2-679651-8	FRONT STRIP GUIDE		23
-	-	-	-	-	-	2-21000-7	SCR, SKT HD CAP 8-32 X .500		21
-	4	4	4	4	-	21024-4	WASHER, SPRG LOCK, REG NO 8		20
-	-	-	-	-	-	691353-1	STRIPPER		19
-	-	-	-	-	-	679625-2	SHEAR HOLDER, FRONT (NO CUT)		17
-	-	-	-	-	-	3-22280-3	SPRING, COMPRESSION		12
-	-	-	-	-	-	690461-2	STOP, SHEAR		11
-	-	-	-	-	-	1-690459-0	SHEAR HOLDER, FRONT		10
-	-	-	-	-	-	454276-9	FLOATING SHEAR, FRONT		9
-	-	-	-	-	-	6-1633117-1	ANVIL COMBINATION		8
-	-	-	-	-	-	240641-5	SPACER		7
-	-	-	-	-	-	2-455889-1	DEPRESSOR, SHEAR		5
-	-	-	-	-	-	1-455888-0	SPACER, CRIMPER		2
-	-	-	-	-	-	456414-2	CRIMPER, WIRE		1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1852343-1](#)