

Customer Information Sheet

DRAWING No.: P19-XX21

SHEET 2 OF 2


IF IN DOUBT - ASK

(C)

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



ORDER CODE:


P19-XX21

PROBE HEAD: _____
VARIANT (SEE TABLE)


NOTES:

1. TO BE USED WITH SLEEVE S19-501.
2. SUITABLE FOR A MINIMUM DISTANCE BETWEEN CENTRES OF 1.90mm.


PROBE HEAD VARIANTS




SPEAR HEAD
P19-0121



CONVEX HEAD
P19-2221



CONCAVE HEAD
P19-1121



SERRATED HEAD
P19-4021

SPECIFICATIONS:

MATERIAL:

PLUNGER:

P19-0121 = STEEL

P19-1121, P19-2221, P19-4021 = BERYLLIUM COPPER

BARREL = BRASS

SPRING = STAINLESS STEEL

FINISH:

PLUNGER AND BARREL = GOLD

ELECTRICAL:

CURRENT RATING = 3A

CONTACT RESISTANCE = 100mΩ MAX AT 2/3 TRAVEL

MECHANICAL:

DURABILITY = 100,000 CYCLES MIN

FULL TRAVEL = 2.54mm

SPRING FORCES:

AT FULL TRAVEL = 1.26N ± 0.25N (128g ± 20%)

AT 2/3 TRAVEL = 0.88N ± 0.18N (90g ± 20%)

ENVIRONMENTAL:

OPERATING TEMPERATURE = -40°C TO +180°C

MSP	6	21.07.17	20124
NAME	ISS.	DATE	C/NOTE
APPROVED:		M.PERREN	
CHECKED:		M.PLESTED	
DRAWN:		W. J. BOURNE	
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

www.harwin.com
technical@harwin.com

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.50mm
X.XX = ±0.10mm
X.XXX = ±0.01mm

ANGLES = ±5°

UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH:

SEE ABOVE

S/AREA:

mm²

TITLE:

1.90mm MIN. CENTRE
TWO-PIECE SPRING PROBE

DRAWING NUMBER:

P19-XX21

SHT
2 OF 2