

Miniature Circuit Breakers

- Overview
- Data
- Contacts

S201-K16

Print View.
Print to Pdf.

→ OK

☒Products & Services only

+Rate this page

+Share this page

Your preferences:

Egypt

→ OK

English

→ OK

ABB contact for Egypt

Sales: → Amr Younis

Service: → Ahmed El-Saeed

Select another country

→ OK

General Information

Extended Product Type:	S201-K16
Product ID:	2CDS251001R0467
EAN:	4016779496124
Catalog Description:	Miniature Circuit Breaker - S200 - 1 - K - 16 A
Long Description:	System pro M compact S200 miniature circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (B,C,D,K,Z), configurations (1P,1P+N,2P,3P,3P+N,4P), breaking capacities (up to 6 kA at 230/400 V AC) and rated currents (up to 63A). All MCBs of the product range S200 comply with IEC/EN 60898-1, IEC/EN 60947-2, UL1077 and CSA 22.2 No. 235, allowing the use for residential, commercial and industrial applications. Bottom-fitting auxiliary contact can be mounted on S200 to save 50% space.



Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Miniature Circuit Breakers MCBs

Accessories [Show accessory images](#)

Ordering

EAN:	4016779496124
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85362010

Dimensions

Product Net Width:	17.5 mm
Product Net Depth:	69 mm
Product Net Height:	88 mm
Product Net Weight:	0.125 kg

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	92 mm
Package Level 1 Length:	183 mm
Package Level 1 Height:	80 mm
Package Level 1 Gross Weight:	1.295 kg
Package Level 1 EAN:	4016779607186

Environmental

Ambient Air Temperature:	Operation -25 ... +55 °C Storage -40 ... +70 °C
Resistance to Shock acc. to IEC 60068-2-27:	25g / 2 shocks / 13 ms
Resistance to Vibrations acc. to IEC 60068-2-6:	5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In
Environmental Conditions:	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Technical

Standards:	IEC/EN 60898-1 IEC/EN 60947-2 UL 1077
Number of Poles:	1
Tripping Characteristic:	K
Rated Current (I _n):	16 A
Rated Operational Voltage:	acc. to IEC60898-1 230 / 400 V AC acc. to IEC60947-2 230 V AC
Power Loss:	2 W Per Pole 2 W
Rated Insulation Voltage (U _i):	acc. to IEC/EN 60664-1 440 V
Operational Voltage:	Maximum (incl. tolerance) 253 V AC Maximum (incl. tolerance) 72 V DC Minimum 12 V AC / 12 V DC
Rated Frequency (f):	50 Hz 60 Hz
Rated Short-Circuit Capacity (I _{cn}):	6 kA
Rated Ultimate Short-Circuit Breaking Capacity (I _{cu}):	10 kA
Rated Service Short-Circuit Breaking Capacity (I _{cs}):	7.5 kA
Energy Limiting Class:	3
Overvoltage Category:	III
Pollution Degree:	3
Rated Impulse Withstand Voltage (U _{imp}):	4 kV (6.2 kV @ sea level) kV (5.0 kV @ 2000 m) kV

Dielectric Test Voltage:	50 / 60 Hz, 1 min: 2 kV
Housing Material:	Insulation group II, RAL 7035
Actuator Type:	Insulation group II, black, sealable
Actuator Marking:	I / O
Contact Position Indication:	Red ON / Green OFF
Degree of Protection:	IP20
Remarks:	IP40 in enclosure with cover
Electrical Endurance:	20000 AC cycle
Mechanical Endurance:	20000 cycle
Terminal Type:	Screw Terminals
Screw Terminal Type:	Failsafe Bi-directional Cylinder-lift Terminal
Connecting Capacity:	Busbar 10 / 10 mm² Flexible with Ferrule 0.75 ... 25 mm² Flexible 0.75 ... 25 mm² Rigid 0.75 ... 35 mm² Stranded 0.75 ... 35 mm²
Tightening Torque:	2.8 N·m
Recommended Screw Driver:	Pozidriv 2
Mounting on DIN Rail:	TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715
Mounting Position:	Any

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	277 V AC
Connecting Capacity UL/CSA:	Busbar 18 ... 8 AWG Conductor 18 ... 4 AWG
Tightening Torque UL/CSA:	25 in·lb
Interrupting Rating acc. to UL1077:	6 kA

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	2CDK403001D0602
RoHS Information:	2CDK400003K0201

Classifications

eClass:	7.0 27141901
E-nummer:	2100698
ETIM 4.0:	EC000042 - Miniature circuit breaker (MCB)
ETIM 5.0:	EC000042 - Miniature circuit breaker (MCB)
Object Classification Code:	F

DOWNLOADS