

Sensor/Actuator cable - SAC-3P-M12MS/0,6-PUR/A-1L-Z - 1400769

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



The illustration shows the SPEEDCON version

Sensor/Actuator cable, PUR halogen-free, Black-gray RAL 7021, Plug straight M12, A-coded, on A valve plug, with 1 LED, connected with Z diode, Cable length: 0.6 m

Key commercial data

Packing unit	0
Minimum order quantity	1
GTIN	 4 046356 509510
Custom tariff number	85444290
Country of origin	POLAND

Technical data

General data

Rated current at 40°C	4 A
Rated voltage	24 V
Length of cable	0.6 m

General characteristics

Surge voltage category	III
Pollution degree	3
Degree of protection	IP65/67
Insertion/withdrawal cycles	≥ 100
Status display	1 LED
Protective circuit/component	Z diode

Conductor data

Cable type	PUR halogen-free black
Cable type (abbreviation)	PUR
Cable abbreviation	Li9Y11Y-HF
UL AWM Style	20549
Conductor cross section	3x 0.5 mm ²
AWG signal line	20

Sensor/Actuator cable - SAC-3P-M12MS/0,6-PUR/A-1L-Z - 1400769

Technical data

Conductor data

Conductor structure signal line	28x 0.15 mm
Core diameter including insulation	1.5 mm ±0.05 mm (signal line)
External cable diameter	4.5 mm ± 0.2 mm
Wire colors	Black 1, black 2, green/yellow
External sheath, color	Black-gray RAL 7021
Insulation resistance	min. 20 MΩ*km
Conductor resistance	39 Ω/km (at 20 °C)
Nominal voltage, conductor	≤ 300 V
Test voltage, conductor	≥ 1200 V
Overall twist	3 wires, twisted
Outer sheath, material	PUR
Material conductor insulation	PP
Conductor material	Bare Cu litz wires
Smallest bending radius, fixed installation	22.5 mm
Number of bending cycles	15000000
Bending radius	50 mm
Traversing path	0.9 m
Traversing rate	5 m/s
Acceleration	30 m/s²
Ambient temperature (operation)	-40 °C ... 80 °C (cable, fixed installation)
Ambient temperature (operation)	-20 °C ... 80 °C (cable, flexible installation)
Flame resistance	According to DIN VDE 0482
Flame resistance	According to DIN EN 50265-2-1
Halogen-free	in accordance with DIN VDE 0472 part 815
Other resistance	Largely oil-resistant
Other resistance	partly UV-resistant in accordance with DIN EN ISO 4892-2-A

Classifications

eclass

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801

etim

ETIM 3.0	EC001855
ETIM 4.0	EC001855

Sensor/Actuator cable - SAC-3P-M12MS/0,6-PUR/A-1L-Z - 1400769

Classifications

unspsc

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

Accessories

Accessories

Assembly


Screw - SAC-V-SCREW-M3-29 KNURL - 1403779



Fillister head screw with plastic knurl, M3 x 40


Drawings

Schematic diagram




Pin assignment M12 plug, 3-pos., valve connector

Schematic diagram




Valve connector pin assignment, type A

Cable cross section



PUR halogen-free black [PUR]


Dimensioned drawing



Valve plug, type A


Sensor/Actuator cable - SAC-3P-M12MS/0,6-PUR/A-1L-Z - 1400769

Dimensioned drawing




M12 x 1 male connector, straight

Circuit diagram



Contact assignment of M12 plug and valve connector

Dimensioned drawing



Valve connector, type A, side view