

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION

BELDEN
SENDING ALL THE RIGHT SIGNALS

7428W Multi-Conductor - 600V FCC Control Cables for Moderate Flexing



For more Information
please call

1-800-Belden1



General Description:

16 AWG stranded (26x30) bare copper conductors, PVC-Nylon insulation, unshielded, oil- and abrasion-resistant PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

| # Conductors | AWG | Stranding | Conductor Material |
|--------------|-----|-----------|--------------------|
| 17 | 16 | 26x30 | BC - Bare Copper |

Total Number of Conductors: 18

Ground Wire

Ground Wire (Y/N): Y

Ground Wire AWG: 16

Ground Wire Stranding: 26x30

Ground Wire Conductor Material: BC - Bare Copper

Ground Wire Insulation Material: PVC/Nylon - Polyvinyl Chloride/Nylon

Insulation

Insulation Material:

| Insulation Material | Wall Thickness (in.) |
|--------------------------|----------------------|
| PVC - Polyvinyl Chloride | 0.015 |
| Nylon | 0.005 |

Insulation Color Code Chart:

| Color | Description |
|-------|-----------------------|
| Black | Individually Numbered |

Outer Shield

Outer Shield Material:

| Outer Shield Material |
|-----------------------|
| Unshielded |

Outer Jacket

Outer Jacket Material:

| Outer Jacket Material | Nom. Wall Thickness (in.) |
|-------------------------------|---------------------------|
| TPE - Thermoplastic Elastomer | 0.063 |

Overall Cable

Overall Nominal Diameter: 0.636 in.

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +90°C

Other Temperature Range: Flexing: -5°C To +90°C

UL Temperature Rating: 90°C (UL AWM Style 2587)

Bulk Cable Weight: 275 lbs/1000 ft.

Max. Recommended Pulling Tension: 630 lbs.

Min. Bend Radius (Continuous Flexing): 6.400 in.

Flex Cycle Rating: 1 Million Flexes

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: TC-ER, WTTC

CEC/C(UL) Specification: 600V Type CIC TC

AWM Specification: UL Style 2587 (600 V 90°C), UL Style 21486 (1000 V 90°C)

Detailed Specifications & Technical Data



ENGLISH MEASUREMENT VERSION

7428W Multi-Conductor - 600V FCC Control Cables for Moderate Flexing

| | |
|---------------------------------------|--------------|
| CSA Specification: | AWM I/II A/B |
| EU Directive 2011/65/EU (ROHS II): | Yes |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2002/95/EC (RoHS): | Yes |
| EU RoHS Compliance Date (mm/dd/yyyy): | 10/01/2005 |
| EU Directive 2002/96/EC (WEEE): | Yes |
| EU Directive 2003/11/EC (BFR): | Yes |
| EU REACH SVHC Present: | Yes |
| CA Prop 65 (CJ for Wire & Cable): | Yes |
| MII Order #39 (China RoHS): | Yes |

Flame Test

| | |
|-------------------|---|
| UL Flame Test: | UL1685 FT4/IEEE 1202 Vertical Tray Flame Test |
| C(UL) Flame Test: | FT4 |
| IEEE Flame Test: | 1202 |

Suitability

| | |
|-----------------------|------------------|
| Suitability - Burial: | Yes |
| Sunlight Resistance: | Yes |
| Oil Resistance: | Yes - Oil Res II |
| Non-halogenated: | No |

Plenum/Non-Plenum

| | |
|---------------|----|
| Plenum (Y/N): | No |
|---------------|----|

Electrical Characteristics (Overall)

Nom. Conductor DC Resistance:

| |
|--------------------------|
| DCR @ 20°C (Ohm/1000 ft) |
| 4.000 |

Put Ups and Colors:

| Item # | Putup | Ship Weight | Color | Notes | Item Desc |
|---------------|----------|--------------|--------|-------|--------------------------|
| 7428W 0601000 | 1,000 FT | 288.000 LB | CHROME | C | 17 #16 + GRD PVC/NYL TPE |
| 7428W 060250 | 250 FT | 78.750 LB | CHROME | C | 17 #16 + GRD PVC/NYL TPE |
| 7428W 0605000 | 5,000 FT | 1,490.000 LB | CHROME | | 17 #16 + GRD PVC/NYL TPE |

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 10-02-2013

© 2017 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.