

FLEX STACK

MICRO BOARD STACKER

(1.27 mm) .050" PITCH • FW SERIES

4
Gbps



FW

Board Mates:

CLP, FLE

Cable Mates:

FFSD

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over 50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 $^{\circ}$ C to +125 $^{\circ}$ C

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max (02-30)

(0.15 mm) .006" max (31-50)*






*(.004" stencil solution may be available; contact ipg@samtec.com)

MATED HEIGHT

FW LEAD STYLE	CLP LEAD STYLE	MATED HEIGHT*
FW-XX-03-X-X-233-065	-02	(8.13 mm) .320"
FW-XX-03-X-X-303-065		(9.91 mm) .390"

*Processing conditions will affect mated height.

SURFACE MOUNT



-ES
= End Shroud
(-.075 post height only.
Mate only with CLP)
(5.46 mm) .215" to (15.49 mm) .610" stacker height only
9 pins/row min.

-EP
= End Shroud with Guide Post
(-.075 post height only.
Mate only with CLP)
(5.46 mm) .215" to (15.49 mm) .610" stacker height only
9 pins/row min.

-A
= Alignment Pin
(3 positions min.)
(5.46 mm) .215" to (15.75 mm) .620" stacker height only
(SMT only)

-P
= Pick & Place Pad
(5 positions min.)
(SMT only)

-TR
= Tape & Reel
(Max overall height = Post+Stacker Height+Pad+Alignment Pin = (17.78) .700")
(SMT only)

-FR
= Full Reel
Tape & Reel
(must order max. quantity per reel; contact Samtec for quantity breaks)
(SMT only)





ALSO AVAILABLE

Smaller stack heights

Notes:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

This Series is non-standard, non-returnable.



LEAD STYLE	TAIL (B)
-01	(1.14) .045
-02	(1.91) .075
-04	(2.29) .090

samtec.com?FW-SM or samtec.com?FW-TH

F-224 (Rev 06JAN25)

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.