



Wiha. Premium Tools
for Professionals.

Wiha PicoFinish. The Specialist for Precision Applications.



The soft material of the handle, together with the rotating cap, enables optimum and sensitive twisting.



The clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver.




The Wiha PicoFinish screwdrivers are predestined for high-precision work, predominantly with electro-technical and precision components.

The octagonal rapid-rotation zone at the front of the handle allows rapid twisting.

The extraordinarily easy-to-twist rotating cap permits the delicate turning of fine screws with just one hand.

PicoFinish Advantages:

- Special soft plastic material assures comfortable, delicate work
- Ideal for fine adjustments in electronic assembly work and precision applications, as well as for hobby use and model making
- Clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver
- Convex handle end allows the transmission of a controlled high torque to powerfully tighten or loosen the screw head
- Palm saving rotating cap with a large surface for the fingers makes incremental adjustment easy
- Wiha ChromeTop-finish on tip for a perfect fit every time





Wiha. Premium Tools
for Professionals.

Wiha PicoFinish. The Specialist for Precision Applications.

For Slotted & Phillips Screws.



260 P Pozidriv Screwdriver.

With rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.	Ø	mm	mm	mm	mm	mm	mm
00475 0	0.8	40	0.16	140	2.0	18	10
00476 7	1.0	40	0.18	140	2.0	18	10
00477 4	1.2	40	0.2	140	2.0	18	10
00478 1	1.5	40	0.25	140	2.0	18	10
00479 8	1.5	60	0.25	160	2.0	18	10
00480 4	1.8	40	0.3	140	2.0	18	10
00481 1	1.8	60	0.3	160	2.0	18	10
00482 8	2.0	40	0.4	140	2.0	18	10
00484 2	2.0	60	0.4	160	2.0	18	10
00485 9	2.0	100	0.4	200	2.0	18	10
00486 6	2.5	50	0.4	150	2.5	18	10
00487 3	2.5	75	0.4	175	2.5	18	10
00488 0	2.5	100	0.4	200	2.5	18	10
00490 3	3.0	50	0.5	150	3.0	18	10
00492 7	3.0	100	0.5	200	3.0	18	10
00493 4	3.0	150	0.5	250	3.0	18	10
00495 8	3.5	60	0.6	160	3.5	18	10
00497 2	4.0	60	0.8	160	4.0	18	10
00498 9	4.0	100	0.8	200	4.0	18	10
00499 6	4.0	150	0.8	250	4.0	18	10



261 P Phillips Screwdriver.

With rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.	Ø	mm	mm	mm	mm	mm	mm
00513 9	000	40	140	2.0	18	10	
00512 2	00	40	140	2.0	18	10	
00514 6	00	60	160	2.0	18	10	
00511 5	0	50	150	3.0	18	10	
00515 3	0	75	175	3.0	18	10	
00516 0	1	60	160	4.0	18	10	
00517 7	1	80	180	4.0	18	10	
00518 4	1	150	250	4.0	18	10	

For Pozidriv & TORX® Screws.



262 P Pozidriv Screwdriver.

With rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.	Ø	mm	mm	mm	mm	mm	mm
04461 9	0	50	150	3.0	18	10	
04462 6	1	60	160	4.0	18	10	



267 P TORX® Screwdriver.

With rotating cap and rapid-turning zone.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop finish on tip for a perfect fit every time.

Handle: Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision components.

Order-No.	Ø	mm	mm	mm	mm	mm	mm
25673 9	T1	40	140	2.5	18	10	
25674 6	T2	40	140	2.5	18	10	
20122 7	T3	40	140	2.5	18	10	
20123 4	T4	40	140	2.5	18	10	
00566 5	T5	40	140	2.5	18	10	
00567 2	T6	40	140	2.5	18	10	
00568 9	T7	40	140	2.5	18	10	
00569 6	T8	40	140	2.5	18	10	
00570 2	T9	50	150	3.0	18	10	
00571 9	T10	50	150	3.0	18	10	
00572 6	T15	60	160	3.5	18	10	
00573 3	T20	60	160	4.0	18	10	