


AOL1420
N-Channel Enhancement Mode Field Effect Transistor

General Description

The AOL1420 uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and low gate resistance. This device is ideally suited for use as a low side switch in CPU core power conversion. *Standard Product AOL1420 is Pb-free (meets ROHS & Sony 259 specifications). AOL1420L is a Green Product ordering option. AOL1420 and AOL1420L are electrically identical.*


Features

$V_{DS} (V) = 30V$
 $I_D = 85A (V_{GS} = 10V)$
 $R_{DS(ON)} < 3.7m\Omega (V_{GS} = 10V)$
 $R_{DS(ON)} < 5.5m\Omega (V_{GS} = 4.5V)$

Ultra SO-8™ Top View


Bottom tab
connected to
drain

**Fits SOIC8
footprint !**


Absolute Maximum Ratings $T_A=25^\circ C$ unless otherwise noted

Parameter	Symbol	Maximum	Units
Drain-Source Voltage	V_{DS}	30	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current ^{B,G}	I_D	85	A
$T_C=25^\circ C$		63	
$T_C=100^\circ C$	I_{DM}	150	
Pulsed Drain Current			
Continuous Drain Current ^G	I_{DSM}	18	A
$T_A=25^\circ C$		14	
$T_A=70^\circ C$			
Avalanche Current ^C	I_{AR}	30	A
Repetitive avalanche energy $L=0.1mH$ ^C	E_{AR}	112	mJ
Power Dissipation ^B	P_D	100	W
$T_C=25^\circ C$		50	
$T_C=100^\circ C$			
Power Dissipation ^A	P_{DSM}	2.1	W
$T_A=25^\circ C$		1.3	
$T_A=70^\circ C$			
Junction and Storage Temperature Range	T_J, T_{STG}	-55 to 175	$^\circ C$

Thermal Characteristics

Parameter	Symbol	Typ	Max	Units
Maximum Junction-to-Ambient ^A	$R_{\theta JA}$	19.6	25	$^\circ C/W$
$t \leq 10s$				
Maximum Junction-to-Ambient ^A		50	60	$^\circ C/W$
Steady-State				
Maximum Junction-to-Case ^C	$R_{\theta JC}$	0.9	1.5	$^\circ C/W$
Steady-State				

Electrical Characteristics (T_j=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Units
STATIC PARAMETERS						
BV _{DSS}	Drain-Source Breakdown Voltage	I _D =250μA, V _{GS} =0V	30			V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =24V, V _{GS} =0V T _j =55°C			1 5	μA
I _{GSS}	Gate-Body leakage current	V _{DS} =0V, V _{GS} = ±20V			100	nA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250μA	1	1.8	3	V
I _{D(ON)}	On state drain current	V _{GS} =10V, V _{DS} =5V	85			A
R _{DS(ON)}	Static Drain-Source On-Resistance	V _{GS} =10V, I _D =20A T _j =125°C		2.9 4.4	3.7 5.5	mΩ
		V _{GS} =4.5V, I _D =20A		4.4	5.5	mΩ
g _{FS}	Forward Transconductance	V _{DS} =5V, I _D =20A		106		S
V _{SD}	Diode Forward Voltage	I _S =1A, V _{GS} =0V		0.72	1	V
I _S	Maximum Body-Diode Continuous Current				85	A
DYNAMIC PARAMETERS						
C _{iss}	Input Capacitance	V _{GS} =0V, V _{DS} =15V, f=1MHz		3200	3840	pF
C _{oss}	Output Capacitance			590		pF
C _{rss}	Reverse Transfer Capacitance			414		pF
R _g	Gate resistance	V _{GS} =0V, V _{DS} =0V, f=1MHz		0.54	0.7	Ω
SWITCHING PARAMETERS						
Q _g (10V)	Total Gate Charge	V _{GS} =4.5V, V _{DS} =15V, I _D =20A		63	76	nC
Q _g (4.5V)	Total Gate Charge			33	40	nC
Q _{gs}	Gate Source Charge			8.6		nC
Q _{gd}	Gate Drain Charge			17.6		nC
t _{D(on)}	Turn-On DelayTime	V _{GS} =10V, V _{DS} =15V, R _L =0.75Ω, R _{GEN} =3Ω		12		ns
t _r	Turn-On Rise Time			15.5		ns
t _{D(off)}	Turn-Off DelayTime			40		ns
t _f	Turn-Off Fall Time			14		ns
t _{rr}	Body Diode Reverse Recovery Time	I _F =20A, dI/dt=100A/μs		34	41	ns
Q _{rr}	Body Diode Reverse Recovery Charge	I _F =20A, dI/dt=100A/μs		30		nC

A: The value of R_{qJA} is measured with the device in a still air environment with T_A=25°C.

B: The power dissipation PD is based on T_J(MAX)=175°C, using junction-to-case thermal resistance, and is more useful in setting the upper dissipation limit for cases where additional heatsinking is used.

C: Repetitive rating, pulse width limited by junction temperature T_J(MAX)=175°C.

D: The R_{qJA} is the sum of the thermal impedance from junction to case R_{qJC} and case to ambient.

E: The static characteristics in Figures 1 to 6 are obtained using <300 ms pulses, duty cycle 0.5% max.

F: These curves are based on the junction-to-case thermal impedance which is measured with the device mounted to a large heatsink, assuming a maximum junction temperature of T_J(MAX)=175°C.

G: The maximum current rating is limited by bond-wires.

Rev0: August 2005

THIS PRODUCT HAS BEEN DESIGNED AND QUALIFIED FOR THE CONSUMER MARKET. APPLICATIONS OR USES AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS ARE NOT AUTHORIZED. AOS DOES NOT ASSUME ANY LIABILITY ARISING OUT OF SUCH APPLICATIONS OR USES OF ITS PRODUCTS. AOS RESERVES THE RIGHT TO IMPROVE PRODUCT DESIGN, FUNCTIONS AND RELIABILITY WITHOUT NOTICE.

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Fig 1: On-Region Characteristics




Figure 2: Transfer Characteristics




Figure 3: On-Resistance vs. Drain Current and Gate Voltage




Figure 4: On-Resistance vs. Junction Temperature




Figure 5: On-Resistance vs. Gate-Source Voltage




Figure 6: Body-Diode Characteristics

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Figure 7: Gate-Charge Characteristics




Figure 8: Capacitance Characteristics




Figure 9: Maximum Forward Biased Safe Operating Area (Note F)




Figure 10: Single Pulse Power Rating Junction-to-Ambient (Note F)




Figure 11: Normalized Maximum Transient Thermal Impedance (Note F)

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS




Figure 12: Single Pulse Avalanche capability




Figure 13: Power De-rating (Note B)




Figure 14: Current De-rating (Note B)




Figure 15: Single Pulse Power Rating Junction-to-Ambient (Note H)




Figure 16: Normalized Maximum Transient Thermal Impedance (Note H)