

A photograph showing three microswitches. Two are black with black levers, and one is white with a white lever. They are arranged on a light-colored surface.

Specifications

- * Due to ongoing technological advances, consult factory for certification specifics.

Technical drawing of the 1000 Series Plug showing two views: a front view (left) and a side view (right). Dimensions are provided in inches [millimeters].

Front View Dimensions:

- Top section height: .687 [17.44]
- Threaded section height: .280 [7.11]
- Base section height: .687 [17.44]
- Overall height: 1.000 [25.40]
- Base width: .375 [9.52]

Side View Dimensions:

- Overall width: .588 [14.93]

Keyway Details:

- Keyway width: .072 [1.82]
- Keyway depth: .038 [.965] DP

The image displays three technical drawings of shaft-hub assembly configurations, each with dimensions in inches and millimeters in brackets.

- MOUNTING HOLE:** Shows a shaft with a diameter of .500 [12.70] DIA. The shaft is inserted into a hub with a hole that is slightly larger than the shaft diameter.
- WITH KEYWAY:** Shows a shaft with a diameter of .500 [12.70] DIA. The shaft has a keyway with a width of .038 [9.65]. The hub has a keyway with a width of .062 [1.57]. The shaft is inserted into the hub, and the keyway dimensions are shown.
- WITH LOCKING RING:** Shows a shaft with a diameter of .500 [12.70] DIA. The shaft is inserted into a hub with a hole that is slightly larger than the shaft diameter. A locking ring is used to secure the assembly. The locking ring has an outer diameter of .376 [9.55] and an inner diameter of .125 [3.17] DIA. The shaft diameter is .500 [12.70] DIA.

NOTES:
Shading indicates standard configurations.
Available with neoprene seal. Consult factory.
1 Custom colors are available. Consult factory.