


LOC	DIST	REVISIONS							
A1	-	ÄNDERUNGEN							
		P	LTR	DESCRIPTION BESCHREIBUNG			DATE	DWN	APVD
PROJEKT NR.:			A1	NEW-DRAWN			05.11.08	GW	ST

ITEM	DESCRIPTION	MATERIAL	FINISH/COLOUR	QUANTITY / ITEM			
				-1	-2	-3	-4
1	CONNECTOR HOUSING	GF NYLON	BLACK	1	1	1	1
2	SOCKET CONTACT	BRASS	0.15µm GOLD OVER NICKEL	3	4	5	8
3	CONNECTOR BODY	ZINC DIE CAST	2.5µm NICKEL PLATED	1	1	1	1
4	'O' RING	VITON	GREEN	1	1	1	1
5	'O' RING	EPDM	BLACK	1	1	1	1
6	SCREW NUT	ZINC DIE CAST	2.5µm NICKEL PLATED	1	1	1	1

NOTES:


- | | | |
|---------------------|------------------------|--|
| 1. ELECTRICAL DATA: | CONTACT RESISTANCE: | 10 mOhm MAX |
| | INSULATION RESISTANCE: | 100 MOhm MIN at 500VDC |
| | CURRENT RATING: | 5 AMPS (FOR 3, 4 AND 5 POSITIONS) AND 2 AMPS (FOR 8 POSITION ONLY) |
| | BREAKDOWN VOLTAGE: | 500 VAC MIN PER MINUTE |
| 2. ENVIRONMENTAL: | OPERATING TEMPERATURE: | -25°C TO +90°C |
| | SEALING REQUIREMENTS: | IP68 |



0-1


PIN ASSIGNMENTS

FRONT VIEW




0-2

PIN ASSIGNMENTS
FRONT VIEW



0-3


PIN ASSIGNMENTS
FRONT VIEW




0-4

PIN ASSIGNMENTS


FRONT VIEW




RECOMMENDED PANEL CUT-OUT
(MAX PANEL THICKNESS 4.5mm)




RECOMMENDED PANEL CUT-OUT
(MAX PANEL THICKNESS 4.5mm)




RECOMMENDED PANEL CUT-OUT
(MAX PANEL THICKNESS 4.5mm)




RECOMMENDED PANEL CUT-OUT
(MAX PANEL THICKNESS 4.5mm)




RECOMMENDED PCB LAYOUT




RECOMMENDED PCB LAYOUT



RECOMMENDED PCB LAYOUT



RECOMMENDED PCB LAYOUT



M12 METAL FEMALE PANEL MOUNT CONNECTOR, PCB, STRAIGHT, FRONT (HEXAGONAL) MOUNTING	8	0-4
M12 METAL FEMALE PANEL MOUNT CONNECTOR, PCB, STRAIGHT, FRONT (HEXAGONAL) MOUNTING	5	0-3
M12 METAL FEMALE PANEL MOUNT CONNECTOR, PCB, STRAIGHT, FRONT (HEXAGONAL) MOUNTING	4	0-2
M12 METAL FEMALE PANEL MOUNT CONNECTOR, PCB, STRAIGHT, FRONT (HEXAGONAL) MOUNTING	3	0-1
DESCRIPTION	NO. OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESER ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. ÄNDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, SIND VORZUHALTEN. DEN JEWEILS LETZTGÜLTIGEN ÄNDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE.		DWN G.WROBLEWSKI		05.11.08		HTS Elektrotechnik 53819 Neunkirchen, Germany	
DIMENSIONS: DIMENSIONEN: -		TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN n. ISO 8015 n. ISO 2768 - mH - E n. DIN 16901 - 140		CHK T.SCHNURPFEL		05.11.08	
		APVD T.SCHNURPFEL		ZAD		NAME M12,METAL-FEMALE-PANEL-MOUNT CONNECTOR	
		PRODUCT SPEC PRODUKTSPEZ 108-3641					
		APPLICATION SPEC 2713					
		ANGLES / WINKEL # -					
MATERIAL		FINISH / OBERFLÄCHE / FARBE -		SIZE A2		CAGE CODE 00779	
		WEIGHT GEWICHT -		DRAWING NO ZEICHNUNGS-NR. C=1991135		RESTRICTED TO NUR FUER -	
		-		/KUNDENZEICHNUNG		MASSSTAB NTS	
		-		BLATT 1		OF 1	
		-		REV A1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1991135-2](#)