




	10	9	8	7	6	5	4	3	2	1	
F					CIRCUIT SIZE	PLATING TYPE A	PLATING TYPE E	PLATING TYPE F	PLATING TYPE G		
					PART NO.	PART NO.	PART NO.	PART NO.	PART NO.		
					1 X 1	90120-0121	90120-0761	90120-0921	90120-1081		
					1 X 2	↑ -0122	↑ -0762	↑ -0922	↑ -1082		
					1 X 3	-0123	-0763	-0923	-1083		
					1 X 4	-0124	-0764	-0924	-1084		
					1 X 5	-0125	-0765	-0925	-1085		
					1 X 6	-0126	-0766	-0926	-1086		
					1 X 7	-0127	-0767	-0927	-1087		
					1 X 8	-0128	-0768	-0928	-1088		
					1 X 9	-0129	-0769	-0929	-1089		
					1 X 10	-0130	-0770	-0930	-1090		
					1 X 11	-0131	-0771	-0931	-1091		
					1 X 12	-0132	-0772	-0932	-1092		
					1 X 13	-0133	-0773	-0933	-1093		
					1 X 14	-0134	-0774	-0934	-1094		
					1 X 15	-0135	-0775	-0935	-1095		
					1 X 16	-0136	-0776	-0936	-1096		
					1 X 17	-0137	-0777	-0937	-1097		
					1 X 18	-0138	-0778	-0938	-1098		
					1 X 19	-0139	-0779	-0939	-1099		
					1 X 20	-0140	-0780	-0940	-1100		
					1 X 21	-0141	-0781	-0941	-1101		
					1 X 22	-0142	-0782	-0942	-1102		
					1 X 23	-0143	-0783	-0943	-1103		
					1 X 24	-0144	-0784	-0944	-1104		
					1 X 25	-0145	-0785	-0945	-1105		
					1 X 26	-0146	-0786	-0946	-1106		
					1 X 27	-0147	-0787	-0947	-1107		
					1 X 28	-0148	-0788	-0948	-1108		
					1 X 29	-0149	-0789	-0949	-1109		
					1 X 30	-0150	-0790	-0950	-1110		
					1 X 31	-0151	-0791	-0951	-1111		
					1 X 32	-0152	-0792	-0952	-1112		
					1 X 33	-0153	-0793	-0953	-1113		
					1 X 34	-0154	-0794	-0954	-1114		
					1 X 35	-0155	-0795	-0955	-1115		
					1 X 36	-0156	-0796	-0956	-1116		
					1 X 37	-0157	-0797	-0957	-1117		
					1 X 38	-0158	-0798	-0958	-1118		
					1 X 39	↓ -0159	↓ -0799	↓ -0959	↓ -1119		
					1 X 40	90120-0160	90120-0800	90120-0960	90120-1120		
E					PLATING OPTIONS	PLATING DESCRIPTION					F
					A	3.00µm MIN TIN OVER 1.27MIN NICKEL OVERALL					D
					E	0.38µm MIN GOLD IN SELECTED AREA (2 SIDES) AND 3.00µm MIN TIN IN SELECTED AREA AND 1.30µm MIN NICKEL OVERALL					
					F	0.76µm MIN GOLD IN SELECTED AREA (2 SIDES) AND 3.00µm MIN TIN IN SELECTED AREA AND 1.30µm MIN NICKEL OVERALL					C
					G	0.05-0.10µm GOLD FLASH IN SELECTED AREA (2 SIDES) AND 3.00µm MIN TIN IN SELECTED AREA AND 1.30µm MIN NICKEL OVERALL					
B											A