


EPC2016C – Enhancement Mode Power Transistor

 $V_{DS}, 100\text{ V}$

NEW PRODUCT

 $R_{DS(on)}, 16\text{ m}\Omega$
 $I_D, 18\text{ A}$


RoHS

Halogen-Free

Gallium nitride is grown on silicon wafers and processed using standard CMOS equipment leveraging the infrastructure that has been developed over the last 55 years. GaN's exceptionally high electron mobility and low temperature coefficient allows very low $R_{DS(on)}$, while its lateral device structure and majority carrier diode provide exceptionally low Q_G and zero Q_{RR} . The end result is a device that can handle tasks where very high switching frequency, and low on-time are beneficial as well as those where on-state losses dominate.



EPC2016C eGaN® FETs are supplied only in passivated die form with solder bars

Applications

- High Speed DC-DC conversion
- Class-D Audio
- High Frequency Hard-Switching and Soft-Switching Circuits

Benefits

- Ultra High Efficiency
- Ultra Low $R_{DS(on)}$
- Ultra low Q_G
- Ultra small footprint

Maximum Ratings			
V_{DS}	Drain-to-Source Voltage (Continuous)	100	V
	Drain-to-Source Voltage (up to 10,000 5ms pulses at 150° C)	120	V
I_D	Continuous ($T_A = 25^\circ\text{C}, \theta_{JA} = 13.4$)	18	A
	Pulsed (25° C, $T_{\text{pulse}} = 300\text{ }\mu\text{s}$)	75	
V_{GS}	Gate-to-Source Voltage	6	V
	Gate-to-Source Voltage	-4	
T_J	Operating Temperature	-40 to 150	°C
T_{STG}	Storage Temperature	-40 to 150	

Static Characteristics (T _J = 25°C unless otherwise stated)						
PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
BV _{DSS}	Drain-to-Source Voltage	V _{GS} = 0 V, I _D = 300 μA	100			V
I _{DSS}	Drain Source Leakage	V _{GS} = 0 V, V _{DS} = 80 V		25	150	μA
I _{GSS}	Gate-Source Forward Leakage	V _{GS} = 5 V		0.5	3	mA
	Gate-Source Reverse Leakage	V _{GS} = -4 V		0.25	0.15	
V _{GS(th)}	Gate Threshold Voltage	V _{GS} = V _{GSr} I _D = 3 mA	0.8	1.4	2.5	V
R _{DS(on)}	Drain-Source On Resistance	V _{GS} = 5 V, I _D = 11 A		12	16	mΩ
V _{SD}	Source-Drain Forward Voltage	I _S = 0.5 A, V _{GS} = 0 V		1.8		V

All measurements were done with substrate shorted to source.

Thermal Characteristics			
		TYP	
$R_{\theta JC}$	Thermal Resistance, Junction to Case	2	°C/W
$R_{\theta JB}$	Thermal Resistance, Junction to Board	4	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1)	69	°C/W

Note 1: $R_{\theta JA}$ is determined with the device mounted on one square inch of copper pad, single layer 2 oz copper on FR4 board.
See http://epc-co.com/epc/documents/product-training/Appnote_Thermal_Performance_of_eGaN_FETs.pdf for details.

Dynamic Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise stated)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
C_{ISS}	Input Capacitance	$V_{GS} = 0\text{ V}, V_{DS} = 50\text{ V}$		360	420	pF
C_{OSS}	Output Capacitance			210	310	
C_{RSS}	Reverse Transfer Capacitance			3.2	4.8	
R_G	Gate Resistance			0.4		Ω
Q_G	Total Gate Charge	$V_{DS} = 50\text{ V}, I_D = 11\text{ A}$		3.4	4.5	nC
Q_{GS}	Gate-to-Source Charge			1.1		
Q_{GD}	Gate-to-Drain Charge			0.55	1	
$Q_{G(TH)}$	Gate Charge at Threshold			0.7		
Q_{OSS}	Output Charge	$V_{GS} = 0\text{ V}, V_{DS} = 50\text{ V}$		16	24	
Q_{RR}	Source-Drain Recovery Charge			0		

All measurements were done with substrate shorted to source.


Figure 1: Typical Output Characteristics at 25°C 

Figure 2: Transfer Characteristics




Figure 3: $R_{DS(on)}$ vs. V_{GS} for Various CurrentsFigure 4: $R_{DS(on)}$ vs. V_{GS} for Various Temperatures

Figure 5a: Capacitance (Linear Scale)




Figure 5b: Capacitance (Log Scale)




Figure 6: Gate Charge




Figure 7: Reverse Drain-Source Characteristics




Figure 8: Normalized On Resistance vs. Temperature





Figure 9: Normalized Threshold Voltage vs. Temperature



All measurements were done with substrate shorted to source.

Figure 10: Gate Current




Figure 11: Transient Thermal Response Curves






Figure 12: Safe Operating Area



TAPE AND REEL CONFIGURATION

4mm pitch, 8mm wide tape on 7" reel




Dimension (mm)	EPC2016C (note 1)		
	target	min	max
a	8.00	7.90	8.30
b	1.75	1.65	1.85
c (see note)	3.50	3.45	3.55
d	4.00	3.90	4.10
e	4.00	3.90	4.10
f (see note)	2.00	1.95	2.05
g	1.5	1.5	1.6

Die is placed into pocket
solder bar side down
(face side down)

Note 1: MSL1 (moisture sensitivity level 1) classified according to IPC/JEDEC industry standard.
Note 2: Pocket position is relative to the sprocket hole measured as true position of the pocket, not the pocket hole.


DIE MARKINGS



Part Number	Laser Markings		
	Part # Marking Line 1	Lot_Date Code Marking line 2	Lot_Date Code Marking Line 3
EPC2016C	2016	YYYY	ZZZZ


DIE OUTLINE

Solder Bar View




DIM	MICROMETERS		
	MIN	Nominal	MAX
A	2076	2106	2136
B	1602	1632	1662
c	1379	1382	1385
d	577	580	583
e	235	250	265
f	195	200	205
g	400	400	400

Side View

**RECOMMENDED
LAND PATTERN**(units in μm)

The land pattern is solder mask defined.



Pad no. 1 is Gate;

Pads no. 3, 5 are Drain;

Pads no. 4, 6 are Source;

Pad no. 2 is Substrate.

Efficient Power Conversion Corporation (EPC) reserves the right to make changes without further notice to any products herein to improve reliability, function or design. EPC does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

eGaN® is a registered trademark of Efficient Power Conversion Corporation.

U.S. Patents 8,350,294; 8,404,508; 8,431,960; 8,436,398; 8,785,974; 8,890,168; 8,969,918; 8,853,749; 8,823,012

Information subject to
change without notice.
Revised September, 2015