

ADAPTERS, BETWEEN-SERIES

7/16 - DIN / Type N , DC - 7.5 GHz

SPECIFICATIONS:

Models: 5704, 5705, 5706, 5707

RoHS
Compliant

AEROFLEX
A passion for performance.

Electrical:


Frequency Range _____ DC – 7.5 GHz
VSWR _____ 1.35:1 Max.
Impedance _____ 50 Ohms
Operating Temp. Range _____ -65°C to +125°C

Mechanical:

Type N Connectors _____ Passivated Stainless Steel
Mates with MIL-STD-348
7/16 DIN Connectors _____ Silver or White Bronze
Mates with DIN 47 223 _____ Plated Brass
Conductors _____ Silver or White Bronze
_____ Plated Beryllium Copper


Model Number: **5707**

7/16 – DIN Male / Type N Male




Model Number: **5706**

7/16 – DIN Male / Type N Female




Model Number: **5705**

7/16 DIN Female / Type N Male



Model Number: **5704**

7/16 DIN Female / Type N Female



Note: Dimensions in Brackets are Expressed in Millimeters and are for Reference Only.

Design specifications are subject to change without notice.

Contact factory for technical specifications before purchasing or use.

5707: REV F

AEROFLEX
INMET

Aeroflex / Inmet, Inc. • 300 Dino Drive, Ann Arbor, MI 48103 • U.S.A.
888-244-6638 or 734-426-5553 • FAX: 734-426-5557
www.aeroflex.com/inmet • inmet@aeroflex.com