

<p>0496</p> <p>0496-0-15-XX-23-XX-10-0 Press-fit in 2,69 mounting hole</p>	<p>0368</p> <p>0368-0-33-XX-13-XX-10-0 #16A Crimp Barrel</p>	<p>8067</p> <p>8067-0-19-XX-13-XX-10-0 Wire Termination</p>	<p>1105</p> <p>1105-0-15-XX-13-XX-04-0 Press-fit in 2,03 mounting hole</p>
--	--	---	--

<p>8730</p> <p>8730-0-19-XX-23-XX-10-0 Wire Termination</p>	<p>3667</p> <p>3667-0-19-XX-23-XX-10-0 Wire Termination</p>	<p>9372</p> <p>9372-0-15-XX-23-XX-10-0 Solder mount in 2,59 min. mounting hole</p>	<p>4582</p> <p>4582-0-15-XX-23-XX-10-0 Square press-fit in 1,02 plated thru hole</p>
---	---	--	--

<p>5834</p> <p>5834-0-15-XX-23-XX-10-0 Press-fit in 2,72 mounting hole</p>	<p>9401</p> <p>9401-0-15-XX-23-XX-10-0 Solder mount in 2,59 min. mounting hole Also available on 24mm wide carrier tape: 1,100 parts per 330mm reel. Order as: 9401-0-57-XX-23-XX-10-0</p>	<p>9801</p> <p>9801-0-15-XX-23-XX-10-0 Solder mount in 2,59 min. mounting hole Also available on 16mm wide carrier tape: 1,200 parts per 330mm reel. Order as: 9801-0-57-XX-23-XX-10-0</p>	<p>8829</p> <p>8829-0-15-XX-23-XX-10-0 Solder mount in 2,59 min. mounting hole</p>
--	--	--	--

<p>SPECIFICATIONS</p> <p>SHELL MATERIAL: Brass Alloy 360, 1/2 Hard</p> <p>CONTACT MATERIAL: Beryllium Copper Alloy 172, HT</p> <p>DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±0,13 DIAMETERS: ±0,05 ANGLES: ± 2°</p>	<p>ORDER CODE: XXXX - X - XX - XX - X3 - XX - XX - 0</p> <p>BASIC PART # →</p> <p>SPECIFY SHELL FINISH:</p> <p>01 5,08µm TIN/LEAD OVER NICKEL</p> <p>80 5,08µm TIN OVER NICKEL ◊</p> <p>15 0,25µm GOLD OVER NICKEL ◊</p> <p>SPECIFY CONTACT FINISH:</p> <p>01 5,08µm TIN/LEAD OVER NICKEL</p> <p>80 5,08µm TIN OVER NICKEL ◊</p> <p>27 30µm GOLD OVER NICKEL ◊</p> <p align="center">SELECT CONTACT #13 or #23 CONTACT (DATA ON PAGES 224 & 225)</p>
---	---

