







Polzahl No. of pos.	A ± 0.2	B ± 0.1	C ± 0.1	D ± 0.1	Art.-Nr. Part-No
13	45.6	12x2.5=30	12x2.5=30	40	101A10079X
21	65.6	20x2.5=50	20x2.5=50	60	101A10099X
31	90.6	30x2.5=75	30x2.5=75	85	101A10119X

NOTES:

1. INSULATOR: PC GF UL 94 V-1, GREY
2. CONTACTS: COPPER ALLOY
PLATING: GOLD OVER NICKEL
50 MATING CYCLES

3. CONNECTOR IS PART MARKED: PART-NO CONEC ABC

P.C.B. HOLE DRILLINGS



Directive 2002/95/EC RoHS compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
				dim. in mm		
				2006	date	name
				drawn	15.11	Schwenkler
				appd.	16.11	Lehmenkühler
				norm	DIN 4 1617	
1 x c	Ä4688	15.03.2013	E.Mick.	d-old		
3 x b	Ä3087	21.08.2008	Sonne			
a	Origin					
rev.	description	date	name			



scale:		2:1	
material:		SEE NOTES	
title:			
MALE CONNECTOR (b) 13pos.-31pos. / 2.5mm with angled solder pins			
dwg no:		AutoCAD 2006	DIN-A
10K1A014		3	
		sh: 1/1	
part no:		SFF TABLE (b)	