

Common-mode chokes, ring core 4.7 ... 50 mH, 100 ... 600 mA, 60 °C

Series/Type: B82792C0

Date: April 2008

© EPCOS AG 2015. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



B82792C0

### Common-mode chokes, ring core

**SMD** 

Rated voltage 42 V AC/80 V DC Rated inductance 4.7 mH to 50 mH Rated current 100 mA to 600 mA

#### Construction

- Current-compensated ring core double choke
- Ferrite core
- LCP case (UL 94 V-0)
- Silicone potting
- Bifilar winding

#### **Features**

- Suitable for reflow soldering
- RoHS-compatible

#### **Function**

Suppression of asymmetrical interference coupled in on lines, whereas data signals up to some MHz can pass unaffectedly.

### **Applications**

- Telecom interfaces
- ISDN systems

#### **Terminals**

- Base material CuSn6
- Layer composition Ni, Sn
- Hot-dipped

#### Marking

- Marking on component:
  Manufacturer, ordering code, inductance,
  date of manufacture (YYWWD)
- Minimum data on reel:
  Manufacturer, ordering code, L value and tolerance,
  quantity, date of packing

### Delivery mode and packing unit


- 24-mm blister tape, wound on 330-mm Ø reel
- Packing unit: 500 pcs./reel

B82792C0


### Common-mode chokes, ring core


### **SMD**

### Dimensional drawing and pin configuration










1) Soldering area

IND0164-H-E


Dimensions in mm

### Taping and packing

#### Blister tape



### Reel



Dimensions in mm



B82792C0

### Common-mode chokes, ring core

### **SMD**

### Technical data and measuring conditions

42 V AC (50/60 Hz) / 80 V DC			
60 °C			
Referred to 50 Hz and rated temperature			
Measured with Agilent 4284A at 10 kHz, 50 mV, 20 °C Inductance is specified per winding.			
−30%/+50% at 20 °C			
< 10% at DC magnetic bias with I <sub>R</sub> , 20 °C			
Measured with Agilent 4284A at 10 kHz, 50 mV, 20 °C, typical values			
Measured at 20 °C, typical values, specified per winding			
Sn96.5Ag3.0Cu0.5: (245 $\pm$ 5) °C, (3 $\pm$ 0.3) s Wetting of soldering area $\geq$ 95% (to IEC 60068-2-58)			
(260 ±5) °C, (10 ±1) s (to IEC 60068-2-58)			
40/125/56 (to IEC 60068-1)			
–25 °C +40 °C, ≤75% RH			
Approx. 1.3 g			

### **Characteristics and ordering codes**

$\overline{L_R}$	L <sub>stray,typ</sub>	I <sub>R</sub>	R <sub>typ</sub>	V <sub>test</sub>	Ordering code	
mH	nH	mA	m $Ω$	V DC, 2 s		
4.7	240	600	400	750	B82792C0475N365	
6.8	300	600	500	750	B82792C0685N365	
10	350	500	1100	750	B82792C0106N365	
22	700	200	1600	750	B82792C0226N365	
33	850	100	2000	750	B82792C0336N365	
50	1100	100	2600	750	B82792C0506N365	



### Common-mode chokes, ring core


### **SMD**

**Insertion loss**  $\alpha$  (typical values at  $|Z| = 50 \Omega$ , 20 °C)


asymmetrical, all branches in parallel (common mode)

- - - - - - symmetrical (differential mode)


$$L_R = 4.7 \text{ mH}$$




$$L_R = 6.8 \text{ mH}$$



$$L_R = 10 \text{ mH}$$



 $L_R = 22 \text{ mH}$ 



### Common-mode chokes, ring core


### **SMD**

**Insertion loss**  $\alpha$  (typical values at  $|Z| = 50 \Omega$ , 20 °C)


asymmetrical, all branches in parallel (common mode)

- - - - - - symmetrical (differential mode)


$$L_R = 33 \text{ mH}$$



$$L_R = 50 \text{ mH}$$



# Current derating I<sub>op</sub>/I<sub>R</sub> versus ambient temperature






B82792C0

### Common-mode chokes, ring core

**SMD** 

### Recommended reflow soldering curve

Pb-free solder material (based on JEDEC J-STD 020C)



T <sub>1</sub>	T <sub>2</sub>	T <sub>3</sub>	T <sub>4</sub>	t <sub>1</sub>	t <sub>2</sub>	t <sub>3</sub>
°C	°C	°C	°C	S	S	S
150	200	217	250	< 110	< 90	< 30 @ T <sub>4</sub> –5 °C

Time from 25 °C to T<sub>4</sub>: max 300 s Maximal numbers of reflow cycles: 3



#### **Cautions and warnings**

- Please note the recommendations in our Inductors data book (latest edition) and in the data
  - Particular attention should be paid to the derating curves given there.
  - The soldering conditions should also be observed. Temperatures quoted in relation to wave soldering refer to the pin, not the housing.
- If the components are to be washed varnished it is necessary to check whether the washing varnish agent that is used has a negative effect on the wire insulation, any plastics that are used, or on glued joints. In particular, it is possible for washing varnish agent residues to have a negative effect in the long-term on wire insulation.
- The following points must be observed if the components are potted in customer applications:
  - Many potting materials shrink as they harden. They therefore exert a pressure on the plastic housing or core. This pressure can have a deleterious effect on electrical properties, and in extreme cases can damage the core or plastic housing mechanically.
  - It is necessary to check whether the potting material used attacks or destroys the wire insulation, plastics or glue.
  - The effect of the potting material can change the high-frequency behaviour of the components.
- Ferrites are sensitive to direct impact. This can cause the core material to flake, or lead to breakage of the core.
- Even for customer-specific products, conclusive validation of the component in the circuit can only be carried out by the customer.



#### Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application.
  - As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order.
  - We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available.
  - The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, BAOKE, Alu-X, CeraDiode, CSMP, CSSP, CTVS, DSSP, MiniBlue, MKK, MLSC, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SIMID, SineFormer, SIOV, SIP5D, SIP5K, ThermoFuse, WindCap are trademarks registered or pending in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.