


SPECIAL T/FRIDGE

Incandescent lamps, tubular shape, for fridge lighting




Areas of application


- Domestic refrigerators
- Sewing machines




Product family datasheet




Product line drawing



Product line drawing




Product line drawing



E14
IEC 7004-23

Base



E 14

Base

Product family datasheet

Technical data

Product description	Nominal wattage	Nominal voltage	Luminous flux	Base (standard designation)	Diameter	Length
SPC.T CL 15 W 230 V E14	15 W	230 V	100 lm	E14	17.0 mm	54.0 mm
SPC.T FR 10 W 225 V E14	10 W	230 V	30 lm	E14	25.0 mm	57.0 mm
SPC.T CL 15 W 230 V E14	15 W	230 V	110 lm	E14	26.0 mm	57.0 mm
SPC.T CL 25 W 230 V E14	25 W	230 V	190 lm	E14	26.0 mm	57.0 mm
SPC.T FR 15 W 230 V E14	15 W	230 V	110 lm	E14	26.0 mm	57.0 mm
SPC.T FR 25 W 230 V E14	25 W	230 V	190 lm	E14	26.0 mm	57.0 mm

Product description	Rated luminous flux	Overall length	Nominal lamp life time	Dimmable	Starting time	ILCOS
SPC.T CL 15 W 230 V E14	N/A lm	54.0 mm	1500 h	Yes	0.0 s	IBT/C-15-230-E14-17
SPC.T FR 10 W 225 V E14	30 lm	57.0 mm	1000 h	Yes	0.0 s	IBT/F-10-230-E14-25
SPC.T CL 15 W 230 V E14	N/A lm	57.0 mm	1000 h	Yes	0.0 s	IBT/C-15-230-E14-26
SPC.T CL 25 W 230 V E14	N/A lm	57.0 mm	1000 h	Yes	0.0 s	IBT/C-25-230-E14-26
SPC.T FR 15 W 230 V E14	N/A lm	57.0 mm	1000 h	Yes	0.0 s	IBT/F-15-230-E14-26
SPC.T FR 25 W 230 V E14	N/A lm	57.0 mm	1000 h	Yes	0.0 s	IBT/F-25-230-E14-26

Product description	Color rendering index Ra	Warm-up time (60 %)	Lamp mercury content	Mercury-free	Nominal luminous flux	EEI – Energy Label
SPC.T CL 15 W 230 V E14	100	0.00 s	N/A mg	Yes		
SPC.T FR 10 W 225 V E14	100	0.00 s	0.0 mg	Yes	30 lm	
SPC.T CL 15 W 230 V E14	100	0.00 s	0.0 mg	Yes		

Product family datasheet

Product description	Color rendering index Ra	Warm-up time (60 %)	Lamp mercury content	Mercury-free	Nominal luminous flux	EEI – Energy Label
SPC.T CL 25 W 230 V E14	100	0.00 s	0.0 mg	Yes		F
SPC.T FR 15 W 230 V E14	100	0.00 s	0.0 mg	Yes		
SPC.T FR 25 W 230 V E14	100	0.00 s	0.0 mg	Yes		F

Application advice

For more detailed application information and graphics please see product datasheet.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.