

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0712340119

Status:


Obsolete

Description:

4.20mm (.165") Pitch Mini-Fit® Header, Surface Mount, Single Row, Right Angle, with Snap-in Plastic Peg PCB Lock, 11 Circuits, 0.76µm (30µ") Gold (Au) Selective Plating, with Positive Lock

Replacement Part Number:

NONE



Documents:

[Drawing \(PDF\)](#)

General	
Product Family	PCB Headers
Series	71234
Application	Power, Wire-to-Board
Comments	Square Pin
Obsolete Date	2006/05/01
Product Name	Mini-Fit®
Replacement Part Number	NONE
Physical	
Breakaway	No
Circuits (Loaded)	11
Circuits (maximum)	11
Color - Resin	Natural
Durability (mating cycles max)	30
Glow-Wire Compliant	No
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Rows	1
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.40mm (.094")
Packaging Type	Tray
Pitch - Mating Interface	4.20mm (.165")
Plating min - Mating	0.762µm (30µ")
Plating min - Termination	2.540µm (100µ")
Shrouded	Partial
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount
Electrical	
Current - Maximum per Contact	7A
Voltage - Maximum	600V
Solder Process Data	
Lead-free Process Capability	SMC & Wave Capable (TH only)
Process Temperature max. C	235
Material Info	
Reference - Drawing Numbers	
Product Specification	PS-71690-001

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

71234Series

Mates With

Mini-Fit® IDT Receptacle Housing 5557 , 71694

This document was generated on 05/17/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION