





MATERIAL:

MOUNTING BUSHING: COPPER ALLOY, NICKEL PLATED.
HOUSING: THERMOPLASTIC, BLACK
PIN, SPRING AND TERMINALS: COPPER ALLOY, SILVER PLATED.
INSULATORS: PHENOLIC
HARDWARE: HEX NUT: COPPER ALLOY, NICKEL PLATED
FLAT WASHER: STEEL, NICKEL PLATED
(NOT SHOWN)



CIRCUIT DIAGRAM

CUSTOMER DRAWING

CAD/CAM DWG. NO.
L712A-CD
SHEET 1 OF 1

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION. SEE S/C ENGINEERING STANDARD ES-0001.					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSE ONLY.				
					UNLESS OTHERWISE SPECIFIED					SIZE				
					1. ALL DIMENSIONS IN INCHES TWO PLACE DECIMAL ±.01 THREE PLACE DECIMAL ±.005 ANGLES ±0.5° ALL DIA'S CONCENTRIC WITHIN .005 T.I.R. 2. REMOVE ALL BURRS 3. MAKE NO DIMENSIONAL ALLOWANCES FOR APPLIED FINISHES, I.E., PLATING, PAINTING, ETC. 4. HOLES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±.002					FINISH SPEC. NO. FIRST USED ON DATE DRAWN 2-21-94 BY ES CHK'D JLD 2-22-94 APP'D GHJ 2-22-94				
										MATERIAL SPEC. NO. Switchcraft®				
					NAME POWER JAX					PART NO. L712A				
					REVISIONS					ISSUE J				