



LOC —	DIST —	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			5	CAD-NEUERSTELLUNG, WAR AUF 826 545-550 C-FORMAT FORM-UND LAGETOLERANZ KORRIGIERT	11.05.90	A.HO	—
			6	REV PER ECO-10-000443	16.01.10	KK	AEG
			7	ECR-10-025774	21JAN11	KK	HMR

POLZ.	L±0.3	BESTELL-NR.
1	3.3	826 576 -1
2	7.3	-2
3	11.3	-3
4	15.2	-4
5	19.2	-5
6	23.1	-6
7	27.1	-7
8	31.1	-8
9	35.1	-9
10	39.0	-0
11	43.0	-1
12	46.9	-2
13	50.9	-3
14	54.8	-4
15	58.8	-5
16	62.8	-6
17	66.7	-7
18	70.7	-8
19	74.7	-9
20	78.6	-0
21	82.6	-1
22	86.5	-2
23	90.5	-3
24	94.4	-4
25	98.4	-5
26	102.4	-6
27	106.3	-7
28	110.3	-8
29	114.2	-9
30	118.2	-0
31	122.2	-1
32	126.1	-2
33	130.1	-3
34	134.0	-4
35	138.0	-5
36	141.6	3- 826 576 -6

ZEICHNUNG GÜLTIG AB 20/90



1 2.5 μm-5 μm ZINN ÜBER 1.27 μm NICKEL

2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

3 OBSOLETE

KONTAKTSTIFT	Cu Zn	1
STIFTGEHÄUSE	PBTP GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE

DIMENSIONS:

mm

DWN	HIRT	02.11.78	MATERIAL	—	FINISH	—
CHK	HÖWEL	09.02.79				
APVD	—	—				
PRODUCT SPEC	—	—	AMPMODU I STIFTL. RASTER 3.96 EINREIHIG			
APPLICATION SPEC	—	—				
WEIGHT	—	—	SIZE	A4	CAGE CODE	00779
CUSTOMER DRAWING			DRAWING NO	C-826576	RESTRICTED TO	—
			SCALE	4:1	SHEET	1 OF 1
			REV 7			

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

By —

COPYRIGHT —

©

0 PLC	± —
1 PLC	± —
2 PLC	± —
3 PLC	± —
4 PLC	± —
ANGLES	± —

