






1	2	3	4	5																																																																											
HOW TO ORDER 2227MC-XX-XX 03: 0.3", 06: 0.6" ROW TO ROW SPACE NO. OF POSITION MC: MACHINE PIN		<table><tr><th>CIRCUITS</th><th>DIM. A</th><th>DIM. B</th><th>DIM. C</th><th>SPACE</th></tr><tr><td>6</td><td>7.62</td><td>7.62</td><td>10.16</td><td rowspan="8">03</td></tr><tr><td>8</td><td>10.16</td><td>7.62</td><td>10.16</td></tr><tr><td>10</td><td>12.70</td><td>7.62</td><td>10.16</td></tr><tr><td>14</td><td>17.78</td><td>7.62</td><td>10.16</td></tr><tr><td>16</td><td>20.32</td><td>7.62</td><td>10.16</td></tr><tr><td>18</td><td>22.86</td><td>7.62</td><td>10.16</td></tr><tr><td>20</td><td>25.40</td><td>7.62</td><td>10.16</td></tr><tr><td>22</td><td>27.94</td><td>7.62</td><td>10.16</td></tr><tr><td>24</td><td>30.48</td><td>7.62</td><td>10.16</td><td rowspan="8">06</td></tr><tr><td>28</td><td>35.56</td><td>7.62</td><td>10.16</td></tr><tr><td>24</td><td>30.48</td><td>15.24</td><td>17.78</td></tr><tr><td>28</td><td>35.56</td><td>15.24</td><td>17.78</td></tr><tr><td>32</td><td>40.64</td><td>15.24</td><td>17.78</td></tr><tr><td>36</td><td>45.66</td><td>15.24</td><td>17.78</td></tr><tr><td>40</td><td>50.80</td><td>15.24</td><td>17.78</td></tr><tr><td>42</td><td>53.34</td><td>15.24</td><td>17.78</td></tr><tr><td>48</td><td>60.96</td><td>15.24</td><td>17.78</td></tr></table>	CIRCUITS	DIM. A	DIM. B	DIM. C	SPACE	6	7.62	7.62	10.16	03	8	10.16	7.62	10.16	10	12.70	7.62	10.16	14	17.78	7.62	10.16	16	20.32	7.62	10.16	18	22.86	7.62	10.16	20	25.40	7.62	10.16	22	27.94	7.62	10.16	24	30.48	7.62	10.16	06	28	35.56	7.62	10.16	24	30.48	15.24	17.78	28	35.56	15.24	17.78	32	40.64	15.24	17.78	36	45.66	15.24	17.78	40	50.80	15.24	17.78	42	53.34	15.24	17.78	48	60.96	15.24	17.78	MATERIAL & FINISH * Contact: Beryllium Copper (BeCu) * Sleeve: Brass Plating: G=Gold Plated T=Tin Plated * Insulator: IC Socket=PBT * Insertion Standard Force: Average 300 GR * Extraction Standard Test: Average 60 GR * Resist to Soldering Heat: Max. 120~130°C, 5 Sec. * Current Rating: 1A * Operating Humidity Range: Annual mean 75% * Contact Resistance : 10 Milliohm * Insulator Resistance : 5000 Mege Ohm at 500 VDC * Dielectric Strength : 1000 VRMS Min * Rated Voltage : 100 VRMS / 150VDC * Temperature: - 55°C TO + 125°C	
CIRCUITS	DIM. A	DIM. B	DIM. C	SPACE																																																																											
6	7.62	7.62	10.16	03																																																																											
8	10.16	7.62	10.16																																																																												
10	12.70	7.62	10.16																																																																												
14	17.78	7.62	10.16																																																																												
16	20.32	7.62	10.16																																																																												
18	22.86	7.62	10.16																																																																												
20	25.40	7.62	10.16																																																																												
22	27.94	7.62	10.16																																																																												
24	30.48	7.62	10.16	06																																																																											
28	35.56	7.62	10.16																																																																												
24	30.48	15.24	17.78																																																																												
28	35.56	15.24	17.78																																																																												
32	40.64	15.24	17.78																																																																												
36	45.66	15.24	17.78																																																																												
40	50.80	15.24	17.78																																																																												
42	53.34	15.24	17.78																																																																												
48	60.96	15.24	17.78																																																																												
 2227MC-XX-06		 2227MC-XX-03																																																																													
																																																																															
E				DRAWN: Jerry Chen GENERAL TOLERANCE: ±0.2  NELTRON INDUSTRIAL CO.,LTD																																																																											
D					CHECKED: Peter Huang UNIT: MM SCALE: SHEET: 1 / 1 PROJECTION: 																																																																										
C	04-19-2002	2227MC-XX-XX				DESCRIPTION: SCREW MACHINE PIN IC SOCKET PART NO: 2227MC-XX-XX																																																																									
B	04-11-2002	2227MC-XX-XX					SIZE A4																																																																								
A	01-26-1999	2227MC-XX	Jerry Chen																																																																												
REV	DATE	FILE	BY																																																																												