



SOCKETS FOR C3 RELAYS

- Built in retaining clip
- Removable label marking facility
- Coding ring compatible
- One or two level terminals
- DIN rail, solder tag or PCB mount




S3-B

One level.

Integrated clip and marking label

Accepts the exclusive Releco coding ring for coding both the relay and base. DIN rail or panel mountable. Removable label. EN/DIN and sequential numbering. According to EN60947

Wiring diagram



Specifications

Nominal load 10A/250V
Dielectric strength (adjacent screws) 2,5 KV
Dielectric strength (screws/rail) 2,5 KV
Max. screw torque 1,2 Nm
Screw dimensions M3, Pozi
Wire in-lets capacity:
Solid wire 4 mm² or 2 x 2,25 mm²
Multi-core 22 - 14 AWG


S3-S

Two level.

Integrated clip and marking label

Accepts the exclusive Releco coding ring for coding both the relay and base. DIN rail or panel mountable. Removable label. EN/DIN and sequential numbering. According to EN60947

Wiring diagram



Specifications

Nominal load 10A/250V
Dielectric strength (adjacent screws) 2,5 KV
Dielectric strength (screws/rail) 2,5 KV
Max. screw torque 1,2 Nm
Screw dimensions M3, Pozi
Wire in-lets capacity:
Solid wire 4 mm² or 2 x 2,25 mm²
Multi-core 22 - 14 AWG

S3-L


S3-PO

8 pin, solder and printed circuit tags

S3-L Flange panel mountable.

S3-PO Printed circuit tags with flange.

Printed circuit lay-out





Specifications



Nominal load 10 A/250 V
Dielectric strength (adjacent pin) 2,5 KV
Hard brass, tin-plated terminals



S3-B





S3-S



S3-L

S3-PO



S3-BC

Coding Ring

Can be used to code a specific relay to fit a specific socket up to 11 combinations. Supplied in a pack of 5 pieces.