





Printed: Sep 23, 2011

Printed: Sep 23, 2011

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-DXXXXXL	03-381	3.81 mm



2p to 6p with wedge, above 7p
without wedge (including 7p)






N = Number of poles
Dim A = $N \times 3.81 [.150] + 0.80 [.031]$
Dim B = $(N-1) \times 3.81 [.150]$

Poles	Tolerance
2-6p	$\pm 0.15 [.006]$
7-12p	$\pm 0.20 [.008]$
13-17p	$\pm 0.25 [.010]$
18-24p	$\pm 0.30 [.012]$


mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK			
ltr	ecn no	dr	date	tolerances unless otherwise specified			title			
D				angles	X.±0.5		TERMINAL BLOCK			
				linear	X.X±0.3		PLUGGABLE, PLUG, SIGNAL, W/O FLANGE			
				X*±1*	X.XX±0.1		FRONT SCREW			
		dr	WENDY CHEN	051810			dwg no		sheet 3 of 5	size
		enr	JASON HSU	051810			20020013			A4
		chr	GARY HSIEH	051810						
		appd	JOSEPH HSIA	051810						
sheet index	revision						type		CUSTOMER Drawing	
	sheet									

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-GXXXXXXLF	03-500	5.00 mm




N = Number of poles
 Dim A = $N \times 5.0$ [.197]
 Dim B = $(N-1) \times 5.0$ [.197]

Poles	Tolerance
2-7p	± 0.15 [.006]
8-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]






mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK	
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title	
D					angles	X.±0.5	TERMINAL BLOCK	
					linear	X.X±0.3	PLUGGABLE, PLUG, SIGNAL, W/O FLANGE	
					X'±1"	X.XX±0.1	FRONT SCREW	
			dr	WENDY CHEN	051810	scale	sheet 4 of 5	
			enr	JASON HSU	051810	FCI	20020013	
			chr	GARY HSIEH	051810		A4	
			appd	JOSEPH HSIA	051810		CUSTOMER Drawing	
sheet index	revision	sheet						

PRODUCT NUMBER	SERIES NAME	PITCH
20020013-HXXXXXXLF	03-508	5.08 mm



N = Number of poles
Dim A = $N \times 5.08$ [.200]
Dim B = $(N-1) \times 5.08$ [.200]

Poles	Tolerance
2-6p	± 0.15 [.006]
7-12p	± 0.25 [.010]
13-18p	± 0.30 [.012]
19-24p	± 0.40 [.016]



mat'l. code				surface ASME Y14.5 ✓	tolerance ASME Y14.5	projection MM [INCH]	product family TERMINAL BLOCK
ltr	ecn	no	dr	date	tolerances unless otherwise specified		title
D					angles X $\pm$ 1°	scale	TERMINAL BLOCK PLUGGABLE, PLUG, SIGNAL, W/O FLANGE FRONT SCREW
					linear X.XX $\pm$ 0.1		dwg no
			dr	WENDY CHEN	051810	FCI	sheet 5 of 5
			enr	JASON HSU	051810		size
			chr	GARY HSIEH	051810		20020013
			appd	JOSEPH HSIA	051810		A4
sheet index	revision sheet					type	CUSTOMER Drawing