

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A
A DIVISION OF HONEYWELL INC.
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

7SE9-T

7SE9-T

REPLACES

RELEASE NO. PR-15152

M

DRAWING
NUMBER

3

ISSUE

CHECK


REVISIONS

A PRI 15152

JAS 24 OCT 86

B CO61515

CJH 21 APR 87




NOTE

- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON $.375 \pm .002$ CENTERS
- 2 ACTUATION IN LINE WITH ARROW "A" IS RECOMENDED
- 3 - BASIC SWITCH HAS 24K SOLID GOLD CONTACT MATERIAL
- 4 YELLOW MARKING IS ON BOTH SIDES OF HOUSING TO IDENTIFY THAT THIS UNIT HAS GOLD CONTACTS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE----- 4 - 8 OZ	CONTACT ARRANGEMENT S P D T	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
RELEASE FORCE----- 2 OZ MIN	10 VDC----- 0.5 AMP	ONE PLACE (.0) $\pm .030$	
PRETRAVEL----- .004 MIN	30 VOLTS DC RATING	TWO PLACE (.00) $\pm .015$	
DIFFERENTIAL TRAVEL----- .004 MAX	INDUCTIVE---SEA LEVEL----- 1/2 AMP	THREE PLACE (.000) $\pm .005$	
OVERTRAVEL----- .003 MIN	RESISTIVE---SEA LEVEL----- 1 AMP	ANGLES \pm	
	50,000 FT----- 1 AMP	RAW MATERIAL - COMMERCIAL STANDARD	
	MAXIMUM INRUSH----- 2 AMP	DIMENSIONS ARE IN INCHES AND ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED	
		MICRO SWITCH STANDARDS APPLY	
		WEIGHT .26 OZ MAX	

FO-52848-B

DRAWN

CHECK KAG 24 OCT 86

CHECK KAG 24 OCT 86

J A S 24 OCT 86

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[7SE9-T](#)