







SHOWN WITH DUST CAP
INSTALLED (NO MODULE)




SC-SC VERSIONS
SEE SHEET 3




SC-FC VERSIONS
SEE SHEET 4




SC-ST VERSIONS
SEE SHEET 5




SC-LC VERSION
SEE SHEET 6




LC-LC VERSIONS
SEE SHEET 7



LC-SC VERSION
SEE SHEET 8




LC-FC VERSION
SEE SHEET 9




LC-ST VERSION
SEE SHEET 10

ENTER DESCRIPTION EC NO: MF2008-0308 DRAWN: KPEVZNER 2008/02/07 CHKD: 2008/02/07 APPR: IGUMIN 2008/02/14 A3	QUALITY SYMBOLS ▽=0 ▽=0 DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
				MM/IN		TITLE		UNIVERSAL ADAPTER			
		4 PLACES		± ---	± ---	DRAWN BY		DATE			
		3 PLACES		± ---	± ---	SERNST		2006/02/13			
		2 PLACES		± ---	± ---	CHECKED BY		DATE			
		1 PLACE		± ---	± ---	DSZILAGYI		2006/03/07			
						APPROVED BY		DATE			
		ANGULAR ± 1 °		SMIGO		2006/03/07		MOLEX MOLEX INCORPORATED			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.			
				SEE TABLES		SD-106154-002		1 OF 10			
				SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					


MODULE P/N	TYPE	COLOR
1061540020	SC	BLUE
1061540022		BEIGE
1061540025		GREEN
1061540031	FC	BLUE
1061540033		BEIGE
1061540036		GREEN
1061540041	ST	BLUE
1061540043		BEIGE
1061540130	LC	BLUE
1061540131		BEIGE
1061540132		GREEN




SC



FC




ST




LC


BASE P/N	TYPE	SLEEVE MAT'L	TYPE
1061540015	SINGLE MODE	ZIRCONIA	SC BASE TO 2.5mm
1061540016	MULTIMODE	PHOS BRONZE	
1061540017	SM/MM	NICKEL	SC BASE TO 1.25mm
1061540215	SINGLE MODE	ZIRCONIA	LC BASE TO 1.25mm
1061540216	MULTIMODE	PHOS BRONZE	
1061540217	SM/MM	NICKEL	LC BASE TO 2.5mm




SC TO 2.5mm



SC TO 1.25mm



LC TO 1.25mm



LC TO 2.5mm

SLEEVE ASBY	TYPE	SLEEVE MAT'L	TYPE
1061540050	SINGLE MODE	ZIRCONIA	2.5mm
1061540051	MULTIMODE	PHOS BRONZE	
1061540052	SINGLE MODE	ZIRCONIA	1.25mm
1061540053	MULTIMODE	PHOS BRONZE	
1061540054	SM/MM	NICKEL	HYBRID 1.25 TO 2.5mm



2.5mm




1.25mm



HYBRID

DUST CAP
P/N 1061540006



ENTER DESCRIPTION EC NO: MF2008-0308 DRAWN BY: DRWINKPEVZNER CHKD: 2008/02/07 APPR: IGUMIN 2008/02/14	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± 1 ° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE MM/IN DRAWN BY: SERNST DATE: 2006/02/13 CHECKED BY: DSZILAGYI DATE: 2006/03/07 APPROVED BY: SMIGO DATE: 2006/03/07	SCALE 2:1 TITLE UNIVERSAL ADAPTER	DESIGN UNITS METRIC THIRD ANGLE PROJECTION	MATERIAL NO. SEE TABLES	DOCUMENT NO. SD-106154-002	SHEET NO. 2 OF 10

10

9

8

7

6

5




4

3


2

106154

ADAPTER P/N	STYLE	TYPE	SLEEVE MAT'L	MODULE COLOR
1061541100	SC-SC	SINGLE MODE	ZIRCONIA	BLUE
1061541105	SC-SC/APC			GREEN
1061541101	SC-SC	MULTIMODE	PHOSPHOR BRONZE	BEIGE



RECOMMENDED MOUNTING CUTOUT
(1.6mm THICK PANEL)

**NOTES:**

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. PACKAGING: ADAPTERS AND DUSTCAPS ARE PACKED IN A PLASTIC TRAY.

ENTER DESCRIPTION EC NO: MF2008-0308 DRAWN BY: DRWINKPEVZNER CHKD: 2008/02/07 APPR: LGUMIN 2008/02/14	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2.5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY SERNST	DATE 2006/02/13	TITLE UNIVERSAL ADAPTER				
			4 PLACES	± ---	± ---	CHECKED BY DSZILAGYI				DATE 2006/03/07	
			3 PLACES	± ---	± ---	APPROVED BY SMIGO	DATE 2006/03/07	 MOLEX INCORPORATED			
			2 PLACES	± ---	± ---	MATERIAL NO.				DOCUMENT NO.	SHEET NO.
			1 PLACE	± ---	± ---	SEE TABLE				SD-106154-002	3 OF 10
			ANGULAR ± 1 °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
					SIZE B						

9

8

7

6

5





4

3

2

1

ADAPTER P/N	STYLE	TYPE	SLEEVE MAT'L	MODULE COLOR	KEY SIZE (mm)
1061541110	SC-FC	SINGLE MODE	ZIRCONIA	BLUE	2.3
1061541115	SC-FC/APC			GREEN	2
1061541111	SC-FC	MULTIMODE	PHOSPHOR BRONZE	BEIGE	2.3



RECOMMENDED MOUNTING CUTOUT
(1.6mm THICK PANEL)

- NOTES:
- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
 - PACKAGING: ADAPTERS AND DUSTCAPS ARE PACKED IN A PLASTIC TRAY.

ENTER DESCRIPTION EC NO: MF2008-0308 DRW:KPEVZNER CHKD: APPR: LGUMIN A3	DESCRIPTION 2008/02/07 2008/02/07 2008/02/14	QUALITY SYMBOLS ▽=0 C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY SERNST	DATE 2006/02/13	TITLE UNIVERSAL ADAPTER				
			4 PLACES ± ---	± ---	CHECKED BY DSZILAGYI	DATE 2006/03/07					
			3 PLACES ± ---	± ---	APPROVED BY SMIGO	DATE 2006/03/07	MOLEX INCORPORATED				
			2 PLACES ± ---	± ---	MATERIAL NO. SEE TABLE						
			1 PLACE ± ---	± ---	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						
			ANGULAR ± 1 °								
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											

10

9

8

7

6

5





4

3

2

106154

ADAPTER P/N	STYLE	TYPE	SLEEVE MAT'L
1061541120	SC-ST	SINGLE MODE	ZIRCONIA
1061541121		MULTIMODE	PHOS BRONZE



RECOMMENDED MOUNTING CUTOUT
(1.6mm THICK PANEL)

NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. PACKAGING: ADAPTERS AND DUSTCAPS ARE PACKED IN A PLASTIC TRAY.

ENTER DESCRIPTION EC NO: MF2008-0308 DRAWN: KPEVNER 2008/02/07 CHKD: 2008/02/07 APPR: IGUMIN 2008/02/14	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2.5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
				mm	INCH	DRAWN BY SERNST	DATE 2006/02/13	TITLE UNIVERSAL ADAPTER				
			4 PLACES	± ---	± ---	CHECKED BY DSZILAGYI	DATE 2006/03/07	 MOLEX INCORPORATED				
			3 PLACES	± ---	± ---	APPROVED BY SMIGO	DATE 2006/03/07					
			2 PLACES	± ---	± ---	MATERIAL NO.				DOCUMENT NO.	SHEET NO.	
			1 PLACE	± ---	± ---	SEE TABLE				SD-106154-002	5 OF 10	
			ANGULAR ± 1 °									
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS									

9

8

7

6

5

4

3

2

1

10

9

8

7

6

5



4

3



2

106154

ADAPTER P/N	STYLE	TYPE	SLEEVE MAT'L
1061541130	SC-LC	SM OR MM	NICKEL



RECOMMENDED MOUNTING CUTOUT
(1.6mm THICK PANEL)



NOTES:

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- PACKAGING: ADAPTERS AND DUSTCAPS ARE PACKED IN A PLASTIC TRAY.

ENTER DESCRIPTION EC NO: MF2008-0308 DRAWN BY: DRWINKEVZNER CHKD: 2008/02/07 APPR: IGUMIN 2008/02/14	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2.5:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION				
					DRAWN BY	DATE	TITLE						
					SERNST	2006/02/13	UNIVERSAL ADAPTER						
					CHECKED BY	DATE							
					DSZILAGYI	2006/03/07							
					APPROVED BY	DATE							
					SMIGO	2006/03/07	MOLEX INCORPORATED						
					MATERIAL NO.	DOCUMENT NO.				SHEET NO.			
					SEE TABLE			SD-106154-002				6 OF 10	
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

9

8

7

6

5

4

3

2

1

10

9

8

7

6

5




4

3


2

106154

ADAPTER P/N	STYLE	TYPE	SLEEVE MAT'L	MODULE COLOR
1061541630	LC-LC	SINGLE MODE	ZIRCONIA	BLUE
1061541635	LC-LC/APC			GREEN
1061541631	LC-LC	MULTIMODE	PHOSPHOR BRONZE	BEIGE



RECOMMENDED MOUNTING CUTOUT
(1.6mm THICK PANEL)



NOTES:

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- PACKAGING: ADAPTERS AND DUSTCAPS ARE PACKED IN A PLASTIC TRAY.

ENTER DESCRIPTION EC NO: MF2008-0308 DRWN:KPEVZNER 2008/02/07 CHKD: 2008/02/07 APPR: IGUMIN 2008/02/14 A3	DESCRIPTION QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2.5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	TITLE UNIVERSAL ADAPTER			
			mm	INCH	DRAWN BY SERNST	DATE 2006/02/13	MOLEX INCORPORATED					
		4 PLACES	± ---	± ---	CHECKED BY DSZILAGYI	DATE 2006/03/07						
		3 PLACES	± ---	± ---	APPROVED BY SMIGO	DATE 2006/03/07						
		2 PLACES	± ---	± ---	MATERIAL NO. SEE TABLE					DOCUMENT NO. SD-106154-002	SHEET NO. 7 OF 10	
		1 PLACE	± ---	± ---								
		ANGULAR ± 1 °										
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

9

8

7

6

5

4

3

2

1

10

9

8

7

6

5



4

3



2

106154

ADAPTER P/N	STYLE	TYPE	SLEEVE MAT'L
1061541600	LC-SC	SM OR MM	NICKEL



RECOMMENDED MOUNTING CUTOUT
(1.6mm THICK PANEL)



NOTES:

- ALL DIMENSIONS ARE FOR REFERENCE ONLY.
- PACKAGING: ADAPTERS AND DUSTCAPS ARE PACKED IN A PLASTIC TRAY.

ENTER DESCRIPTION EC NO: MF2008-0308 DRAWN BY: DRWINKPEVNER CHKD: 2008/02/07 APPR: LGUMIN 2008/02/14 A3	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2.5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
					DRAWN BY	DATE	TITLE			
					SERNST	2006/02/13	UNIVERSAL ADAPTER			
					CHECKED BY	DATE				
					DSZILAGYI	2006/03/07				
					APPROVED BY	DATE				
					SMIGO	2006/03/07	 MOLEX INCORPORATED			
					MATERIAL NO.	DOCUMENT NO.		SHEET NO.		
					SEE TABLE		SD-106154-002			8 OF 10
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

9

8

7

6

5

4

3

2

1

10

9

8

7

6

5



4

3



2

106154

ADAPTER P/N	STYLE	TYPE	SLEEVE MAT'L
1061541610	LC-FC	SM OR MM	NICKEL



RECOMMENDED MOUNTING CUTOUT
(1.6mm THICK PANEL)



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. PACKAGING: ADAPTERS AND DUSTCAPS ARE PACKED IN A PLASTIC TRAY.

ENTER DESCRIPTION EC NO: MF2008-0308 2008/02/07 DRWNG: KPEVZNER CHKD: 2008/02/07 APPR: LGUMIN 2008/02/14 A3	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2.5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY SERNST	DATE 2006/02/13	TITLE UNIVERSAL ADAPTER					
			4 PLACES ± ---	± ---	CHECKED BY DSZILAGYI	DATE 2006/03/07						
			3 PLACES ± ---	± ---	APPROVED BY SMIGO	DATE 2006/03/07	 MOLEX INCORPORATED					
			2 PLACES ± ---	± ---	MATERIAL NO. SEE TABLE					DOCUMENT NO. SD-106154-002	SHEET NO. 9 OF 10	
			1 PLACE ± ---	± ---	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
ANGULAR ± 1 °												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												

9

8

7

6

5

4

3

2

1

10

9

8

7

6

5




4

3


2

106154

ADAPTER P/N	STYLE	TYPE	SLEEVE MAT'L
1061541620	LC-ST	SM OR MM	NICKEL



RECOMMENDED MOUNTING CUTOUT
(1.6mm THICK PANEL)



NOTES:

1. ALL DIMENSIONS ARE FOR REFERENCE ONLY.
2. PACKAGING: ADAPTERS AND DUSTCAPS ARE PACKED IN A PLASTIC TRAY.

ENTER DESCRIPTION EC NO: MF2008-0308 DRAWN BY: DRWINKEVZNER CHKD: 2008/02/07 APPR: IGUMIN 2008/02/14	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE 2.5:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	
				mm	INCH	DRAWN BY	DATE	TITLE		
			4 PLACES	± ---	± ---	SERNST	2006/02/13	UNIVERSAL ADAPTER		
			3 PLACES	± ---	± ---	CHECKED BY	DATE			
			2 PLACES	± ---	± ---	DSZILAGYI	2006/03/07	MOLEX INCORPORATED		
			1 PLACE	± ---	± ---	APPROVED BY	DATE			
			ANGULAR ± 1 °		SMIGO	2006/03/07				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.					DOCUMENT NO.
					SEE TABLE		SD-106154-002			10 OF 10
					THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

9

8

7

6

5

4

3

2

1