





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	—	E1		text for packaging corrected	ECR-08-001868	23.01.08	SR ST
		E2		REVISED PER ECO-11-002591		17FEB11	HMR MM




Contact arrangement view from termination side

Printing 1-24 Thermo




Contact arrangement view from termination side


Printing 1-24




Printing 1-24 Screw




Printing 25-48




Printing 25-48 Screw



Printing 12+6+6 Screw/Thermo



assembly directions



× distance for a safe
contact max: max: 21 mm


NOTES:



- 1 SUITABLE CRIMP CONTACTS: SERIES HE/HA
OUTER DIMENSIONS OF INSULATION: MAX. Ø3,2 MM
- 2 SUITABLE HOOD SIZE 8; 12: SERIES HB; HD; HIP; EMV
SUITABLE INSERTION AND EXTRACTION TOOL:
SCREWDRIVER 0,5x3 DIN 5264
- 3 Strip lenght: Screw conection 10mm
Spring clamp conection 10mm Crimp conection 7.5mm
- 4 STANDARDS:
DIN EN 61984; DIN EN 60664-1

5 PACKAGING:
5 SETS IN A CARTON, PRE-MOUNTED

6 SPECIAL PACKAGING: Krauss-Maffei
PACKAGING UNIT: 220 PIECES

Panel cut-out for contact insert when used without housing



	1									Socket contact		light grey	5	earth wire contact with drillings Ø3,3 / without fixing screws								
	1					1	1			Deckel Federklemmversion		light grey	4									
								1	1	Crimp Crimp version		light grey	3									
1			1	1	1				1	1	1	Cover screw version	2									
1	1	1	1	1	1	1	1	1	1	1	1	Buchseneinsatz	1									
0-10-29-31-89-49-57-97-12-92-31-91-71-1										DESCRIPTION / BENENNUNG	MATERIAL	COLOR / FARBE	ITEM NO. POS.									
HE.24.Bu.S. B1-24 KM HE.24.Bu.C-3,3 B1-24 HE.24.Bu.SC-AU B1-24 HE.24.Bu.S-T B 12+6+6 HE.24.Bu.S-AU B25-48 HE.24.Bu.S-AU B1-24 HE.24.Bu.SCB B25-48 HE.24.Bu.SC B1-24 HE.24.Bu.CB B25-48 HE.24.Bu.C B1-24 HE.24.Bu.SB B25-48 HE.24.Bu.S-T HE.24.Bu.S B1-24										ORDERING TEXT / BESTELLTEXT	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	08.02.2000	 Tyco Electronics Corporation Harrisburg, Pa 17105-3608							
													CHK	08.02.2000								
											DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: GENERAL TOLERANCES h. ISO 80/5 h. ISO 2768 - mH-E n. DIN 16901 - 14.0		APVD	-	NAME		Female insert HE.24.BU.S/C			
															PRODUCT SPEC							
															APPLICATION SPEC				SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
											MATERIAL		FINISH		WEIGHT		A2		00779	C=1103641		-
CUSTOMER DRAWING												SCALE		1:1		SHEET	1 of 1		REV	E2		