

THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.


REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	10/13/03	


1. SAFETY JACK, REAR MOUNT, VERTICAL PCB, LONG PIN.
2. SPECIFICATIONS:
INSULATOR: POLYACETAL
CONTACT: BRASS, NICKEL PLATED
3. RATING:
VOLTAGE: 1,000 V CATIII P2 (IEC 61010-031)
CURRENT: 25A MAX.
RESISTANCE: $<5\text{m}\Omega$.
TEMPERATURE: -20°C TO $+80^{\circ}\text{C}$.
4. MOUNTING: REF. DIAGRAM
5. MAXIMUM PANEL THICKNESS: .12 (3).

PART NUMBER

CT3150-#

- COLOR: 0 – BLACK
1 – BROWN
2 – RED
4 – YELLOW
5 – GREEN
6 – BLUE
7 – PURPLE
8 – GRAY
9 – WHITE



THIRD ANGLE PROJECTION		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ± 1/32 .XX ± .02 .XXX ±.005 DO NOT SCALE DRAWING	CONTRACT NO.		Cal Test Electronics 28280 Savi Ranch Parkway Yorba Linda, CA 92887-4610			
			APPROVALS	DATE	TITLE 4mm SAFETY JACK, VERTICAL PCB MOUNT, LONG PIN			
		DRAWN	WDH	10/13/03				
		MATERIAL	CHECKED		SIZE	CAGE CODE	DWG. NO.	REV.
		FINISH	ENGR.		A	43F45	P315000	—
NEXT ASSY	USED ON		DESIGN ACTIVITY		SCALE		1:1	SHEET
APPLICATION								1 OF 1