



Super Torq Swage Standoff, Round, Electro Tin - Bright, Brass, 4.7mm Shank OD, M3.0x0.5, 8mm Body Length

Part ID: **BR5114SPC-08.0-43**

Technical Specifications

Material Grade (Alloy):	Brass 360 (ASTM-B-116, QQ-B-626) 353 (ASTM-B-116)
Profile	Round
Outside Diameter	6.0mm
Overall Length	11.4mm
Female Thread	M3.0x0.5
Swage Anvil Code	6-2
Swage Punch Code	188

Shank	Length: 3.4mm Outside Diameter: 4.7mm Inside Diameter: 3.74mm Panel Thickness: 2.4mm Code: C
Panel Hole Size	4.820-4.900
Finish Desc. (Spec)	Electro Tin - Bright (ASTM B 545)
Compliant To	RoHS, WEEE, REACH, Conflict Minerals

Document Downloads

- [Catalog Page](#)
- [PDF](#)
- [DWF](#)
- [IGS](#)
- [STEP](#)
- [X_B](#)

- [Conformity Statement](#)

Stock and Lead Time

Stock	420	Same Day
Stock to Plate	0	2 to 3 weeks
Manufacture Lead Time	9-10	Weeks

Available Finishes

43 - Electro Tin - Bright



Product Description

Super-Torq Swage parts are designed to resist rotation under high assembly torques and to eliminate breaks in electrical connections due to spinning of standoffs during assembly. The unique Super-Torq corner knurl prevents the fastener from twisting after installation. Lyn-Tron standard swaging tools can be used on Super-Torq standoffs in the same way as installing conventional swage standoffs for an easy upgrade. The round shape provide a nice finished look. Brass is corrosion resistant, nonmagnetic, and easily machinable. Base metal is yellow, but many plating options are available when different colors are required.