




All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to
RPC-N according to

Rosenberger SnapN
IEC 60169-16 ; CECC 22 210 ; MIL-STD 348A/304

Documents

N/A

Material and plating

Connector parts

Center contact
Outer contact RPC-N
Outer contact SnapN
Detent spring SnapN
Latching sleeve SnapN
Dielectric RPC-N
Dielectric SnapN

Material

Beryllium copper
Stainless steel
Brass
Spring bronze
Brass
PPE
PTFE

Plating

Gold, min. 1.27 µm, over chemical nickel
Passivated
White bronze(e.g. Optalloy®)
White bronze(e.g. Optalloy®)
White bronze(e.g. Optalloy®)

Technical Data Sheet

Rosenberger

ADAPTOR
SnapN 50Ω PLUG - RPC-N 50Ω JACK

53QS105-K00S3

Electrical data

Impedance	50 Ω
Frequency	DC to 11 GHz
Return loss	≥ 26 dB, DC to 11 GHz
Insertion loss	≤ 0.05 dB x $\sqrt{f \text{ [GHz]}}$ dB
Insulation resistance	≥ 5 GΩ
Center contact resistance	≤ 1 mΩ
Outer contact resistance	≤ 1 mΩ
Test voltage (at sea level)	2500 V rms
Working voltage (at sea level)	500 V rms
RF-leakage	≥ 90 dB @ DC to 3 GHz

Mechanical data

Mating cycles RPC-N	≥ 500
Mating cycles SnapN	≥ 200
Center contact captivation	≥ 28 N
Coupling test torque RPC-N	1.70 Nm
Recommended torque RPC-N	0.70 Nm to 1.10 Nm
Engagement force SnapN	30 N typical
Disengagement force SnapN	30 N typical

Please always use the latching sleeve for locking and unlocking units

Environmental data

Temperature range	-40°C to +85°C
Thermal shock	IEC 61169-1, Subclause 9.4.4
Corrosion	IEC 61169-1, Subclause 9.4.6
Vibration	IEC 61169-1, Subclause 9.3.3
Shock	IEC 61169-1, Subclause 9.3.14
Moisture resistance	IEC 61169-1, Subclause 9.4.3
RoHS	compliant

Tooling

N/A

Suitable cables

N/A

Weight

Weight	59.3 g/pce
--------	------------

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	18/01/05	J_Gramsamer	31.03.15	c00	15-0397	J_Krautenbacher	31.03.15
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de			Page 2 / 2