



Silicon Switching Diode

Rev. V2

Features

- Available in JAN, JANTX, and JANTXV per MIL-PRF-19500/116
- Metallurgically Bonded
- Hermetically Sealed
- Double Plug Construction



Maximum Ratings


Operating & Storage Temperature: -65°C to +175°C
 Operating Current: 125 mA @ $T_A = +75^\circ\text{C}$
 Derating Factor: 2.0 mA/°C above $T_A = +25^\circ\text{C}$
 Surge Current A: 2.00 A, sinewave, $P_w = 8.3$ ms
 Surge Current B: 0.704 A, square, $P_w = 8.3$ ms
 DC Reverse Voltage (VRWM): 75 V

Electrical Specifications @ +25°C (unless otherwise Specified)

JEDEC TYPE#	VBR @ 100 μA	VRWM	IO	Vf1 IF = 10 mA	Vf2 IF = 50 mA	Trr ¹	IR1 @ 20 Vdc	IR2 @ 75 Vdc	IR3 @ 20 Vdc $T_A = 150^\circ\text{C}$	IR4 @ 75 Vdc $T_A = 150^\circ\text{C}$	Capacitance @ 0 V	Capacitance @ 1.5 V
	Volts	Volts (pk)	mA	Vdc	Vdc	nsec	nA	μA	μA	μA	pF	pF
1N914UR	100	75	75	0.8	1.2	5	25	0.5	35	75	4.0	2.8
1N4148UR-1	100	75	200	0.8	1.2	5	35	0.5	35	75	4.0	2.8

1. Note1: IF = IR = 10 mA, RL = 100 ohms.

Outline Drawing



	MILLIMETERS		INCHES	
DIM	MIN	MAX	MIN	MAX
D	1.60	1.70	0.063	0.067
F	0.41	0.55	0.016	0.022
G	3.30	3.70	.130	.146
G1	2.54 REF.		.100 REF.	
S	0.03 MIN.		.001 MIN.	

LEADED DESIGN DATA

CASE: DO-213AA, Hermetically sealed glass case. (MELF, SOD-80, LL34)

LEAD FINISH: Tin / Lead


THERMAL RESISTANCE: ($R_{\theta\text{JEC}}$): 100 °C/W maximum at L = 0 inch

THERMAL IMPEDANCE: ($Z_{\theta\text{JX}}$): 25 °C/W maximum

POLARITY: Diode to be operated with the banded (cathode) end positive.


MOUNTING POSITION: Any.

Graphs



Typical Forward Current
vs Forward Voltage

NOTE : All temperatures shown on graphs are
junction temperatures



Typical Reverse Current
vs Reverse Voltage

MACOM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with MACOM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.