

EW63

EW63, HELIAX® Standard Elliptical Waveguide, 5.925–7.125 GHz, black PE jacket



Product Classification

Product Type	Elliptical waveguide
Product Brand	HELIAX®

General Specifications

Jacket Color	Black
Performance Note	Values typical, unless otherwise stated

Dimensions

Diameter Over Jacket (E Plane)	51.1 mm 2.012 in
Diameter Over Jacket (H Plane)	29.5 mm 1.161 in
Cable Volume	855 L/km 9.203 ft³/kft

Electrical Specifications

eTE11 Mode Cutoff	4.001 GHz
Group Delay at Frequency	126 ns/100 ft @ 6.775 GHz 413 ns/100 m @ 6.775 GHz
Operating Frequency Band	5.925 – 7.125 GHz

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
5.925–7.125 GHz	1.15	23.13

Attenuation

Frequency (GHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)	Group Velocity %
5.925	4.878	1.487	4.45	73.8
6.13	4.738	1.444	4.581	75.8
6.33	4.626	1.41	4.692	77.5

EW63

6.53	4.533	1.382	4.788	79
6.73	4.454	1.358	4.873	80.4
6.93	4.387	1.337	4.948	81.7

Material Specifications

Conductor Material	Corrugated copper
Jacket Material	PE

Mechanical Specifications

Minimum Bend Radius, Multiple Bends (E Plane)	260 mm 10.236 in
Minimum Bend Radius, Multiple Bends (H Plane)	740 mm 29.134 in
Minimum Bend Radius, Single Bend (E Plane)	180 mm 7.087 in
Minimum Bend Radius, Single Bend (H Plane)	510 mm 20.079 in
Maximum Twist	3.281 °/m 1 °/ft

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Temperature Rise	42 °C 107.6 °F

Packaging and Weights

Cable weight	0.76 kg/m 0.511 lb/ft
--------------	-------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

