


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	PART OBSOLESCENCE	03JUL2024	AR	VG

POS.	L ±0.5	PART-NO.
—	—	—
2	5.08	—2
3	7.62	—3
4	10.16	—4
5	12.70	—5
6	15.24	—6
7	17.78	—7
8	20.32	—8
9	22.86	—828 214 9
10	25.40	1— —0
11	27.94	1— —1
12	30.48	1— —2
13	33.02	1— —3
14	35.56	1— —4
15	38.10	1— —5
16	40.64	1— —6
17	43.18	1— —7
18	45.72	1— —8
19	48.26	1— —9
20	50.80	2— —0
21	53.34	2— —1
22	55.88	2— —2
23	58.42	2— —3
24	60.96	2— —4
25	63.50	2— —5
26	66.04	2— —6
27	68.58	2— —7
28	71.12	2— —8
29	73.66	2— —9
30	76.20	3— —0
31	78.74	3— —1
32	81.28	3— —2
33	83.82	3— —3
34	86.36	3— —4
35	88.90	3— —5
36	91.44	3— —6
37	93.98	3— —7
38	96.52	3— —8
39	99.06	3— —9
40	101.60	4— —0
41	104.14	4— —1
42	106.68	4— —2
43	109.22	4— —3
44	111.76	4— —4
45	114.30	4— 828 214 —5
46	116.84	4— —6
47	119.38	4— —7
48	121.92	4— —8
49	124.46	4— —9
50	127.00	5— 828 214 —0



NOTES:

- ① MIN.3.0μm TIN OVER 1.27μm NICKEL
② OBSOLETE

CONTACT PIN	①	CuZn	2
PIN HOUSING	GREEN	PBT	1
DESCRIPTION	COLOR/FINISH	MATERIAL	ITEM NO.

TE Connectivity. All Rights Reserved.



DIMENSIONS: mm	DWN R.FORELL 07.02.85	MATERIAL SEE TABLE	FINISH SEE NOTE 1
	CHK M.SCHAARSCHMIDT 07.02.85	TE Connectivity	
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 mm	APVD G.FELDMEIER 25.02.92		
0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —	PRODUCT SPEC 108-18012	NAME AMPMODU II PIN HEADER, SINGLE ROW	
	APPLICATION SPEC —	SIZE A4	CAGE CODE 00779
	WEIGHT	DRAWING NO C-828214	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 4:1	SHEET 1 OF 1
		REV D1	