



Heat Shrinkable Tubing 3:1 flexible and transparent

• TF34

Features and Benefits

This flexible, halogen free tubing provides good insulation, while the clear colour allows excellent visibility of the substrate below. For general purpose applications, bundling and jacketing of cables where visual inspection is required.



TF34 transparent tubing with 3:1 shrink ratio allowing for a wider range of application.

Cut lengths available on request. Please contact us!

Material Data

Material	Polyolefin, cross-linked (POX)
Colour	Transparent (CL)
Shrink Ratio	3:1
Operating Temperature	-55 °C to +135 °C
Minimum Shrink Temperature	+110 °C
Longitudinal change after shrinkage	-5% max.
Dielectric Strength	46 kV/mm



Technical Table

Article-No.	Type	Supplied Ø D	Recov. Ø d	Wall (WT) nom.	Reel Length (m)
333-30153	TF34-1.5/0.5	1.5	0.5	0.50	30
333-30303	TF34-3/1	3.0	1.0	0.50	30
333-30603	TF34-6/2	6.0	2.0	0.70	30
333-30903	TF34-9/3	9.0	3.0	0.80	30
333-31203	TF34-12/4	12.0	4.0	0.85	30
333-31803	TF34-18/6	18.0	6.0	1.00	30
333-32403	TF34-24/8	24.0	8.0	1.20	30
333-34003	TF34-40/13	40.0	13.0	1.25	30

All dimensions in mm. Subject to technical changes.